Poly Sync 20-M Speakerphone +USB-A to USB-C Cable (7S4M1AA)

Overview

Quality sound made portable

Sound like the professional you are with Poly Sync 20 USB/Bluetooth® smart speakerphone — for conference calls and music anywhere you work. Take it wherever you go — it's got up to 20 hours of talk time.

Dynamic audio

Take conference room-quality audio on the go. Enjoy remarkable sound from meetings to music and reduced echo and noise so you can be heard clearly.

Works the way you do

A programable button puts your favorite function at your fingertips — play / pause music, last-number redial and voice assistant — it's up to you. What's the status of a call? Know from a distance with the highly visible light bar.

Additional specifications

Audio	Ideal for up to 4 m x 4 m room sizes; Full duplex audio; Noise and echo reduction; Bass reflect with dual passive radiators; Up to 7 ft / 2 m microphone pickup range
Battery life	Up to 20 hours (talk time)
Battery type	Rechargeable Li-ion
Bluetooth version	5.1
Button user controls	Power on/off; Bluetooth® pairing
Cable length	715 mm
Cable length (imperial)	28.1 in
Cartons per layer	10
Cartons per pallet	80
Certified collaboration software	Microsoft Teams
Charge time	<4 hours
Color	Black
Compatibility	Compatible with PCs via USB Type-A cable and smartphones via Bluetooth®
Compatible Operating Systems	Windows; macOS
Connection type	USB Type-A (PC); USB Type-C® (PC); Bluetooth® (smartphone)
Datasheet photo 1	https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08378917.png
Indicator light	On call
Management Software	Poly Lens; Plantronics Hub (desktop and mobile versions); Plantronics Manager Pro suites (Asset Management and Adoption)
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone type	Three-microphone steerable array
Minimum System Requirements	USB Type-A port; USB Type-C® port; Bluetooth®
Minimum dimensions (W x D x H)	1.3 x 3.7 x 7.2 in
Minimum dimensions (W x D x H)	34 x 95 x 182 mm
Nominal sound pressure level	86 dB SPL
Number of microphones	3
Package dimensions (W x D x H)	7.4 x 2.36 x 8.31 in
Package dimensions (W x D x H)	188 x 60 x 211 mm
Package weight	0.59 kg
Package weight	1.3 lb
Pallet (layers)	8

Pallet weight	516.2 kg
Pallet weight	1138.02 lb
Products per pallet	800
Products per pallet layer	100
Speaker size	40 mm
Supported bluetooth profiles	A2DP; AVRCP; HFP; HSP; BLE
Touch user controls	Call/answer end; Mute; Volume +/-; Programmable function button
UNSPSC code	43191638
Weight	360 g
Weight	0.79 lb
What's in the box	Wired Speakerphone; Travel case; Lanyard; BT600 Bluetooth® USB adapter

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly Sync 20 Case	85R77AA
Poly Sync 40 Charge Stand with Universal Power Supply	85R78AA
Poly Sync 40 Desk Mount	85R80AA
Poly Sync 60 Universal Power Supply	85R82AA

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Aug 17, 2023 7:09 AM UTC+0000