



USB-C 11-in-1 Triple-Monitor Docking Station with MST

USB 3.2 Type-C Male to HDMI, DP and VGA Females, Two USB 3.2 Gen 1, SuperSpeed (5 Gbps) Type-A Ports, USB 2.0 Type-A Port, USB-C PD Port, Gigabit RJ45 Port, SD/MicroSD Card Reader and 3.5 mm Audio Port; Aluminum, Dark Gray

Part No.: [153478](#)

EAN-13: 0766623153478 | UPC: 766623153478

The USB-C Docking Station with MST from Manhattan - drive three monitors at once with 11 connections to your device

Increase your productivity with your desktop, notebook or tablet using this highly versatile docking station from Manhattan. Its Multi-Stream Transport (MST) technology helps you to multitask on three monitors at the same time since it includes an HDMI, a DisplayPort and a VGA port.

Connections to all your peripherals

With three USB ports for mice, keyboards and flash drives, a 3.5 mm stereo port for a headset and two slots for SD/microSD cards, this docking station easily satisfies all your connectivity demands. Plus, its Gigabit RJ45 port provides the wired network connection that's missing in most modern Ultrabooks and Macbooks.

Up to 100 W charging power with USB-C Power Delivery (PD)

The included USB-C PD port lets you charge your notebook with up to 100 W while simultaneously charging your other mobile devices, such as smartphones or tablets through the USB-A ports. The Power Delivery function also provides faster charging than standard chargers since it determines the power needs of compatible devices and supplies it at the quickest and safest rate.

Take your phone to the big screen

Connect any Android 9 and later smartphone that supports video output over USB-C and enjoy your apps and media even more. Watch a video on your monitor or flip through the slides of your presentation – all from your phone.

A multiport adapter that's made to go where you go

Sturdy aluminum housing makes this multiport adapter the perfect travel companion. Despite its massive connectivity options, it's still compact enough to fit right in your backpack or computer bag with your main device. Thanks to its fold-out kickstand, you can place your laptop directly on the docking station.

Features:

- Multi-function docking station that connects a USB-C device to HDMI, DisplayPort and VGA displays simultaneously, two USB 3.2 Gen 1 Type-A ports, a USB 2.0 Type-A port, a 10/100/1000 Mbps Ethernet port, a 3.5 mm stereo port, a USB-C power port and an SD Card Reader
- Dual-video output with resolutions up to 1080p@60Hz or triple-video output with resolutions up to 720p@60Hz
- Up to 4K@30Hz (UHD) resolution on HDMI connection
- Up to 4K@30Hz (UHD) resolution on DisplayPort connection
- Up to 1080p@60Hz (Full HD) resolution on VGA connection
- Display modes in Mirror or Extended with Multi-Stream Transport (MST)
- Lets your smartphone work like a desktop PC* while also charging it
- One Gigabit Ethernet (10/100/1000) port for faster downloads, media streaming and gaming
- Two USB 3.2 Gen 1, SuperSpeed (5 Gbps) and one USB 2.0 type-A ports to connect mice, keyboards, flash drives and more or to charge and sync mobile devices
- USB-A SuperSpeed ports offering 5 Gbps data transmission speeds and supporting BC 1.2 to charge up to 7.5 W (5 V / 1.5 A)
- Micro SD and SD card slots with read/write function; supports automatic card detection and data transfer speeds up to 832 Mbps
- USB-C Power Delivery (PD) port (requires minimum 15-W-output PD wall charger) for a maximum of 100 W (20 V at 5 A) to connected devices
- Supports USB Power Delivery (PD) function up to 100 W; requires an external PD charger – available from Manhattan
- 3.5 mm jack for high-quality stereo sound; supports both a mic (audio input) and headphone (audio output)
- Aluminum housing for improved durability; converter is the perfect desktop or travel companion

- Fold-out kickstand to place your phone on the docking station
- Compatible with all USB-C DP-Alt-Mode-supported desktops, notebooks and tablets including Apple[®] MacBook[®], Chromebook[™], Pixel[™] and more
- Compliant with DisplayPort 1.2 Alternate Mode (DP Alt Mode)
- Fully shielded to reduce EMI and other interference sources
- Sturdy cable with molded PVC boot and nylon-braided protective jacket
- Plug and Play
- *Desktop setup requires devices with Android 9 or above that offer video output over USB-C
- Three-year warranty

Specifications:

Standards and Certifications

- DP 1.2 over USB-C
- USB 3.2 Gen 1
- HDMI 1.4
- HDCP 1.4
- CE
- FCC
- RoHS

General

- Video Resolutions: 640x480, 800x600, 1024x768, 1920x1200, 1920x1080, 3840x2160p
- USB-A ports 1 & 2 data transfer speed: 5 Gbps
- USB-A port 3 data transfer speed: 480 Mbps
- Supported flash cards: SD / SDHC / SDXC / EXTREME SD / EXTREME II SD / EXTREME III SD / ULTRA SD / ULTRA II SD / ULTRA II SD P PLUS / SD-ULTRA-X / ULTRA SPEED SD / SD PRO / SD ELITE PRO / HS SD / MMC / MMC 4.0 / HS MMC / HS RS MMC / RS MMC / RS MMC 4.0 / MMC Mobile
- Supported flash cards: SD, SDHC and SDXC up to 128 GB
- 34-AWG cable gauge
- Bus powered
- USB-C PD Charging Port: 100 W (20 V at 5 A)
- USB-A Charging: two BC 1.2 ports: 7.5 W (5 V at 1.5 A)
- Mylar and aluminum shielding
- Withstanding voltage: 300 VDC
- Insulation resistance: 10 MOhm
- Conductive resistance: 5 Ohm

Connections

- One USB-C 24-pin, male
- One HDMI 19-pin, female
- One DisplayPort 20-pin, female
- One VGA 15-pin, female

- One 10/100/1000 Mbps RJ45, female
- Three USB-A 4-pin, female
- One SD memory slot
- One Micro SD memory slot
- One 3.5 mm stereo, female
- One USB-C 24-pin, Power Delivery, female

Physical

- Dimensions: 260 x 88 x 23 mm (10.24 x 3.46 x 0.91 in.)
- Cable Length: 20 cm (8 in.)
- Weight: 340 g (12 oz.)
- Housing: aluminum

Operating Environment

- Operation temperature: 0 – 50°C (32 – 122°F)
- Storage temperature: -10 – 70°C (14 – 158°F)
- Humidity (noncondensing): 5 – 90% RH

System Requirements

- Windows 7/8.1/10, Linux or Mac 10.7.1 or above

Package Contents

- USB-C 11-in-1 Triple-Monitor Docking Station with MST
- Quick Instruction Guide



