



Wall Mounting Guide

Wall Mountable Switches

1.1 Wall Mounting Preparation

Before mounting the switch, you need to prepare the tools below:

- A screw driver.
- Two screws which complies to the corresponding standard. For details, see [Wall Mounting Specification](#).

1.2 Wall Mounting Procedure

On the bottom of the panel, there are two mounting holes. You need to drive two screws into the wall, then mount the switch on the wall. Note that the switch should be mounted on the wall upright rather than sideways. For TL-SF1008P/TL-SF1008LP/TL-SF1009P/TL-SG1008P, the switch should be mounted with the ports facing downward and the LEDs facing upward.

- 1) Determine the location on the wall where you want to mount the switch.
- 2) Mark the wall where the two mounting holes are. The distance between the two marks must be the same as that between the two mounting holes of the switch. For the wall-mounting-holes distance, see [Wall Mounting Specification](#).
- 3) Drive the screws into the wall at the marks using the screw driver. For the Screw-Head-to-Wall Minimum Distance, see [Wall Mounting Specification](#).
- 4) Mount the switch on the wall.

1.3 Wall Mounting Specification

Model	Screw Standard of ANSI B1.1	Minimum Length of Screw	Screw-Head-to-Wall Minimum Distance	Wall-Mounting-Holes Distance
DS105G	4#, (5#), 6#, 8#	7.5mm	1.5mm	39mm
DS105GE	4#, (5#), 6#	7.5mm	1.5mm	52mm
DS105G-M2	4#, (5#), 6#	7.5mm	1.5mm	52mm
DS105GP	4#, (5#), 6#, 8#	8.5mm	1.5mm	39mm
DS105X	4#, (5#), 6#	7.5mm	1.5mm	150mm
DS106GPP	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
DS106P	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
DS108G	4#, (5#), 6#, 8#	7.5mm	1.5mm	94mm
DS108GE	4#, (5#), 6#	7.5mm	1.5mm	110mm
DS108G-M2	4#, (5#), 6#	7.5mm	1.5mm	110mm
DS108GP	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
DS110GMP	4#, (5#), 6#	8.5mm	1.5mm	150mm
DS110GMP2C	4#, (5#), 6#	8.5mm	1.5mm	150mm

Model	Screw Standard of ANSI B1.1	Minimum Length of Screw	Screw-Head-to-Wall Minimum Distance	Wall-Mounting-Holes Distance
DS111P	4#, (5#), 6#	8.5mm	1.5mm	150mm
DS116GE	4#, (5#), 6#	8.5mm	1.5mm	200mm
ES205G	4#, (5#), 6#	11mm	4.5mm	52mm
ES205GP	4#	10mm	4.5mm	39mm
ES210GMP	4#, (5#), 6#	8.5mm	1.5mm	150mm
Festa FS308G	4#, (5#), 6#	8.5mm	1.5mm	150mm
Festa FS308GP	4#, (5#), 6#	8.5mm	1.5mm	150mm
Festa FS310GP	4#, (5#), 6#	8.5mm	1.5mm	150mm
LS1005G	4#, (5#), 6#	8.5mm	2.5mm	38mm
LS1008G	4#, (5#), 6#	8.5mm	2.5mm	48mm
LS105G	4#, (5#), 6#	7.5mm	1.5mm	76mm
LS105GP	4#, (5#), 6#	7.5mm	1.5mm	65mm
LS105LP	4#, (5#), 6#, 8#	8.5mm	1.5mm	39mm
LS106LP	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
LS108G	4#, (5#), 6#	7.5mm	1.5mm	65mm
LS108GP	4#, (5#), 6#	7.5mm	1.5mm	65mm
LS109P	4#, (5#), 6#, 8#	8.5mm	1.5mm	105mm
LS1210GP	4#, (5#), 6#	7.5mm	1.5mm	150mm
S4500-16GP	4#, (5#), 6#	8.5mm	1.5mm	200mm
S4500-8G	4#, (5#), 6#	8.5mm	1.5mm	150mm
S4500-8GP	4#, (5#), 6#	8.5mm	1.5mm	150mm
S4500-8GP2F	4#, (5#), 6#	8.5mm	1.5mm	150mm
SG2008	4#, (5#), 6#	8.5mm	1.5mm	150mm
SG2008P	4#, (5#), 6#	8.5mm	1.5mm	150mm
SG2016P	4#, (5#), 6#	8.5mm	1.5mm	200mm
SG2210P	4#, (5#), 6#	8.5mm	1.5mm	150mm
SG2210XMP-M2	4#, (5#), 6#	8.5mm	1.5mm	150mm
T1500G-8T	4#, (5#), 6#	8.5mm	1.5mm	150mm
TL-RP108GE	4#, (5#), 6#	8.5mm	1.5mm	65mm
TL-SF1005LP	4#, (5#), 6#, 8#	8.5mm	1.5mm	39mm
TL-SF1005P	4#, (5#), 6#, 8#	8.5mm	1.5mm	39mm

Model	Screw Standard of ANSI B1.1	Minimum Length of Screw	Screw-Head-to-Wall Minimum Distance	Wall-Mounting-Holes Distance
TL-SF1006P	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
TL-SF1008LP	4#, (5#), 6#, 8#	8.5mm	1.5mm	105mm
TL-SF1008P	4#, (5#), 6#, 8#	8.5mm	1.5mm	105mm
TL-SF1009P	4#, (5#), 6#, 8#	8.5mm	1.5mm	105mm
TL-SF1016D	4#, (5#), 6#	9mm	3mm	157.2mm
TL-SG1005D	4#	10mm	4.5mm	60mm
TL-SG1005LP	4#, (5#), 6#, 8#	8.5mm	1.5mm	39mm
TL-SG1005P	4#, (5#), 6#, 8#	8.5mm	1.5mm	39mm
TL-SG1005P-PD	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
TL-SG1006PP	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
TL-SG1008D	4#	10mm	4mm	100mm
TL-SG1008P	4#, (5#), 6#, 8#	8.5mm	1.5mm	105mm
TL-SG105	4#, (5#), 6#, 8#	7.5mm	1.5mm	39mm
TL-SG105E	4#, (5#), 6#	7.5mm	1.5mm	52mm
TL-SG105-M2	4#, (5#), 6#	7.5mm	1.5mm	150mm
TL-SG105MPE	4#, (5#), 6#, 8#	8.5mm	1.5mm	39mm
TL-SG105PE	4#, (5#), 6#, 8#	7.5mm	1.5mm	39mm
TL-SG105PP-M2	4#, (5#), 6#	7.5mm	1.5mm	150mm
TL-SG105S	4#, (5#), 6#, 8#	7.5mm	1.5mm	39mm
TL-SG105S-M2	4#, (5#), 6#	7.5mm	1.5mm	52mm
TL-SG108	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
TL-SG108E	4#, (5#), 6#	7.5mm	1.5mm	110mm
TL-SG108-M2	4#, (5#), 6#	7.5mm	1.5mm	150mm
TL-SG108PE	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
TL-SG108S	4#, (5#), 6#, 8#	7.5mm	1.5mm	94mm
TL-SG108S-M2	4#, (5#), 6#	7.5mm	1.5mm	110mm
TL-SG116	4#, (5#), 6#	8.5mm	1.5mm	200mm
TL-SG116E	4#, (5#), 6#	8.5mm	1.5mm	200mm
TL-SG116P	4#, (5#), 6#	8.5mm	1.5mm	200mm
TL-SG1210MP	4#, (5#), 6#	8.5mm	1.5mm	150mm
TL-SG1210MPE	4#, (5#), 6#	8.5mm	1.5mm	150mm

Model	Screw Standard of ANSI B1.1	Minimum Length of Screw	Screw-Head-to-Wall Minimum Distance	Wall-Mounting-Holes Distance
TL-SG1210P	4#, (5#), 6#	7.5mm	1.5mm	150mm
TL-SG1210PP	4#, (5#), 6#	7.5mm	1.5mm	150mm
TL-SG2008	4#, (5#), 6#	8.5mm	1.5mm	150mm
TL-SG2008P	4#, (5#), 6#	8.5mm	1.5mm	150mm
TL-SG2016P	4#, (5#), 6#	8.5mm	1.5mm	200mm
TL-SG2210P	4#, (5#), 6#	8.5mm	1.5mm	150mm
TL-SG605	4#, (5#), 6#, 8#	7.5mm	1.5mm	39mm
TL-SG605E	4#, (5#), 6#	7.5mm	1.5mm	52mm
TL-SG605P	4#, (5#), 6#, 8#	7.5mm	1.5mm	39mm
TL-SG608	4#, (5#), 6#, 8#	8.5mm	1.5mm	94mm
TL-SG608E	4#, (5#), 6#	7.5mm	1.5mm	110mm
TL-SG608P	4#, (5#), 6#, 8#	8.5mm	1.5mm	105mm
TL-SL1311MP	4#, (5#), 6#	8.5mm	1.5mm	150mm
TL-SL1311P	4#, (5#), 6#	8.5mm	1.5mm	150mm
TL-SX105	4#, (5#), 6#	7.5mm	1.5mm	150mm