


OVERVIEW



1. Volume control toggle	6. DC-in
2. Headphone / microphone combo jack (3.5mm)	7. 2x USB 3.2 Gen 1
3. 2x Ethernet (RJ-45)	8. USB-C 3.2 Gen 1
4. HDMI-in	9. Kensington MiniSaver lock slot
5. 2x HDMI-out	10. USB-C 2.0 (for ThinkSmart Controller)

Notes:

- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

11th Generation Intel® Core™ i5 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i5-1145G7E	4	8	1.5GHz	4.1GHz ^[1]	8MB	DDR4-3200	Intel Iris® Xe Graphics

Notes:

[1] Intel Max Turbo frequency will vary depending on application workload and the hardware and software configurations, see

<http://www.intel.com/technology/turboboost/> for more information.

Operating System

Operating System

- Windows® 10 IoT Enterprise
- Windows 11 IoT Enterprise

Graphics

Graphics

Graphics	Type	Memory	Connector	Max Resolution
Intel Iris Xe Graphics	Integrated	Shared	2x HDMI®	4096x2304@30Hz(HDMI)

Monitor Support

Monitor Support

Supports up to 2 external monitors via 2x HDMI

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory

16GB soldered memory, not upgradable

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Memory Type

DDR4-3200

Storage

Storage Support

One drive, 256GB M.2 2280 SSD

Storage Type

Disk Type	Interface	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe 3.0 x4	Opal

Multi-Media

Speakers

Stereo speakers, 15W x2, 85+/-3dB sound pressure level (SPL)

Microphone

Eight microphones for 180° audio capture, 6m pickup range, -35dBFS sensitivity

Camera

ThinkSmart One for Zoom

Field of View: 125 degree (D) / 100 degree (H) / 68 degree (V)

Power Supply

Power Supply

Power	Type	Efficiency	Key Features
135W	Adapter	89%	Autosensing

DESIGN

Mechanical

Controller**

Component Name	Display	Sensors	Multi-touch	Ports	Key Features
Lenovo® IP Controller	<ul style="list-style-type: none"> • 10.1" Display, HD (1280x800) • 360 nits brightness • 16:10 aspect ratio • Anti-Fingerprint 	IR sensors for motion detection, up to 3 meters distance and 90° angle	10-point touch	<ul style="list-style-type: none"> • 1x Gigabit Ethernet (RJ-45) • 1x Kensington® Security Slot™ • 1x HDMI-in (on Link Box) • 1x Power Connector (on Link Box) • 1x Gigabit Ethernet (RJ-45, on Link Box) • 1x HDMI out (on Link Box) • 1x USB-B (on Link Box) 	Wall mountable (For wall mounting, mount kits are needed. The kits are sold separately and coming soon)
ThinkSmart™ Controller	<ul style="list-style-type: none"> • 10.1" Display, HD (1280x800) • Up to 340 nits brightness • 16:10 aspect ratio • Anti-Fingerprint, Anti-Glare • 30° or 60° rotatable 	IR sensors for motion detection, up to 3 meters distance and 90° angle	10-point touch	<ul style="list-style-type: none"> • 1x USB-C® (connect to compute unit, 10m USB-C cable included) • 1x 3.5mm headphone / mic combo jack • 1x Kensington Security Slot 	-

LED indicators

- LED Clock on right bottom
- LED RGB Light bar, indicates power and communication states

Dimensions (WxDxH)^[1]

Models	Dimensions
ThinkSmart controller	265.5 x 13 x 168.1 mm (10.5 x 0.5 x 6.6 inches)
ThinkSmart One (Bar Only)	700 x 89 x 110 mm (27.56 x 3.5 x 4.33 inches)
Link Box	210 x 96 x 27 mm (8.27 x 3.78 x 1.06 inches)
Lenovo IP controller	248 x 151 x 100 mm (9.76 x 5.94 x 3.94 inches)

Weight^[2]

Models	Weight
Lenovo IP controller	Around 0.97 kg (2.16 lbs)
Link Box	Around 212 g (0.45 lbs)
ThinkSmart One (Bar Only)	Around 3.55 kg (7.83 lbs)
ThinkSmart controller	753.8 g (1.7 lbs)

Case Color

Black

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

Gigabit Ethernet, 2x RJ-45

WLAN + Bluetooth®

Intel Wi-Fi® 6E AX210, 802.11ax 2x2 Wi-Fi + Bluetooth 5.0, M.2 Card

Ports^[1]

Rear Ports

- 1x USB-C 2.0 (display only)
- 1x USB-C 3.2 Gen 1
- 2x USB 3.2 Gen 1
- 1x HDMI-in
- 2x HDMI-out
- 2x Ethernet (one supports POE, one with vPro®)

Right Ports

1x headphone / microphone combo jack (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

Physical Locks

- Integrated cable management
- Kensington MicroSaver® lock Slot

Other Security

Camera privacy shutter

MANAGEABILITY

System Management

System Management

Intel vPro Enterprise

SERVICE

Warranty^[1]

Base Warranty

3-year limited onsite service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

SOFTWARE

Preinstalled Software

Preinstalled Software

Zoom Rooms Application (for MT 12BU / 12BV)

- This is a telepresence technology product.
- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

