Poly Savi 8410 Office Monaural DECT 1920-1930 MHz Headset

Built for the modern office

Ready for the modern office with an intuitive user interface on the universal base that can connect to almost any Savi headset. Ensure flexibility for users with the ability to connect from your computer, desk phone or mobile phone [1].

Be heard clearly With the Poly Savi 8400 Office series headset system, you can stay focused on your tasks while enjoying crystal-clear conversations thanks to a noise-canceling microphone with close conversation limiting.	**Untether from your desk** Enjoy the convenience of hands-free calling and a longer roaming range with the Poly Savi 8400 office series. With up to 13 hours of talk time and the ability to roam up to 590 ft / 180 m means you can keep the calls going, even away from the desk [2].	**Multi-device connectivity** Designed for the modern office with 3-way connectivity, the Poly Savi 8400 office series is the perfect solution for business calls allowing you to stay connected in the office. You can even conference four headsets together with the base for increased productivity.

3-way connectivity
Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Crystal-clear calls
Reduce background sounds with noise-canceling microphone and close conversation limiting.

Take it further
Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

Privacy is ensured
Privacy of your conversation is ensured: DECT™ security-certified headset.

Poly Savi 8410 Office Monaural DECT 1920-1930 MHz Headset

Specifications

Compatible with

Compatible operating systems: macOS; Windows

Connectivity and communications

Wireless range: Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial): Up to 590 ft in open area; Up to 180 ft in typical office environment
Bluetooth version: 5.2
Supported bluetooth profiles: A2DP; HFP; HSP
Connection type: Bluetooth®; DECT™
Ear cushions: Artificial leather (surface material)
Headphone type: On-ear (monoaural)
Base controls: Scroll wheel; Back key; USB softphone line button; Bluetooth® line button; Telephone interface line button; Configurable button

User interface features

Button user controls: Power on/off; Call answer/end; Mute; Volume +/-

Audio

Speaker bandwidth: 100 Hz to 6.8 kHZ (wideband mode); 20 Hz to 20 kHZ (multimedia mode)
Speaker size: 32 mm
Charge time: 3 hours
Frequency response (microphone): 100 Hz to 6.8 kHz
Sensitivity (microphone): 112 dB SPL

Battery

Battery life: Up to 13 hours (talk time)
Battery description: Rechargeable Li-ion polymer
Battery capacity: 490 mAh
Impedance: 32 ohms

Certifications

Special features: Color display on office base for audio settings management

Applications supported

Management software:
Poly Lens

Minimum system requirements

USB Type-A port (PC); USB Type-C® port (PC); Bluetooth® (mobile phone); EHS interface (desk phone)

Weight and dimensions

Product Primary Color: Black
Weight (imperial): 0.25 lb
Weight (metric): 115 g
UPC number: 197497815122
Product number: 8L7E6AA

Warranty

Poly standard two-year limited warranty

What is in the box

Wireless headset
USB Type-A cable
USB Type-C® cable
Office base
AC power adapter
Charging cradle
Telephone interface cable (TIC)

Key Selling Points Footnotes

[1] Does not connect to the Savi 7200 headset. [2] Line of sight from computer. [3] Visit www.poly.com/savi-8400-office for more detail.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

July 2023