

Overview

DDR4 Memory for HP Business Desktop PCs

Models

DDR4-2133 Memory UDIMMs

HP 4GB DDR4-2133 UDIMM

P1N51AA/P1N51AT

HP 8GB DDR4-2133 UDIMM

P1N52AA/P1N52AT

HP 16GB DDR4-2133 UDIMM

Y3X96AA/Y3X96AT

DDR4-2400 Memory UDIMMs

HP 4GB DDR4-2400 UDIMM

Z9H59AA/Z9H59AT

HP 8GB DDR4-2400 UDIMM

Z9H60AA/Z9H60AT

HP 16GB DDR4-2400 UDIMM

Z9H57AA/Z9H57AT

DDR4-2133 Memory SoDIMMs

HP 4GB DDR4-2133 SoDIMM

P1N53AA/P1N53AT

HP 8GB DDR4-2133 SoDIMM

P1N54AA/P1N54AT

HP 16GB DDR4-2133 SoDIMM

P1N55AA/P1N55AT

DDR4-2400 Memory SoDIMMs

HP 4GB DDR4-2400 SoDIMM

Z9H55AA/Z9H55AT

HP 8GB DDR4-2400 SoDIMM

Z9H56AA/Z9H56AT

HP 16GB DDR4-2400 SoDIMM

Z9H53AA/Z9H53AT

DDR4-2666 Memory UDIMMs

HP 4GB DDR4-2666 UDIMM

3TK85AA/3TK85AT

HP 8GB DDR4-2666 UDIMM

3TK87AA/3TK87AT

HP 16GB DDR4-2666 UDIMM

3TK83AA/3TK83AT

HP 32GB DDR4-2666 UDIMM

1C918AA/1C918AT

DDR4-2666 Memory SoDIMMs

HP 4GB DDR4-2666 SoDIMM

3TK86AA/3TK86AT

HP 8GB DDR4-2666 SoDIMM

3TK88AA/3TK88AT

HP 16GB DDR4-2666 SoDIMM

3TK84AA/3TK84AT

HP 32GB DDR4-2666 SoDIMM

1C919AA/1C919AT

DDR4-3200 Memory UDIMMs

HP 4GB DDR4-3200 UDIMM *New!*

13L78AA/13L78AT

HP 8GB DDR4-3200 UDIMM *New!*

13L76AA/13L76AT

HP 16GB DDR4-3200 UDIMM *New!*

13L74AA/13L74AT

HP 32GB DDR4-3200 UDIMM *New!*

13L72AA/13L72AT

DDR4-3200 Memory SoDIMMs

HP 4GB DDR4-3200 SoDIMM *New!*

13L79AA/13L79AT

HP 8GB DDR4-3200 SoDIMM *New!*

13L77AA/13L77AT

HP 16GB DDR4-3200 SoDIMM *New!*

13L75AA/13L75AT

HP 32GB DDR4-3200 SoDIMM *New!*

13L73AA/13L73AT

Key Benefits



Overview

- Dual channel configuration - HP Desktops feature motherboards designed with two memory channels instead of a single channel.
 - Reduce system latencies and significantly improve your system performance with dual channel memory configurations by utilizing the theoretical bandwidth of two memory modules instead of one.
 - Expect fast start-up times with reduced delays during routine operations and system maintenance functions. Meet everyday workloads head on, and run more programs simultaneously. Easily toggle back and forth between several open applications with noticeable speed.
-

Service and Support

Your Option Limited Warranty is a one (1) year (HP Option Limited Warranty Period) parts replacement warranty on any HP-branded or Compaq-branded options (HP Options). If your HP Option is installed in an HP Hardware Product, HP may provide warranty service either for the HP Option Limited Warranty Period or the remaining Limited Warranty Period of the HP Hardware Product in which the HP Option is being installed, whichever period is the longer but not to exceed three (3) years from the date you purchased the HP Option.

Technical Specifications

DDR4-2133 Memory UDIMMs

Kit Size	# of DIMMs	Compatibility*	Data Rate**	# of Pins	Motherboard Keynotch
HP 4GB UDIMM (P1N51AA/P1N51AT)	1	HP 280 G2 MT, HP ProDesk 400 G3 SFF, HP ProDesk 400 G3 MT, HP ProDesk 600 G2 MT, HP ProDesk 600 G2 SFF, HP EliteDesk 800 G2 TWR, HP EliteDesk 800 G1 TWR and HP EliteDesk 800 G2 SFF NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2133 MT/s	288	Single
HP 8GB UDIMM (P1N52AA/P1N52AT)	1	HP 280 G2 MT, HP ProDesk 400 G3 SFF, HP ProDesk 400 G3 MT, HP ProDesk 600 G2 MT, HP ProDesk 600 G2 SFF, HP EliteDesk 800 G2 TWR, HP EliteDesk 800 G1 TWR and HP EliteDesk 800 G2 SFF NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2133 MT/s	288	Single
HP 16GB DDR4-2133 UDIMM (Y3X96AA/Y3X96AT)	1	HP 280 G2 MT, HP 280 G2 SFF, HP ProDesk 400 G3 SFF, HP ProDesk 400 G3 MT, HP ProDesk 490 G3 MT, HP ProDesk 600 G2 MT, HP ProDesk 600 G2 SFF, HP EliteDesk 705 G3 MT, HP EliteDesk 705 G3 SFF, HP EliteDesk 800 G2 TWR, HP EliteDesk 800 G2 SFF NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2133 MT/s	288	Single

Technical Specifications

DDR4-2133 Memory SoDIMMs

Kit Size	# of SoDIMMs	Compatibility*	Data Rate**	# of Pins	Motherboard Keynotch
HP 4GB SoDIMM (P1N53AA/P1N53AT)	1	<p>HP 260 G2 DM, HP ProDesk 400 G2 DM, HP ProOne 400 G2 AiO Touch, HP ProOne 400 G2 AiO Non-Touch, HP ProDesk 600 G2 DM, HP ProOne 600 G2 AiO 21.5-inch Touch, HP ProOne 600 G2 AiO 21.5-inch Non-Touch, HP EliteDesk 800 G2 35W DM, HP EliteDesk 800 G2 65W DM, HP Collaboration PC G2, HP EliteOne 800 G2 AIO 23" Touch, HP EliteOne 800 G2 AIO 23" Non-Touch</p> <p>NOTE: Please check this product's web page on HP.com for current compatibility information.</p>	Transfer rates up to 2133 MT/s	260	Single
HP 8GB SoDIMM (P1N54AA/P1N54AT)	1	<p>HP 260 G2 DM, HP ProDesk 400 G2 DM, HP ProOne 400 G2 AiO Touch, HP ProOne 400 G2 AiO Non-Touch, HP ProDesk 600 G2 DM, HP ProOne 600 G2 AiO 21.5-inch Touch, HP ProOne 600 G2 AiO 21.5-inch Non-Touch, HP EliteDesk 800 G2 35W DM, HP EliteDesk 800 G2 65W DM, HP Collaboration PC G2, HP EliteOne 800 G2 AIO 23" Touch, HP EliteOne 800 G2 AIO 23" Non-Touch</p> <p>NOTE: Please check this product's web page on HP.com for current compatibility information.</p>	Transfer rates up to 2133 MT/s	260	Single
HP 16GB SoDIMM (P1N55AA/P1N55AT)	1	<p>HP 260 G2 DM, HP ProDesk 400 G2 DM, HP ProOne 400 G2 AiO Touch, HP ProOne 400 G2 AiO Non-Touch, HP ProDesk 600 G2 DM, HP ProOne 600 G2 AiO 21.5-inch Touch, HP ProOne 600 G2 AiO 21.5-inch Non-Touch, HP EliteDesk 800 G2 35W DM, HP EliteDesk 800 G2 65W DM, HP Collaboration PC G2, HP EliteOne 800 G2 AIO 23" Touch, HP EliteOne 800 G2 AIO 23" Non-Touch</p> <p>NOTE: Please check this product's web page on HP.com for current compatibility information.</p>	Transfer rates up to 2133 MT/s	260	Single

Technical Specifications

DDR4-2400 Memory UDIMMs

Kit Size	# of DIMMs	Compatibility*	Data Rate***	# of Pins	Motherboard Keynotch
HP 4GB DDR4-2400 UDIMM (3TK85AA/3TK85AT)	1	HP ProDesk 400 G4 SFF, HP ProDesk 400 G4 MT, HP ProDesk 600 G3 MT, HP ProDesk 600 G3 SFF, HP EliteDesk 800 G3 TWR, HP EliteDesk 800 G3 SFF NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2400 MT/s	288	Single
HP 8GB DDR4-2400 UDIMM (Z9H60AA/Z9H60AT)	1	HP ProDesk 400 G4 SFF, HP ProDesk 400 G4 MT, HP ProDesk 600 G3 MT, HP ProDesk 600 G3 SFF, HP EliteDesk 800 G3 TWR, HP EliteDesk 800 G3 SFF NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2400 MT/s	288	Single
HP 16GB DDR4-2400 UDIMM (Z9H57AA/Z9H57AT)	1	HP ProDesk 400 G4 SFF, HP ProDesk 400 G4 MT, HP ProDesk 600 G3 MT, HP ProDesk 600 G3 SFF, HP EliteDesk 800 G3 TWR, HP EliteDesk 800 G3 SFF NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2400 MT/s	288	Single

Technical Specifications

DDR4-2400 Memory SoDIMMs

Kit Size	# of SoDIMMs	Compatibility*	Data Rate***	# of Pins	Motherboard Keynotch
HP 4GB DDR4-2400 SoDIMM (Z9H55AA/Z9H55AT)	1	The HP 4GB DDR4-2400 SoDIMM is compatible with the HP ProDesk 400 G3 DM (Mini); HP ProOne 400 G3 AIO Touch; HP ProOne 400 G3 AIO Non-Touch; HP ProDesk 600 G3 Desktop Mini; HP ProOne 600 G3 AIO 21.5" Non-Touch; HP EliteDesk 800 G3 35W Desktop Mini; HP EliteDesk 800 G3 65W Desktop Mini; HP EliteOne 800 G3 AIO 23.8" NT; HP EliteOne 800 G3 AIO 23.8" Touch; HP EliteOne 1000 G1 AiO; HP Elite Slice; HP Elite Slice for Meeting Rooms. NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2400 MT/s	260	Single
HP 8GB DDR4-2400 SoDIMM (Z9H56AA/Z9H56AT)	1	HP EliteDesk 800 G3 35W Desktop Mini, HP EliteDesk 800 G3 65W Desktop Mini, HP ProDesk 600 G3 Desktop Mini, HP ProDesk 400 G3 DM (Mini) NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2400 MT/s	260	Single
HP 16GB DDR4-2400 SoDIMM (Z9H53AA/Z9H53AT)	1	HP EliteDesk 800 G3 35W Desktop Mini, HP EliteDesk 800 G3 65W Desktop Mini, HP ProDesk 600 G3 Desktop Mini, HP ProDesk 400 G3 DM (Mini) NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2400 MT/s	260	Single

DDR4-2666 Memory UDIMMs

Kit Size	# of DIMMs	Compatibility*	Data Rate***	# of Pins	Motherboard Keynotch
HP 4GB DDR4-2666 UDIMM (3TK85AA/3TK85AT)	1	HP 280 G3/4/5 Small Form Factor, HP 280 G4/5/6 MT / 290 G2/3/4 Microtower, HP ProDesk 400 G5/6/7 Small Form Factor, HP ProDesk 400 G5/6/7 Microtower, HP ProDesk 600 G4/5/6 Microtower, HP ProDesk 600 G4/5/6 Small Form Factor, HP EliteDesk 705 G4 Microtower, HP EliteDesk 705 G4/5 Small Form Factor, EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G4/5/6 Microtower, HP EliteDesk 800 G4/5/6 Small Form Factor	Transfer rates up to 2666 MT/s	288	Single

Technical Specifications

		NOTE: Please check this product's web page on HP.com for current compatibility information.			
HP 8GB DDR4-2666 UDIMM (3TK87AA/3TK87AT)	1	HP 280 G3/4/5 Small Form Factor, HP 280 G4/5/6 MT / 290 G2/3/4 Microtower, HP ProDesk 400 G5/6/7 Small Form Factor, HP ProDesk 400 G5/6/7 Microtower, HP ProDesk 600 G4/5/6 Microtower, HP ProDesk 600 G4/5/6 Small Form Factor, HP EliteDesk 705 G4 Microtower, HP EliteDesk 705 G4/5 Small Form Factor, EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G4/5/6 Microtower, HP EliteDesk 800 G4/5/6 Small Form Factor NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2666 MT/s	288	Single
HP 16GB DDR4-2666 UDIMM (3TK83AA/3TK83AT)	1	HP 280 G3/4/5 Small Form Factor, HP 280 G4/5/6 MT / 290 G2/3/4 Microtower, HP ProDesk 400 G5/6/7 Small Form Factor, HP ProDesk 400 G5/6/7 Microtower, HP ProDesk 600 G4/5/6 Microtower, HP ProDesk 600 G4/5/6 Small Form Factor, HP EliteDesk 705 G4 Microtower, HP EliteDesk 705 G4/5 Small Form Factor, EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G4/5/6 Microtower, HP EliteDesk 800 G4/5/6 Small Form Factor NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2666 MT/s	288	Single
HP 32GB DDR4-2666 UDIMM (1C918AA/1C918AT)	1	HP 280 G3/4/5 Small Form Factor, HP 280 G4/5/6 MT / 290 G2/3/4 Microtower, HP ProDesk 400 G5/6/7 Small Form Factor, HP ProDesk 400 G5/6/7 Microtower, HP ProDesk 600 G4/5/6 Microtower, HP ProDesk 600 G4/5/6 Small Form Factor, HP EliteDesk 705 G4 Microtower, HP EliteDesk 705 G4/5 Small Form Factor, EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G4/5/6 Microtower, HP EliteDesk 800 G4/5/6 Small Form Factor NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2666 MT/s	288	Single

Technical Specifications

DDR4-2666 Memory SoDIMMs

Kit Size	# of SoDIMMs	Compatibility*	Data Rate***	# of Pins	Motherboard Keynotch
HP 4GB DDR4-2666 SoDIMM (3TK86AA/3TK86AT)	1	HP ProDesk 400 G4/5/6 Desktop Mini, HP ProDesk 600 G4/5/6 Desktop Mini, HP EliteDesk 705 G4/5 Desktop Mini, HP EliteDesk 800 G4/5/6 95W Desktop Mini, HP Collaboration PC G4/5, HP EliteOne 800 G4/5/6 AiO G4/5 23.8 HC (NT), HP EliteOne 1000 G2 AiO, HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2666 MT/s	260	Single
HP 8GB DDR4-2666 SoDIMM (3TK88AA/3TK88AT)	1	HP ProDesk 400 G4/5/6 Desktop Mini, HP ProDesk 600 G4/5/6 Desktop Mini, HP EliteDesk 705 G4/5 Desktop Mini, HP EliteDesk 800 G4/5/6 95W Desktop Mini, HP Collaboration PC G4/5, HP EliteOne 800 G4/5/6 AiO G4/5 23.8 HC (NT), HP EliteOne 1000 G2 AiO, HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2666 MT/s	260	Single
HP 16GB DDR4-2666 SoDIMM (3TK84AA/3TK84AT)	1	HP ProDesk 400 G4/5/6 Desktop Mini, HP ProDesk 600 G4/5/6 Desktop Mini, HP EliteDesk 705 G4/5 Desktop Mini, HP EliteDesk 800 G4/5/6 95W Desktop Mini, HP Collaboration PC G4/5, HP EliteOne 800 G4/5/6 AiO G4/5 23.8 HC (NT), HP EliteOne 1000 G2 AiO, HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2666 MT/s	260	Single
HP 32GB DDR4-2666 SoDIMM (1C919AA/1C919AT)	1	HP ProDesk 400 G4/5/6 Desktop Mini, HP ProDesk 600 G4/5/6 Desktop Mini, HP EliteDesk 705 G4/5 Desktop Mini, HP EliteDesk 800 G4/5/6 95W Desktop Mini, HP Collaboration PC G4/5, HP EliteOne 800 G4/5/6 AiO G4/5 23.8 HC (NT), HP EliteOne 1000 G2 AiO, HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 2666 MT/s	260	Single

Technical Specifications

DDR4-3200 Memory UDIMMs

Kit Size	# of DIMMs	Compatibility*	Data Rate***	# of Pins	Motherboard Keynotch
HP 4GB DDR4-3200 UDIMM (13L78AA/13L78AT)	1	HP 280 G4/5 Small Form Factor, HP 280 G5/6 MT / 290 G3/4 Microtower, HP ProDesk 400 G6/7 Small Form Factor, HP ProDesk 400 G6/7 Microtower, HP ProDesk 600 G5/6 Microtower, HP ProDesk 600 G5/6 Small Form Factor, HP EliteDesk 705 G5 Small Form Factor, HP EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G5/6 Microtower, HP EliteDesk 800 G5/6 Small Form Factor NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	288	Single
HP 8GB DDR4-3200 UDIMM (13L76AA/13L76AT)	1	HP 280 G4/5 Small Form Factor, HP 280 G5/6 MT / 290 G3/4 Microtower, HP ProDesk 400 G6/7 Small Form Factor, HP ProDesk 400 G6/7 Microtower, HP ProDesk 600 G5/6 Microtower, HP ProDesk 600 G5/6 Small Form Factor, HP EliteDesk 705 G5 Small Form Factor, HP EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G5/6 Microtower, HP EliteDesk 800 G5/6 Small Form Factor NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	288	Single
HP 16GB DDR4-3200 UDIMM (13L74AA/13L74AT)	1	HP 280 G4/5 Small Form Factor, HP 280 G5/6 MT / 290 G3/4 Microtower, HP ProDesk 400 G6/7 Small Form Factor, HP ProDesk 400 G6/7 Microtower, HP ProDesk 600 G5/6 Microtower, HP ProDesk 600 G5/6 Small Form Factor, HP EliteDesk 705 G5 Small Form Factor, HP EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G5/6 Microtower, HP EliteDesk 800 G5/6 Small Form Factor NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	288	Single
HP 32GB DDR4-3200 UDIMM (13L72AA/13L72AT)	1	HP 280 G4/5 Small Form Factor, HP 280 G5/6 MT / 290 G3/4 Microtower, HP ProDesk 400 G6/7 Small Form Factor, HP ProDesk 400 G6/7 Microtower, HP ProDesk 600 G5/6 Microtower, HP ProDesk 600 G5/6 Small Form Factor NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	288	Single

Technical Specifications

		<p>Microtower, HP ProDesk 600 G5/6 Small Form Factor, HP EliteDesk 705 G5 Small Form Factor, HP EliteDesk 805 G6 Small Form Factor, HP EliteDesk 800 G5/6 Microtower, HP EliteDesk 800 G5/6 Small Form Factor</p> <p>NOTE: Please check this product's web page on HP.com for current compatibility information.</p>			
--	--	---	--	--	--

Technical Specifications

DDR4-3200 Memory SoDIMMs

Kit Size	# of SoDIMMs	Compatibility*	Data Rate***	# of Pins	Motherboard Keynotch
HP 4GB DDR4-3200 SoDIMM (13L79AA/13L79AT)	1	HP ProDesk 400 G5/6 Desktop Mini, HP ProDesk 600 G5/6 Desktop Mini, HP EliteDesk 705 G5 Desktop Mini, HP EliteDesk 805 G6 Desktop Mini, HP EliteDesk 800 G5/6 95W Desktop Mini, HP Collaboration PC G5, HP EliteOne 800 G5/6 AiO G5 23.8 HC (NT), HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	260	Single
HP 8GB DDR4-3200 SoDIMM (13L77AA/13L77AT)	1	HP ProDesk 400 G5/6 Desktop Mini, HP ProDesk 600 G5/6 Desktop Mini, HP EliteDesk 705 G5 Desktop Mini, HP EliteDesk 805 G6 Desktop Mini, HP EliteDesk 800 G5/6 95W Desktop Mini, HP Collaboration PC G5, HP EliteOne 800 G5/6 AiO G5 23.8 HC (NT), HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	260	Single
HP 16GB DDR4-3200 SoDIMM (13L75AA/13L75AT)	1	HP ProDesk 400 G5/6 Desktop Mini, HP ProDesk 600 G5/6 Desktop Mini, HP EliteDesk 705 G5 Desktop Mini, HP EliteDesk 805 G6 Desktop Mini, HP EliteDesk 800 G5/6 95W Desktop Mini, HP Collaboration PC G5, HP EliteOne 800 G5/6 AiO G5 23.8 HC (NT), HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	260	Single
HP 32GB DDR4-3200 SoDIMM (13L73AA/13L73AT)	1	HP ProDesk 400 G5/6 Desktop Mini, HP ProDesk 600 G5/6 Desktop Mini, HP EliteDesk 705 G5 Desktop Mini, HP EliteDesk 805 G6 Desktop Mini, HP EliteDesk 800 G5/6 95W Desktop Mini, HP Collaboration PC G5, HP EliteOne 800 G5/6 AiO G5 23.8 HC (NT), HP Elite Slice for Meeting Rooms G2 NOTE: Please check this product's web page on HP.com for current compatibility information.	Transfer rates up to 3200 MT/s	260	Single

NOTE: Full availability of 4 GB or more of memory requires a 64-bit operating system. With Windows 32-bit operating systems, the amount of usable memory is dependent upon your configuration, so that above 3 GB all memory may not be available due to system resource requirements.

Technical Specifications

***NOTE:** All models may not be available in all regions.

****NOTE:** Memory modules support data transfer rates up to 2133 MT/s; actual data rate is determined by the system's configured processor. See processor specifications for supported memory data rate.

*****NOTE:** Memory modules support data transfer rates up to 2400 MT/s; actual data rate is determined by the system's configured processor. See processor specifications for supported memory data rate.

Dimensions

DDR4 Memory UDIMMs	Dimensions (H x W x D)	30.75 x 133.35 x 3.98 mm (1.2 x 5.25 x .15 in)
DDR4 Memory SoDIMMs	Dimensions (H x W x D)	30 x 69.6 x 3.98 mm (1.18 x 2.74 x .15 in)

Operating Systems supported

Windows 10*

***NOTE:** Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>

Change log

© Copyright 2020 HP Development Company, L.P. All rights reserved.

The information contained herein is subject to change without notice. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries

Change Log

February 05 2016 / From v2 to v3

Changed 4GB SoDIMM P1N52AA to P1N53AA/AT

Changed 8GB SoDIMM P1N52AT to P1N54AA/AT

February 05 2016 / From v3 to v4

Added DDR4-2400 SoDIMMs and DDR4-2400 SoDIMMs

November 13, 2017/ From v4 to v5

Changed DDR4-2400 SoDIMMs Compatibility updated

Added 2666 Memory DIMM and SoDIMM Cards

August 1, 2018/ From v6 to v7

Added DDR4-2666Mhz Memory Cards added

July 20, 2020/ From v7 to v8

Addition HP 32GB DDR4-2666 UDIMM, HP 32GB DDR4-2666 SoDIMM and general update.

July 21, 2020/ From v8 to v9

Addition DDR4-3200 Memory UDIMMs and DDR4-3200 Memory SoDIMMs

August 5, 2020/ From v9 to v10

Removal DDR4-2666Mhz Memory Cards