

## OVERVIEW



1. Control Buttons	4. HDMI 1.4
2. Kensington Security Slot	5. VGA
3. AC Power-in	6. Audio-out (3.5mm)

## PERFORMANCE

### Panel

#### Panel

3-side NearEdgeless, In-Plane Switching

#### Backlight

WLED

#### Display Size

21.5 inches

#### Max View Area

WxH: 476.1 x 267.8 mm

#### Resolution

1920 x 1080

#### Aspect Ratio

16:9

#### Pixel Pitch

0.248 x 0.248 mm

#### Dot / Pixel Per Inch

102 dpi

#### Brightness

250 cd/m<sup>2</sup>

#### Contrast Ratio

- Dynamic Contrast Ratio: 3000000:1
- Contrast Ratio: 1000:1

#### View Angle (H / V)

Horizontal: 178°, Vertical: 178°

#### Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

#### Refresh Rate

75Hz

#### Color Gamut

99% sRGB

#### Color Support

16.7 Million

#### Color Depth

8-bit (6-bit+FRC)

#### Screen Surface Treatment

Anti-glare

### Operating System

#### Operating System

- Windows® 11 Support
- Windows® 10 Support

### Power Supply

#### Power Consumption

- Typical / Max: 15.1W / 21W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 13.1W
- Energy Star TEC: 42.6kWh
- Internal Power Supply

**Voltage Required**

AC 100 to 240 V (50-60Hz)

**Special Features****Special Features**

Natural Low Blue Light

**DESIGN****Mechanical****ThinkCentre® M Series Support**

ThinkCentre® M Series Tiny Support

For supporting Tiny devices, additional VESA Mount II (PN 4XFON03161) and sandwich mounting kit (PN: 4XHON04098) are needed (sold separately). Additional flexible arm/stand are required to support sandwich mounting kit installation.

**Bezel Width**

- Thickness of Head: 6.9mm (Minimum)
- Side: 1.5 mm
- Top / Bottom: 1.5mm / 22mm

**Buttons**

- Menu joystick
- Power button
- Source Key

**Cable Management**

Support

**Case Color**

Raven Black / Storm Grey

**Dimensions (WxDxH)<sup>[1]</sup>**

Models	Dimensions
Lowest Position	488 x 182.9 x 408.6 mm (19.21 x 7.2 x 16.09 inches)
Highest Position	488 x 182.9 x 408.6 mm (19.21 x 7.2 x 16.09 inches)
Head Only	488 x 41 x 297.3 mm (19.21 x 1.61 x 11.70 inches)

**Packaging Dimensions (WxDxH)**

580 x 115 x 355 mm (22.83 x 4.53 x 13.98 inches)

**Weight<sup>[2]</sup>**

Models	Weight
Monitor With Stand	3.1 kg (6.8 lbs)
Monitor Head Only	2.3 kg (5.1 lbs)

**Packaging Weight**

4.6 kg (10.1 lbs)

**Mounting**

Supports VESA mount 100 x 100 mm

**Stand**

Supports -5° to +22° tilt

**In the Box**

- Monitor with Stand
- 1x Screw
- Quick Setup Guide
- 1x HDMI® Cable (1.8m)
- 1x Power Cable

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

## CONNECTIVITY

### Ports<sup>[1]</sup>

#### Rear Ports

- 1x HDMI® 1.4
- 1x VGA
- 1x audio-out (3.5mm)

#### Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

## SECURITY & PRIVACY

### Security

#### Physical Locks

Kensington® Security Slot™ (2.5 mm x 6 mm)

## SERVICE

### Warranty

#### Base Warranty

3-year limited warranty

## CERTIFICATIONS

### Green Certifications<sup>[1]</sup>

#### Green Certifications

- ENERGY STAR® Certified
- EPEAT™ Gold Registered
- EU Energy Label (E-class)
- TCO Certified 9.0
- TCO edge 2.0

#### Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

### Other Certifications

#### Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Eye Comfort Certification 2.0
- TÜV Rheinland® Low Blue Light
- TÜV Rheinland® Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

