

Info

- Product
 - Outdoor
- Year
 - Y24
- Month
 - M08

Panel

- Screen Size (Inch)
 - 49"
- Panel Technology
 - IPS, M+
- Back Light Type
 - Direct
- Aspect Ratio
 - 16:9
- Native Resolution
 - 1920x1080 (FHD)
- Refresh Rate
 - 60Hz
- Brightness
 - 3,500 nit (Typ), 2,800 nit(Min)
- Contrast Ratio
 - 1,300:1
- Dynamic CR
 - 500,000:1
- Color gamut
 - 67%
- Viewing Angle (H x V)
 - 178 x 178
- Color Depth (Number of Colors)
 - 10bit, 1.07Billion colors
- Response Time
 - Typ. 8ms (G to G BW)
- Surface Treatment (Haze)
 - 3%
- Life time
 - 50,000 Hrs (Typ)
- Operation Hours (Hours/Day)
 - 24/7
- Portrait / Landscape
 - Yes / Yes
- QWP (Quarter Wave Plate)
 - Yes

Connectivity(Jack Interface)

- HDMI IN
 - Yes(2), HDCP2.2
- DP IN
 - Yes(1), HDCP2.2
- RS232C IN
 - Yes(1) (4pin phone jack)
- RJ45(LAN) IN
 - Yes(2) (Lan (1), HDbaseT(1))
- USB IN
 - USB2.0 Type A (2)
- External Speaker Out
 - Yes(1, L/R, 10W+10W)
- RS232C Out
 - Yes(1)
- RJ45(LAN) Out
 - Yes(1)

Mechanical

- Bezel Color
 - Black
- Bezel Width
 - 38.4/26/26/38.4mm
- Weight (Head)
 - 31.2kg
- Packed Weight
 - 36.2kg
- Monitor Dimensions (W x H x D)
 - 1153.0 x 656.2 x 88.0mm
- Carton Dimensions (W x H x D)
 - 1287 x 797 x 207mm

Protection Glass

- Thickness
 - 5mm
- Degree of Protection
 - Yes (IK10)
- Tempered / Chemical strengthening
 - Tempered
- Anti-Reflective
 - Yes
- Infrared - Resistance (IR)
 - Yes
- Shatter-Proof
 - Yes

HW Feature

- Internal Memory (eMMC)
 - 16GB
- Wi-Fi/BT (Built-in)
 - Yes
- Temperature Sensor
 - Yes
- IR Temperature Sensor
 - Yes
- Auto Brightness sensor
 - Yes
- Pixel sensor
 - Yes
- Current Sensor
 - Yes
- BLU Sensor
 - Yes
- Humidity Sensor
 - Yes
- Acceleration(Gyro) Sensor
 - Yes
- Power Indicator
 - Yes
- FAN (Built-in)
 - Yes

SW Feature

- OS Ver. (webOS)
 - webOS6.1
- Local Contents Scheduling
 - Yes
- Group Manager
 - Yes
- USB Plug & Play
 - Yes
- Fail over
 - Yes
- Bootling Logo Image
 - Yes
- No Signal Image
 - Yes
- RS232C Sync
 - Yes
- Local Network Sync
 - Yes
- Backlight Sync
 - Yes
- PIP
 - Yes
- PBP
 - Yes(2)
- Video Tag
 - Yes(4)
- Play via URL
 - Yes
- Screen Rotation
 - Yes
- External Input Rotation
 - Yes
- Gapless Playback
 - Yes
- Tile Mode Setting
 - Yes (Max. 15x15)
- Setting Data Cloning
 - Yes
- SNMP
 - Yes
- ISM Method
 - Yes
- Auto Set ID
 - Yes
- Status Mailing
 - Yes
- Control Manager
 - Yes
- Smart Energy Saving
 - Yes
- PM mode
 - Yes
- Wake on LAN
 - Yes (LAN in / HDbaseT port)
- Network Ready
 - Yes
- Beacon
 - Yes
- HDMLI-CEC
 - Yes
- SI Server Setting
 - Yes
- webRTC
 - Yes
- Pro:Idiom
 - Yes

Environment Conditions

- Operation Temperature
 - 30°C to 50 °C
- Operation Humidity
 - 5% to 100%

Power

- ### Power Consumption

Power Consumption

- ### Certification

- ### Software Compatibility

- Language

- ### Accessory

- Special Feature

- ### Product Dedicated Feature