


OVERVIEW



1. USB-C (USB 10Gbps)	9. Ethernet (RJ-45)
2. USB-C (Thunderbolt 4)	10. Kensington Security Slot
3. HDMI-in 1.4	11. Ethernet (15W POE, for touch controller)
4. HDMI-out 2.1 TMDS	12. Ethernet (15W POE, for camera)
5. HDMI-out 2.1 TMDS	13. Ethernet (15W POE)
6. USB-C (USB 10Gbps)	14. Ethernet (100W POE, for smart audio bar)
7. USB-A (USB 10Gbps), for remote in small room	15. DC-in (AC adapter input)
8. USB-A (USB 10Gbps)	

PERFORMANCE

Compute Unit

Compute Unit

Features	Information
Processor	Intel® Core™ i5-1335U, 10C (2P + 8E) / 12T, P-core 1.3 / 4.6GHz, E-core 0.9 / 3.4GHz, 12MB Cache
Operating System	ChromeOS
Graphics	Integrated Intel® Iris® Xe Graphics. Max Resolution: 4096x2304@60Hz(HDMI®), 4096x2304@60Hz(USB-C®), 4096x2304@60Hz(Thunderbolt™)
Chipset	Intel® SoC (System on Chip) platform
Memory	Up to 32GB DDR5-5600
Storage	One drive, 256GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal
Audio Chip	High Definition (HD) Audio, Realtek® ALC5682I codec
Power Supply	240W adapter, 100V - 240V
Ethernet	Gigabit ethernet, Realtek® RTL8111G (1x RJ-45, uplink) and Intel® Ethernet Controller I350 (4x RJ-45, downlink)
WLAN + Bluetooth®	Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.2, M.2 Card
Case Color	Charcoal
Rear Ports	• 1x USB-C® (USB 10Gbps / 3.2 Gen 2), with data transfer and DisplayPort™ • 1x USB-C® (Thunderbolt™ 4), with data transfer and DisplayPort™ • 1x USB-C® (USB 10Gbps / 3.2 Gen 2), data transfer only • 2x HDMI®-out 2.1 TMDS with CEC • 2x USB-A (USB 10Gbps / USB 3.2 Gen 2) • 1x HDMI®-in 1.4b • 1x power connector • 5x RJ-45 Ethernet (one uplink port for internet connection, four downlink ports for IP-based peripherals)
Dimension (WxDxH)	284 x 135 x 29 mm (11.18 x 5.31 x 1.14 inches)
Weight	985 g (2.17 lbs)

DESIGN

Mechanical

Component Options**

Product	Compute System	Controller	Audio Bar	Microphone Component	Camera Component
Large Room Kit	1x Compute Unit	1x Touch Controller	1x Smart Audio Bar + 1x Add-on Audio Bar	2x Mic Pod	1x Smart Camera XL
Medium Room Prime Kit	1x Compute Unit	1x Touch Controller	1x Smart Audio Bar	1x Mic Pod	1x Smart Camera XL
Medium Room Kit	1x Compute Unit	1x Touch Controller	1x Smart Audio Bar	1x Mic Pod	1x Smart Camera
Medium Room Lite Kit	1x Compute Unit	1x Touch Controller	1x Smart Audio Bar	-	1x Smart Camera
Small Room Kit	1x Compute Unit	1x Remote Controller	1x Smart Audio Bar	-	1x Smart Camera
Compute Unit Only	1x Compute Unit	-	-	-	-

Controller

Touch Controller

Features	Information
Display	• 10.1" Display, 1280x800(HD)x3(RGB) LCD, 16:9 aspect ratio • multi-touch touch • Anti-glare, Anti Smudge
Sensors	• Color sensor • Orientation sensor
Ports	1x RJ45 Ethernet (PoE, connect to Compute System)
Dimension	245 x 164 x 91 mm (9.65 x 6.46 x 3.58 inches)
Weight	990 g (2.18 lbs)

Remote Control

Features	Information
Keypad	• 10 function keys on front (Navi keys, Microphone on/off, Menu, End, Volume up/down keys) • QWERTY keyboard on rear (38 keys)
Connections	2.4 RF remote
Power supply	Embedded rechargeable lithium ion battery with USB-powered charging dock
Dimension	45 x 130 x 14 mm (1.77 x 5.12 x 0.55 inches)
Weight	65 g (0.14 lbs)

Audio Bar

Smart Audio Bar

Features	Information
Speakers	• 2.5 inch neodymium woofer, 1 inch neodymium tweeter • 2x passive radiators • 20W RMS power, 80Hz-24kHz frequency response
Microphone	• 8 element, linear beamforming array • 100Hz-24kHz pickup, optimal pickup range of up to 4m
Ports	• 1x USB-C® with USB 2.0 UAC (only for audio out) • 1x stereo analog RCA output (for assistive listening devices) • 1x RJ-45 Ethernet (PoE, connect to Compute System) • 2x RJ-45 Daisy Chain Ports (PoE like, connect to Add-on Audio Bar and Mic Pod)
Dimension	705 x 95 x 133 mm (27.76 x 3.74 x 5.24 inches)
Weight	3.3 kg (7.28 lbs)

Add-on Audio Bar

Features	Information
Speakers	• 2.5 inch neodymium woofer, 1 inch neodymium tweeter • 2x passive radiators • 20W RMS power, 80Hz-24kHz frequency response
Microphone	• 8 element, linear beamforming array • 100Hz-24kHz pickup, optimal pickup range of up to 4m
Ports	1x RJ-45 Daisy Chain Port (PoE like, connect to Smart Audio Bar)
Dimension	705 x 95 x 133 mm (27.76 x 3.74 x 5.24 inches)
Weight	2.8 kg (6.17 lbs)

Microphone

Mic Pod

Features	Information
----------	-------------

Capturing Range	• 100Hz-24kHz pickup • Optimal pickup range of up to 2m
Key Features	8 element, circular beamforming array
Ports	2x RJ-45 Daisy Chain ports (PoE like, one input connects to Smart Audio Bar or previous Mic Pod, one output port connects to next Mic Pod)
Dimension	95 x 95 x 30 mm (3.74 x 3.74 x 1.18 inches)
Weight	215 g (0.47 lbs)

Camera

Smart Camera

Features	Information
Image	• Up to 1080p@30fps video capture, f/2.8 aperture • 12 MP 1/2.3" CMOS sensor • 16:9 aspect ratio output
Optics	• Ultra-wide angle glass optics • 120° horizontal field of view • 90° vertical field of view
Microphone	Omnidirectional microphone
Mounting	Wall mount kit, TV mount kit, Magnetic dock
Ports	1x RJ-45 Ethernet (PoE, connect to Compute System)
Dimension	107 x 84 x 42 mm (4.21 x 3.3 x 1.65 inches)
Weight	321 g (0.71)

Smart Camera XL

Features	Information
Image	• Up to 1080p@30fps video capture, f/2.9 aperture • 20.30 MP 1" CMOS sensor • 16:9 aspect ratio output
Optics	• Wide angle glass optics • 90° - 95° horizontal field of view • 90° vertical field of view
Microphone	Omnidirectional microphone
Mounting	Wall mount kit, TV mount kit, Magnetic dock
Ports	1x RJ-45 Ethernet (PoE, connect to Compute System)
Dimension	122 x 84 x 52 mm (4.8 x 3.3 x 2.04 inches)
Weight	480 g (1.06 lbs)

SERVICE

Warranty^[1]

Base Warranty

3-year premier support service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

SOFTWARE

Preinstalled Software

Preinstalled Software

Google Meet

- This is a telepresence technology product.
- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

