



Display						
Active Screen Size	43"	55"	65"	75"	85"	98"
Backlight	LCD	LCD	LCD	LCD	LCD	LCD
Display Area	37.1 x 20.8 in	47.6 x 26.8 in	56.2 x 31.6 in	64.9 x 36.5 in	73.7 x 41.5 in	84.9 x 47.8 in
Display Ratio	16:9	16:9	16:9	16:9	16:9	16:9
Resolution	3840 x 2160 (4K)	3840 x 2160 (4K)	3840 x 2160 (4K)	3840 x 2160 (4K)	3840 x 2160 (4K)	3840 x 2160 (4K)
Pixel Pitch (mm)	0.0817 [H] x 0.2451 [V]	0.105 [H] x 0.315 [V]	0.124 [H] x 0.372 [V]	0.14325 [H] x 0.42975 [V]	0.1625 [H] x 0.4875 [V]	0.1874 [H] x 0.5622 [V]
Refreshing Frequency	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz
Display Colors	1.07 Billion	1.07 Billion	1.07 Billion	1.07 Billion	1.07 Billion	1.07 Billion
Color Depth	8bit+FRC	8bit+FRC	8bit+FRC	8bit+FRC	8bit+FRC	8bit+FRC
Brightness	260 nits	260 nits	270 nits	300 nits	350 nits	450 nits
Haze	2%	2%	2%	2%	2%	2%
Contrast Ratio (Dynamic)	4000:1	4000:1	4000:1	4000:1	5000:1	4000:1
Response Time	6.5 ms	6.5 ms	6.5 ms	6.5 ms	6.5 ms	6.5 ms
Viewing Angle	178°	178°	178°	178°	178°	178°
Operation Time	24/7	24/7	24/7	24/7	24/7	24/7
Display Orientation	Landscape	Landscape	Landscape	Landscape	Landscape	Landscape
Glass Surface	Anti-Glare	Anti-Glare	Anti-Glare	Anti-Glare	Anti-Glare	Anti-Glare
Power						
Working Voltage	AC100-240 V~ 50/60 Hz	AC100-240 V~ 50/60 Hz	AC100-240 V~ 50/60 Hz	AC100-240 V~ 50/60 Hz	AC100-240 V~ 50/60 Hz	AC100-240 V~ 50/60 Hz
Power Consumption (normal)	<=80W	<=140W	<=150W	<=190W	<=250W	<=410W
Power Consumption (full load)	<=95W	<=140W	<=160W	<=250W	<=275W	<=435W
Power Consumption (Standby mode)	<=0.5W	<=0.5W	<=0.5W	<=0.5W	<=0.5W	<=0.5W
Power Consumption (Wake-on-LAN or Wake-on-WiFi)	<2W	<2W	<2W	<2W	<2W	<2W
Speakers						
Speaker Position	Back Bottom	Back Bottom	Back Bottom	Back Bottom	Back Bottom	Back Bottom
Max Power Output	2 x 10 W	2 x 10 W	2 x 10 W	2 x 10 W	2 x 15 W	2 x 15 W
Transportation/Storage						
Storage Temperature/Humidity	20~60°C 0~85%RH (non-condensing)	20~60°C 0~85%RH (non-condensing)	20~60°C 0~85%RH (non-condensing)	20~60°C 0~85%RH (non-condensing)	20~60°C 0~85%RH (non-condensing)	20~60°C 0~85%RH (non-condensing)
Working Temperature/Humidity	0~40°C 20~80%RH (non-condensing)	0~40°C 20~80%RH (non-condensing)	0~40°C 20~80%RH (non-condensing)	0~40°C 20~80%RH (non-condensing)	0~40°C 20~80%RH (non-condensing)	0~40°C 20~80%RH (non-condensing)
Installation Method (optional)	Wall-mounted / Mobile stand	Wall-mounted / Mobile stand	Wall-mounted / Mobile stand	Wall-mounted / Mobile stand	Wall-mounted / Mobile stand	Wall-mounted / Mobile stand
Bezel Width (Top, Left, Right)	1.2 / 1.2 / 1.2 mm	1.4 / 1.4 / 1.4 mm	1.8 / 1.8 / 1.8 mm	1.8 / 1.8 / 1.8 mm	1.8 / 1.8 / 1.8 mm	3.5 / 3.5 / 3.5 mm
Bottom Bezel Width Including IR Receiver	19.3 mm	22.6 mm	20.4 mm	20.3 mm	17.8 mm	30.2 mm
Bottom Bezel Width (without wall mount bracket thickness)	16.3 mm	19.4 mm	17.1 mm	17.1 mm	14.5 mm	19.4 mm
Outline Dimension	37.67 x 22 x 3.4 in	48.27 x 27.91 x 3.45 in	57.71 x 32.71 x 3.35 in	65.67 x 37.64 x 3.47 in	74.4 x 42.56 x 3.59 in	85.9 x 49.4 x 4.37 in
Packing Dimension	42.32 x 25.66 x 5.59 in	53.14 x 32.95 x 5.66 in	62.99 x 37.79 x 6.45 in	72.44 x 43.42 x 7.48 in	79.92 x 49.21 x 7.55 in	94.09 x 59.05 x 11.02 in
Wall-hanging Screw	M6 x 10 mm	M6 x 12 mm	M6 x 12 mm	M6 x 12 mm	M8 x 16 mm	M8 x 16 mm
VESA Mount Pattern	300 x 300 mm	300 x 300 mm	400 x 300 mm	400 x 300 mm	500 x 400 mm	800 x 200 x 200 mm
Net Weight	13.89 lbs	24.94 lbs	36.60 lbs	50.07 lbs	65.04 lbs	163.14 lbs
Gross Weight	19.84 lbs	34.52 lbs	51.85 lbs	75.57 lbs	93.50 lbs	231.49 lbs
Embedded Operating System						
Android Version	Android 14	Android 14	Android 14	Android 14	Android 14	Android 14
CPU	ARM Cortex A73 x 4	ARM Cortex A73 x 4	ARM Cortex A73 x 4	ARM Cortex A73 x 4	ARM Cortex A73 x 4	ARM Cortex A73 x 4
GPU	ARM Mali-G52 MC1	ARM Mali-G52 MC1	ARM Mali-G52 MC1	ARM Mali-G52 MC1	ARM Mali-G52 MC1	ARM Mali-G52 MC1
RAM	4 GB	4 GB	4 GB	4 GB	4 GB	4 GB
ROM	16 GB	16 GB	16 GB	16 GB	16 GB	16 GB
Wi-Fi / Bluetooth	Wi-Fi 5, BT5.0	Wi-Fi 5, BT5.0	Wi-Fi 5, BT5.0	Wi-Fi 5, BT5.0	Wi-Fi 5, BT5.0	Wi-Fi 5, BT5.0
Wake On LAN	Yes	Yes	Yes	Yes	Yes	Yes
Wake On WiFi	Yes	Yes	Yes	Yes	Yes	Yes
IP Control	Yes	Yes	Yes	Yes	Yes	Yes
I/O Ports						
Rear Input Port	(3) HDMI In 2.0; (1) USB-A 2.0; (1) USB-A 3.0; (1) LAN In (RJ45); (1) AV In; (1) RS-232					
Rear Output Port	(1) S/PDIF Out; (1) Audio Output (Jack 3.5 mm)					
Accessories						
Power Cord By Region	9.8 ft					
Remote Control	1 (with AAA Battery 2 set)					