The Most Secure Network Scanners in the World[3]





	HP ScanJet Enterprise Flow N9000 sn1 Scanner	HP ScanJet Enterprise Flow N9120 fn2[7]
Part number	8Q4W1A	L2763A
Color and black-and-white speed	80 ppm/160 ipm @300dpi	Up to 120 ppm/240 ipm @200 ppi
HP EveryPage (ultrasonic sensor)[1]	Yes	Yes
ADF capacity (sheets)	100	200
Recommended daily duty cycle	30,000	20,000
Scanning options (ADF)	Single-pass, double-sided	Single-pass, double-sided
Max resolution (ppi)	600 x 600 dpi; Optical: Up to 600 dpi	1200
Scans embossed ID cards	Not applicable	On flatbed
Control panel	Resistive 10.9 cm (4.3 in) touch panel with four buttons: Sleep/Power, Home, Back, Help	8.0 inch color touchscreen with configurable scan profiles
Mac support	Yes	Yes
Software included	HP Scan Premium Software	HP Scan Premium Software
Kofax VRS	Certified	Pro 5.1
Scanning destinations	Email, network folder, USB Flash, LAN/Internet fax, Microsoft® SharePoint®	Email, network folder, USB Flash, LAN/Internet fax, Microsoft® SharePoint®
Scanning features	Auto Document Classification; Manual Reduction; Multi Zonal OCR; Scan to Multi Destination; Auto Orientation; Blank Page Removal; Barcode Detection; Digitial Stamp; Batch Seperation; HP EveryPage Technology; Scan to USB	Auto exposure, Auto threshold, Auto detect color, Background smooth/removal, Auto detect size, Straighten content, Enhance content, Multi-streaming, Auto feed, Multi-feed detection sensor, Auto orient, Multi-color dropout, Channel color dropout, Edge erase, Resize page, Delete blank page, Merge pages, Hole fill, PDF permissions, Document separation (Blank page, Barcode, Zonal barcode, Zonal OCR)
Flatbed size (inches W x L)	N/A	11.7 x 17 in
ADF paper size (inches W x L)	2.67 x 5.8 to 11.7 x 34.0	2.7 x 5.8 to 8.5 x 34.0
Media weights (lb)	7.5 to 112.5	12 to 53
Connectivity, standard	1 SuperSpeed USB 3.0; 1 Gigabit Ethernet 10/100/1000 Base-T network	10/100/1000 Ethernet; Hi-Speed USB Host (1 rear/ 1 walk-up); Hardware Integration Pocket (HIP) Hi-Speed USB, USB-Device Port (Rear)
Drivers	HP Scanner Device Driver(Includes HP WIA scan driver, HP TWAIN scan driver), ISIS drive	TWAIN (Network and USB)/ISIS/WIA/SANE
OS support	Windows 11, Windows 10, Windows 8.1, Windows Server, macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; macOS Sequoia; Linux	Windows 11; Windows 10; Windows 8; Windows 8.1; Windows 7; macOS X 10.10 Yosemite; macOS 10.11 El Capitan; macOS 10.12 Sierra; Linux; UNIX
Dimensions (inches W x D x H)	15.3 x 26 x 15.2	23.7 x 29.7 x 24.5
Weight (lb)	10.8 ib	47.2 lb
HP Web Jetadmin[2] manageable	Yes	Yes
Long-life consumables		
Roller replacement kit	9Y0J0A (~200K pages)	J8J95A (~150K pages)
HP Care Pack Services[4]		
Standard warranty	1 year	1 year
3-year next business day with DMR	UF8E0E	U9TX1E
4-year next business day with DMR	UF8E1E	U9TX2E
5-year next business day with DMR	UF8E2E	U9TX3E

[1]The ultrasonic sensor allows the definition of page areas to be excluded from multipage. [2]HP Web Jetadmin is available for download at no additional charge at hp.com/go/wja. [3]HP's most advanced embedded security features are available on HP Enterprise and HP Managed devices with HP FutureSmart firmware 4.5 or above. Claim based on HP review of 2019 published features of competitive in-class printers. Only HP offers a combination of security features to automatically detect, stop, and recover from attacks with a self-healing reboot, in alignment with NIST SP 800-193 guidelines for device cyber resiliency. For a list of compatible products, visit hp.com/go/PrintersThatProtect. For more information, visit hp.com/go/printersecurityclaims. [4]To view entire list of HP Care Pack Services, visit hp.com/go/cpc. O=Onsite, X=Exchange. [5]Standard and available features vary by product. [6]Destination PC must have driver and software installed and must be on the same network as the scanner. [7]The HP ScanJet Enterprise Flow N9120 fn2 Sheet-feed Scanner earned a Highly Recommended rating from Buyers Lab in 2019. [8]May require downloading an updated form hp.com/support. [9]File types for OS X: TIFF, PNG, JPEG, JPEG-2000, PDF, searchable PDF, RTF, TXT. [10]Wireless performance is dependent on physical environment and distance from access point and may be limited during active VPN connections. Wi-Fi Direct scanning requires the mobile device be connected directly to the Wi-Fi network of the scanner.[11]Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT® standard for imaging equipment, IEEE 1680.2.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. All trademarks are property of their respective owners.

Google Drive is a trademark of Google, Inc. Microsoft and SharePoint are U.S. registered trademarks of the Microsoft group of companies.

4AA5-5899ENW, May 2025

Fast scanning with superb results

Keep business moving

Handle large volumes at impressive speeds using the automatic document feeder (ADF).

Optimize workflows with 3rd party apps integration

Scan images directly into popular applications, with full-featured TWAIN and ISIS drivers.

Share or archive scans directly to email, network folders, a PC,[6] or Microsoft SharePoint, as well as cloud destinations like Dropbox and Google Drive™.[5]



Superb paper-handling

With up to 1200 dpi resolution, you'll ensure high image quality for all your scans. Capture a wide range of document sizes and types with HP EveryPage and an ultrasonic sensor.[5]

Automated workflows

Digitize, classify, and save efficiently a wide range of documents with HP Scan (Premium) software.

Designed to conserve

Support your business' environmental initiatives with a scanner designed to use energy efficiently and made with up to 30% recycled plastic.[11]

Safeguard your scans from malware Supporting

HP Secure Boot and firmware code-signing validation help keep every startup and update safe from malware.



Flatbed with automatic document feeder (ADF)

Sheet-fed

	HP Digital Sender Flow 8500 fn2 Document Capture Workstation	HP ScanJet Enterprise N6600 fnw1	HP ScanJet Pro N4600 fnw1	HP ScanJet Pro 3600 f1	HP ScanJet Pro 2600 f1	HP ScanJet Enterprise Flow 9000 s1 Scanner	HP ScanJet Enterprise Flow N7000 snw1	HP ScanJet Enterprise Flow 7000 s3	HP ScanJet Enterprise Flow 5000 s5	HP ScanJet Pro 4200 s1 Scanner	HP ScanJet Pro N4000 snw1	HP ScanJet Pro 3000 s4	HP ScanJet Pro 2000 s2
Part number	L2762A	L2725B	L2749A	L2741A	L2747A	8Q4W0A	6FW10A	L2757A	6FW09A	8Q4W2A	6FW08A	6FW07A	6FW06A
Color and black-and-white speed (ppm/ipm)	100/200 @200 ppi	50/100 @300 ppi	40/80 @300 ppi	30/60 @300 ppi	25/50 @300 ppi	80/160 ipm @300 ppi	75/150 @300 ppi	75/150 @300 ppi	65/130 @300 ppi	40/80 @300 ppi	40/80 @300 ppi	40/80 @300 ppi	35/70 @300 ppi
HP EveryPage (ultrasonic sensor)[1]	Yes	Yes	Yes	Yes	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	No
ADF capacity (sheets)	150	100	100	60	60	100	80	80	80	50	50	50	50
Recommended daily duty cycle	10,000	8,000	6,000	3,000	1,500	30,000	7,500	7,500	7,500	4,500	4,000	4,000	3,500
Scanning options (ADF)	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided	Single-pass, double-sided
Max resolution (ppi)	1200	600	1200	1200	1200	1200	1200	1200	1200	1200	1200	1200	1200
Scans embossed ID cards	On flatbed	On flatbed	On flatbed	On flatbed	On flatbed	Through the ADF	Through the ADF	Through ADF	Through the ADF	Through the ADF	Through the ADF	Through the ADF	Through the ADF
Scanning from front panel	8.0 inch color touchscreen with configurable scan profiles	Menu system for execution of up to 30 scan profiles	2.8 inch touch panel with 4 preconfigured destinations	Menu system for execution of up to 7 scan profiles	4 configurable buttons	2-line 16 character per line LCD display, Simplex button, Duplex button, Cancel button, Power button with a LED and Tool button	4.3 inch touch panel with 6 preconfigured destinations	Menu system for execution of up to 10 scan profiles	Menu system for execution of up to 10 scan profiles	1 light (Error); 3 button (Pwer, Scan, Cancel)	2.8 inch touch panel with 6 preconfigured destinations	Scan button	Scan button
Drivers	TWAIN (Network and USB)/ ISIS/WIA/SANE	TWAIN/ISIS/WIA/SANE	TWAIN (Network and USB)/ ISIS/WIA/SANE	TWAIN/WIA/SANE	TWAIN/WIA/SANE	HP Scanner Device Driver(Includes HP WIA scan driver, HP TWAIN scan driver), ISIS drive	TWAIN (Network and USB)/ ISIS/WIA/SANE	TWAIN/ISIS/WIA/SANE	TWAIN/ISIS/WIA/SANE	TWAIN (Network and USB)/ ISIS/WIA/SANE	TWAIN (Network and USB)/ ISIS/WIA/SANE	TWAIN/ISIS/WIA/SANE	TWAIN/ISIS/WIA/SANE
HP Web Jetadmin[2]	Yes	Yes	Yes	No	No	Yes	Yes	No	No	No	Yes	No	No
Flatbed size (inches W x L)	8.5 x 14	8.5 x 14	8.5 x 14	8.5 x 11.7	8.5 x 11.7	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
ADF paper size – min to max (inches W x L)	2.7 x 5.8 to 8.5 x 34.0	2.67 x 5.8 to 8.5 x 34.0	4.1 x 5.8 to 8.5 x 122.0	4.1 x 5.8 to 8.5 x 122.0	4.1 x 5.8 to 8.5 x 122.0	11.7 x 23.0 to 2.0 x 2.7	2.0 x 2.9 to 8.5 x 122	2 x 2 to 8.5 x 122	2.0 x 2.9 to 8.5 x 122	2.0 x 2.9 to 8.5 x 122	2.0 x 2.9 to 8.5 x 122	2.0 x 2.9 to 8.5 x 122	2.0 x 2.9 to 8.5 x 122
Media weights (lb)	12 to 53	13 to 32	12 to 32	16 to 28	16 to 28	7.5 to 112.5	11.4 to 93.3	10.7 to 110	11.4 to 93.3	7.5 to 115	10.7 to 56	10.7 to 56	10.7 to 56
Connectivity, standard	1 SuperSpeed USB 3.0; 1 Gigabit Ethernet 10/100/1000 Base-T network	USB 2.0	USB 3.0	USB 3.0	USB 2.0	1 SuperSpeed USB 3.0	USB 3.0	USB 3.0	USB 3.0	1 SperSpeed USB 3.0	USB 3.0	USB 3.0	USB 3.0
Networked	Ethernet	Ethernet, Wi-Fi, Wi-Fi Direct[#10]	Ethernet, Wi-Fi, Wi-Fi Direct[#10]	N/A	N/A	N/A	Ethernet, Wi-Fi, Wi-Fi Direct[10]	N/A	N/A	N/A	Ethernet, Wi-Fi, Wi-Fi Direct[10]	N/A	N/A
Digital sending	Scan to PC; Scan to USB Drive; Scan to Email; Scan to Network Folder; Scan to SharePoint; Scan to Shortcut; Scan to Cloud	N/A	Scan to computer, email, folder, FTP	N/A	N/A	Scan to PC; Scan to USB Drive; Scan to Email; Scan to Network Folder; Scan to SharePoint; Scan to Shortcut; Scan to Cloud	Scan to computer, email, folder, FTP, SharePoint, USB drive	N/A	Scan to USB drive	Scan to USB drive	Scan to computer, email, folder, FTP, SharePoint, USB drive	Scan to USB drive	N/A
Dimensions (inches W x D x H)	20.2 x 23.0 x 10.4	20.4 x 17.2 x 8.0	20.5 x 15.2 x 5.7	18.1 x 15.2 x 5.7	17.8 x 13.8 x 4.8	15.3 x 26 x 15.2	12.20 x 7.79 x 7.48	12.20 x 7.79 x 7.48	12.20 x 7.79 x 7.48	12 x 11.3 x 10.7	11.8 x 6.8 x 6.1	11.8 x 6.8 x 6.1	11.8 x 6.8 x 6.1
Weight (lb)	38.5	23.37	13.2	12.3	9.5	10.8	8.8	8.4	8.4	4,4	6.2	6.0	6.0
Software													
Kofax VRS	Pro 5.1	Certified	Certified	No	No	Certified	Certified	Pro 5.1	Certified	Certified	Certified	Certified	Certified
HP software (with OCR)	HP Scan Premium Software	HP Scan Premium Software	HP Scan Software	HP Scan Software	HP Scan Software	HP Scan Premium Software	HP Scan Premium Software	HP Scan Premium Software	HP Scan Premium Software	HP Scan Software	HP Scan Software	HP Scan Software	HP Scan Software
Destinations[8]	Local/network folder, email, FTP, SharePoint, Google Drive, Dropbox					Local/network folder, email, FTP, printer, SharePoint and OneDrive, Google Drive, Office 365, Dropbox, and other destinations							
HP Scan and HP TWAIN features	Auto black and white threshold, auto color detect, auto crop, auto exposure, auto orientation, blank page removal, black and white enhanced content, clean up background, color drop out, erase edges, hole removal, merge pages, multiple destinations, OCR, remove background, straighten content					Auto black and white threshold, auto color detect, auto crop, auto exposure, auto feed, auto orientation, blank page removal, zonal barcode processing, zonal OCR, black and white enhanced content, clean up background, color drop out, document separation, erase edges, hole removal, merge pages, multiple destinations, OCR, remove background, straighten content, multi-streaming, split image							
Additional HP Scan and HP TWAIN features	N/A	Misfeed detection; Automatic multiple destinations; custom destination	Misfeed detection	Misfeed detection	N/A	Advanced misfeed detection; Automatic multiple destinations; custom destination	Advanced misfeed detection; Automatic multiple destinations; custom destination	Advanced misfeed detection; Automatic multiple destinations; custom destination	Advanced misfeed detection; Automatic multiple destinations; custom destination	Advanced misfeed detection; Automatic multiple destinations; custom destination	Advanced misfeed detection	Advanced misfeed detection	N/A
Mac support	Yes	Yes	Yes[9]	Yes[9]	Yes[9]	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Long-life consumables													
Roller replacement kit	J8J95A (~150K pages)	L2718A	L2742A	L2742A	L2748A	9Y0J0A (~200K pag	L2756A (~100K pages)	L2756A (~100K pages)	L2756A (~100K pages)	9Y0H9A (~200K pages)	7QH79A (~100K pages)	7QH79A (~100K pages)	7QH79A (~100K pages)
HP Care Pack Services[4]													
Standard warranty	1 year	1 year	1 year	1 year	1 year	1 year	1 year	1 year	1 year	1 year	1 year	1 year	1 year
1-year post warranty next business day	U9TW2E	UV257PE	U8ZS4PE U8ZS5PE	U8TG4PE U8TG5PE	U8TH2PE	N/A	UD3C8PE UD3C9PE	U5X46PE [X] U5X47PE [OX]	UH373PE UH374PE	UF8F3PE	UD3E8PE UD3E7PE	U9JR5PE U9JR6PE	U9JQ7PE U9JQ8PE
3-year next business day	U9TW3E U9TW4E	U4937E U4938E	U4939E	U8TF9E U8TG1E	U8TG7E U8TG9E	UF8E0E UF8E1E	UD3C0E UD3C3E	U1Q59E [X] U1Q60E [OX]	UH370E UH372E	UF8F0E	UD3E2E UD3E3E	U9JR1E U9JR2E	U9JQ3E U9JQ4E
5-year next business day	N/A	N/A	UH361E	N/A	N/A	UF8E2E	UD3C2E UD3C5E	U5X50E [X] U1Q62E [OX]	U0MF5E U0QN0E	N/A	N/A	N/A	N/A