

Product data sheet

Specifications



APC Performance SurgeArrest 11 Outlet with Phone (Splitter) and Coax Protection, 120V

P11VT3

⚠ Discontinued on: Feb 14, 2024

⚠ To be discontinued

⚠ To be end-of-service on: Sep 30, 2024

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	8 ft (2.4 m)
Number of cables	1
Provided equipment	Coaxial cable Telephone Cable User Manual

Physical

Color	Black
Height	1.6 in (4 cm)
Width	4.7 in (11.9 cm)
Depth	11.9 in (30.2 cm)
Net Weight	2.34 lb(US) (1.06 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
Switching current capacity	15 A

Output

Number of power socket outlets	11
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	L-N: 400 L-G: 500 N-G: 500
Product Certifications	CSA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	UL 1363 UL 1449
Equipment protection policy	Lifetime : \$100000

Environmental

Ambient Air Temperature for Operation	5.0000000000...113.0000000000 °F (-15...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

Data Lines Protected (multi-line only)	1-4
NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	70 dB
Surge energy rating	3020 J

Ordering and shipping details

GTIN	731304249030
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.4 in (6 cm)
Package 1 Width	13.6 in (34.5 cm)
Package 1 Length	7.6 in (19.2 cm)
Package 1 Weight	2.98 lb(US) (1.35 kg)
Number of Units in Package 2	6
Package 2 Height	15 in (381.0000000000 mm)
Package 2 Width	8 in (203.2 mm)
Package 2 Length	15 in (381.0000000000 mm)
Package 2 Weight	19.58 lb(US) (8.88 kg)
SCC14	10731304249037

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Circularity Profile [End of Life Information](#)
