

# Product data sheet

Specifications



## APC 19" Rack LCD Console

AP5719

### Overview

<b>Presentation</b>	1U rack-mountable keyboard, mouse, and LCD console with US English keyboard layout.
<b>Lead time</b>	Usually in Stock

### Main

<b>Main Input Voltage</b>	100 V 240 V
<b>Number of rack unit</b>	1U
<b>Provided equipment</b>	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Rack mounting hardware Single user rack mount kit USB cable USB KVM cable

### Physical

<b>Color</b>	Black
<b>Height</b>	1.7 in (4.4 cm)
<b>Width</b>	19.0 in (48.2 cm)
<b>Depth</b>	26.2 in (66.5 cm)
<b>Net Weight</b>	38.4 lb(US) (17.4 kg)
<b>mounting location</b>	Front Rear
<b>Mounting preference</b>	No preference
<b>Mounting Mode</b>	Rack-mounted
<b>Maximum Mounting Depth</b>	41.33 in (104.98 cm)
<b>minimum mounting depth</b>	26.8 in (68 cm)

### Input

<b>Input Frequency</b>	50/60 Hz
------------------------	----------

### Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

<b>Product Certifications</b>	C-tick CE Industry Canada KCC NOM UL Listed VCCI Class A VDE TAA compliance
-------------------------------	---

---

<b>Standards</b>	EN 55022 Class A EN 55024 EN 60950 FCC Part 15 class A IEC 60950
------------------	--

---

## Environmental

---

<b>Ambient Air Temperature for Operation</b>	32.0000000000...104.0000000000 °F (0...40 °C)
--	---

---

## Supported Hardware

---

<b>display size</b>	19 inch
<b>Trackball Type</b>	PS/2 Touchpad USB mouse
<b>Display Type</b>	LCD display
<b>LCD Power Consumption</b>	19 W
<b>Pixel size</b>	0.26

---

## Ordering and shipping details

---

<b>GTIN</b>	731304283294
<b>Country of origin</b>	CN

---

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	6.0 in (15.2 cm)
<b>Package 1 Width</b>	32.5 in (82.6 cm)
<b>Package 1 Length</b>	26.5 in (67.3 cm)
<b>Package 1 Weight</b>	46.28 lb(US) (20.99 kg)

---

## Contractual warranty

---

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back   Transparency   RoHS/REACH

## Resource performance


 Take-Back Program Available

---


## Well-being performance

 Reach Free Of Svhc


---

 Lead Free

---

 Mercury Free

---

 Rohs Exemption Information   [Yes](#)

---

## Certifications & Standards

Reach Regulation   [REACH Declaration](#)

---

Eu Rohs Directive   Compliant with Exemptions

---

Environmental Disclosure   [Product Environmental Profile](#)

---

Weee   The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

---

Circularity Profile   [End of Life Information](#)

---