


# High Security



Maximum security for confidential documents



## NSA/CSS Specification 02-01 | 04-02 13,270 particles per sheet

NSA approved for U.S. government, military and security services

Dahle high security shredders offer the greatest protection available. These machines are designed for military, federal, state or local governments as well as Department of Defense contractors engaged in projects where National Security is a concern.

**1-5 Users**

Recommended

**Security Levels**

**Special Features**

CleanTEC®  
Air Filter

EvenFlow  
Lubricator

Jam  
Protection

SmartPower  
Energy Mgmt.

German  
Engineered

Optical  
Media

| Model   | Security Level | NSA Volume Rating | Capacity #20 / #16 | Shred Size  | Waste Volume | Feed Width | Special Features |           | Features       |             |            | Staples /Clips | CDs /DVDs | Warranty Shredder   Cylinders | Dimensions length x width x height | Weight  |
|---------|----------------|-------------------|--------------------|-------------|--------------|------------|------------------|-----------|----------------|-------------|------------|----------------|-----------|-------------------------------|------------------------------------|---------|
|         |                |                   |                    |             |              |            | Oil-Free         | CleanTEC® | Jam Protection | Smart Power | Auto Oiler |                |           |                               |                                    |         |
| 20434ds | P-7            | Low               | 4 / 6              | 1mm x 4.7mm | 6 gal.       | 9½"        |                  |           |                |             |            |                |           | 2 years   1 year              | 14" x 16" x 18"                    | 66 lbs  |
| 40334   | P-7            | Medium            | 5 / 7              | 1mm x 4.7mm | 23 gal.      | 10¼"       |                  |           |                |             |            |                |           | 2 years   1 year              | 18¼" x 21½" x 34¼"                 | 94 lbs  |
| 41334   | P-7            | High              | 5 / 7              | 1mm x 4.7mm | 23 gal.      | 10¼"       | CleanTEC®        |           |                |             |            |                |           | 2 years   1 year              | 18¼" x 21½" x 34¼"                 | 94 lbs  |
| 40434   | P-7            | High              | 8 / 10             | 1mm x 4.7mm | 30 gal.      | 10¼"       |                  |           |                |             |            |                |           | 2 years   1 year              | 18¼" x 21½" x 36¾"                 | 105 lbs |
| 41434   | P-7            | High              | 8 / 10             | 1mm x 4.7mm | 30 gal.      | 10¼"       | CleanTEC®        |           |                |             |            |                |           | 2 years   1 year              | 18¼" x 21½" x 36¾"                 | 102 lbs |
| 40534   | P-7            | High              | 8 / 10             | 1mm x 4.7mm | 38 gal.      | 12"        |                  |           |                |             |            |                |           | 2 years   1 year              | 21" x 29" x 34½"                   | 146 lbs |
| 41534   | P-7            | High              | 8 / 10             | 1mm x 4.7mm | 38 gal.      | 12"        | CleanTEC®        |           |                |             |            |                |           | 2 years   1 year              | 21" x 29" x 34½"                   | 146 lbs |
| 20394   | P-7            | High              | 9 / 11             | 1mm x 4.7mm | 50 gal.      | 16"        |                  |           |                |             |            |                |           | 2 years   1 year              | 24½" x 29½" x 46¾"                 | 245 lbs |
| 707 PS  | P-7            | High              | 11 / 13            | 1mm x 5mm   | 53 gal.      | 16"        |                  |           |                |             |            |                |           | 1 year                        | 21¾" x 28" x 43"                   | 320 lbs |
| 717 OS  | O-5            | High              | 1 disc             | 2mm x 4mm   | 20 gal.      | 5"         |                  |           |                |             |            |                |           | 1 year                        | 19¾" x 22¾" x 32¼"                 | 165 lbs |
| 727 CS  | P-7   O-5      | High              | 11 / 13            | 1mm x 5mm   | 53 gal.      | 9"   5"    |                  |           |                |             |            |                |           | 1 year                        | 21¾" x 28" x 43"                   | 330 lbs |

## 20434 DS



- NSA/CSS Specification 02-01
- NSA Tested Volume Rating: Low
- Precision milled cutting cylinders
- Automatic jam protection
- Includes Pelican™ deployment case



**P-7** Sheet Capacity: 4  
Waste Volume: 6 gal.

## 40334



## 41334



- NSA/CSS Specification 02-01
- NSA Tested Volume Rating: Medium
- Automatic EvenFlow lubricator
- Automatic jam protection
- SmartPower energy management



**P-7** Sheet Capacity: 5  
Waste Volume: 23 gal.

## 40434



## 41434



- NSA/CSS Specification 02-01
- NSA Tested Volume Rating: High
- Automatic EvenFlow lubricator
- SmartPower energy management
- Chain driven for maximum power



**P-7** Sheet Capacity: 8  
Waste Volume: 30 gal.

## 40534



## 41534



- NSA/CSS Specification 02-01
- NSA Tested Volume Rating: High
- Automatic EvenFlow lubricator
- SmartPower energy management
- Chain driven for maximum power



**P-7** Sheet Capacity: 8  
Waste Volume: 38 gal.

## 20394



- NSA/CSS Specification 02-01
- NSA Tested Volume Rating: High
- Precision milled cutting cylinders
- Automatic EvenFlow lubricator
- Automatic jam protection
- Chain driven for maximum power



**P-7** Sheet Capacity: 9  
Waste Volume: 50 gal.

## 707 PS



- High Security Paper Shredder
- NSA/CSS 02-01 Approved
- NSA Tested Volume Rating: High
- Chain driven continuous duty motor
- Automatic EvenFlow lubricator
- Automatic Jam protection



**P-7** Sheet Capacity: 11  
Waste Volume: 53 gal.

## 717 OS



- High Security Optical Media Shredder
- NSA/CSS 04-02 Approved
- NSA Tested Volume Rating: High
- Chain driven continuous duty motor
- Automatic EvenFlow lubricator
- Automatic Jam protection



**0-5** Capacity: 1 disc  
Waste Volume: 20 gal.

## 727 CS



- High Security Paper | Optical Shredder
- NSA/CSS 02-01 | NSA/CSS 04-02
- NSA Tested Volume Rating: High
- Chain driven continuous duty motor
- Automatic EvenFlow lubricator
- Automatic Jam protection



**P-7** **0-5** Sheet Capacity: 11  
Waste Volume: 53 gal.