

# APC Symmetra LX 4kVA Power Module, 200/208V

SYPM4KP

#### **Overview**

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main		
Main Input Voltage	200 V 208 V	
Product or Component Type	Power module	
Other Input Voltage	240 V	
Main Output Voltage	100 V 120 V 200 V 208 V	
Other Output Voltage	240 V	
Kw Rating	3200 W	
Rated power in VA	4000 VA	
Output connector type	Hard Wire 4-wire (2PH+N+G) 1	
number of rack unit	0U	
Number of cables	1	
Provided Equipment	Installation guide	
Range of Product	Symmetra Power Module	

## **Batteries & Runtime**

Run Time	View Runtime Graph ☐	
Included Battery Modules	0	
Battery Slots Empty	0	
Additional information	ation Configurable for 120/208 or 120/240 output voltage	

# **Physical**

_	
color	Silver
Height	5.9 in (15 cm)
Width	9.8 in (25 cm)
Depth	22.2 in (56.5 cm)
Net Weight	33.07 lb(US) (15 kg)
Mounting preference	No preference

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting Mode	Not rack-mountable
USB compatible	No

# Input

Input Frequency	4565 Hz auto-sensing
Efficiency at full load	155276 V
Input Power Factor at Full Load	0.98

## **Output**

•	
Max Configurable Power (Watts)	3200 W
Harmonic distortion	Less than 5 % at full load
Output Frequency (sync to mains)	4763 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal not synced 60 Hz +/- 0.1 % for 60 Hz nominal not synced
Crest factor	Up to 5 : 1
Topology	Double Conversion Online
Waveform Type	Sine wave

## Conformance

Product Certifications	CSA
Standards	FCC Part 15 class A UL 1778

#### **Environmental**

Ambient Air Temperature for Operation	32104 °F (040 °C)	
Relative Humidity	095 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	5113 °F (-1545 °C)	
Storage Relative Humidity	095 %	
Storage altitude	015000 ft (0.00000000004572.0000000000 m)	
acoustic level	62 dBA	

# Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS	
GTIN	731304218876	
Returnability	No	
Country of origin	PH	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.3 in (43.9 cm)
Package 1 Width	31.1 in (79 cm)
Package 1 Length	13.0 in (33 cm)

Package 1 Weight

40.08 lb(US) (18.18 kg)

## **Contractual warranty**

Warranty

2 years repair or replace

### **Sustainability**

Green Premium<sup>™</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Energy Efficient Take-back

#### Resource performance

**Energy Efficient Product** 



Take-Back Program Available

#### Well-being performance

Rohs Exemption Information

Yes

Reach Regulation	REACh Declaration

**Eu Rohs Directive** Compliant with Exemptions

**China Rohs Regulation** China RoHS declaration

Product out of China RoHS scope. Substance declaration for your information.