

# Product data sheet

Specifications



## APC Smart-UPS SRT Step-Down Transformer, 10kVA, rackmount, 4U, 2x NEMA L5-20R & 2x NEMA L14-30R outlets

SRT10KRMTF

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage 208 V

Product or Component Type Transformer

Main Output Voltage 120 V  
208 V  
240 V

Output connector type Hard Wire 3-wire (2PH + G) 2  
Hard Wire 4-wire (2PH+N+G) 1

Provided Equipment Mounting Hardware  
Rack Mounting brackets  
Safety guide  
User Manual  
Warranty card

Range of Product Smart-UPS Accessories

### Physical

Color Black

Height 6.9 in (17.4 cm)

Width 17.008 in (43.2 cm)

Depth 29.5 in (74.9 cm)

Net Weight 220.00 lb(US) (99.79 kg)

Mounting preference Lower

Mounting Mode Rack-mounted

Mounting position Horizontal

### Input

Acceptable Input Voltage 200...240 V

Max line current 60 A

Input current limits 60 A

Load Capacity 10000 VA

Input Frequency 45...65 Hz

Number of input connectors 1 Hard Wire 3-wire (2PH + G)

### Output

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum Total Current Draw per Phase	60 A
Number of power socket outlets	4
Number of power socket outlets	2 NEMA L5-20R 2 NEMA L14-30R

## Conformance

Product Certifications	CE CSA UL Listed
------------------------	------------------------

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

GTIN	731304318859
Country of origin	PH

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.0 in (40.6 cm)
Package 1 Width	39.4 in (100 cm)
Package 1 Length	23.6 in (60 cm)
Package 1 Weight	275.005 lb(US) (124.74 kg)

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

## Resource performance

 Take-Back Program Available

## Well-being performance

 Rohs Exemption Information Yes

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

**Eu Rohs Directive** Compliant with Exemptions

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

**Environmental Disclosure** [Product Environmental Profile](#)

**Weee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

**Circularity Profile** [End of Life Information](#)