

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 45U, White, 2124H x 600W x 1200D mm

AR3305W

Overview

Lead time Usually in Stock

Main

Product or Component Type	Rack enclosure
number of rack unit	45U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels User Manual

Physical

Height	83.6 in (212.4 cm)
Width	23.6 in (60 cm)
Depth	47.2 in (120 cm)
Net Weight	310.9 lb(US) (141 kg)
Color	White
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.3 in (104.8 cm)
minimum mounting depth	7.50 in (19.05 cm)
rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 lb(US) (1020.6 kg) dynamic 3750 lb(US) (1701.0 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN 731304322481

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	88.2 in (224 cm)
Package 1 Width	52.5 in (133.4 cm)
Package 1 Length	29.4 in (74.6 cm)
Package 1 Weight	349.2 lb(US) (158.4 kg)

Contractual warranty

Warranty 5 year repair or replace

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)





Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)