

# Product data sheet

Specifications



## APC NetShelter 6U Wallmount Rack Enclosure Cabinet Single Hinged Switch Depth

AR106SH4

**Product availability: Stock - Normally stocked in distribution facility**

### Overview

|                     |  |
|---------------------|--|
| <b>Presentation</b> | Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches, and patch panels. The cabinet's door is reversible and is compatible with APC's Netbotx security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately) Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting Wall mount cabinet, mounting depth range of 2.87 to 12.95 inches, 200lb weight capacity, 19" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty. |
| <b>Lead time</b>    | Usually in Stock   |

### Main

|                                  |                |
|----------------------------------|----------------|
| <b>Product or Component Type</b> | Rack enclosure |
| <b>number of rack unit</b>       | 6U             |

### Physical

|                                   |                             |
|-----------------------------------|-----------------------------|
| <b>Height</b>                     | 14.0 in (35.5 cm)           |
| <b>Width</b>                      | 23.6 in (60 cm)             |
| <b>Depth</b>                      | 15.7 in (40 cm)             |
| <b>Net Weight</b>                 | 24.49 lb(US) (11.11 kg)     |
| <b>Color</b>                      | Black                       |
| <b>Mounting Support</b>           | Wall                        |
| <b>Mounting preference</b>        | No preference               |
| <b>Mounting Mode</b>              | Not rack-mountable          |
| <b>Maximum Mounting Depth</b>     | 12.95 in (32.89 cm)         |
| <b>minimum mounting depth</b>     | 2.87 in (7.29 cm)           |
| <b>rack width</b>                 | 19"                         |
| <b>Permanent permissible load</b> | 200 lb(US) (90.7 kg) static |

### Conformance

|                  |                     |
|------------------|---------------------|
| <b>Standards</b> | UL 2416<br>EIA-310E |
|------------------|---------------------|

### Ordering and shipping details

|                 |                        |
|-----------------|------------------------|
| <b>Category</b> | 80230-IG SEBA TO SEUSA |
|-----------------|------------------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

|                   |              |
|-------------------|--------------|
| Discount Schedule | BMS1         |
| GTIN              | 731304402671 |
| Returnability     | No           |
| Country of origin | CN           |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Number of Units in Package 1 | 1                       |
| Package 1 Height             | 17.1 in (43.5 cm)       |
| Package 1 Width              | 19.09 in (48.5 cm)      |
| Package 1 Length             | 27.0 in (68.5 cm)       |
| Package 1 Weight             | 29.89 lb(US) (13.56 kg) |

## Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

## Resource performance

Energy Efficient Product

Take-Back Program Available

## Well-being performance

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)