

Product data sheet

Specifications



APC NetShelter 12U Wallmount Rack Enclosure Cabinet Single Hinged Switch Depth

AR112SH4

Overview

Presentation Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches, and patch panels. The cabinet's door is reversible and is compatible with APC's Netbotx security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately) Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting 12U Wall mount cabinet, mounting depth range of 2.87 to 12.95 inches, 200lb weight capacity, 19" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

number of rack unit 12U

Physical

Height 24.4 in (62 cm)

Width 23.6 in (60 cm)

Depth 15.7 in (40 cm)

Net Weight 32.80 lb(US) (14.88 kg)

Color Black

Mounting Support Wall

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 12.95 in (32.89 cm)

minimum mounting depth 2.87 in (7.29 cm)

rack width 19"

Permanent permissible load 200 lb(US) (90.7 kg) static

Conformance

Standards UL 2416
EIA-310E

Ordering and shipping details

GTIN 731304402695

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin	CN
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	27.6 in (70 cm)
------------------	-----------------

Package 1 Width	19.09 in (48.5 cm)
-----------------	--------------------

Package 1 Length	27.0 in (68.5 cm)
------------------	-------------------

Package 1 Weight	39.71 lb(US) (18.01 kg)
------------------	-------------------------

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
