

# EATON 9PX LITHIUM ION UPS RUNTIME CHART



| UPS+EBM \ Load (w)      | 75     | 150 | 300   | 450  | 600  | 750   | 900   | 1050  | 1200  | 1350 | 1500 |
|-------------------------|--------|-----|-------|------|------|-------|-------|-------|-------|------|------|
| 9PX1500IRTANZ-L         | 128    | 78  | 45    | 32   | 25   | 21.5  | 17    | 15    | 13    | 11.5 | 10.5 |
| 9PX1500IRTANZ-L + 1 EBM | 324    | 197 | 114   | 81   | 63   | 56    | 43    | 37    | 33    | 29   | 27   |
| 9PX1500IRTANZ-L + 2 EBM | 520    | 316 | 183   | 131  | 101  | 87    | 69    | 60    | 53    | 47   | 42   |
| 9PX1500IRTANZ-L + 3 EBM | 715    | 435 | 252   | 180  | 139  | 119   | 95    | 82    | 72    | 64   | 58   |
| 9PX1500IRTANZ-L + 4 EBM | 911    | 553 | 321   | 229  | 177  | 152   | 121   | 104   | 92    | 82   | 74   |
| UPS+EBM \ Load (w)      | 90     | 180 | 360   | 540  | 720  | 900   | 1080  | 1260  | 1440  | 1620 | 1800 |
| 9PX2000IRTAU-L          | 154    | 109 | 64    | 43   | 33   | 26.5  | 23    | 19.5  | 17    | 15   | 13.5 |
| 9PX2000IRTAU-L + 1 EBM  | 388    | 275 | 163   | 110  | 83.5 | 68    | 58    | 50    | 43.5  | 39   | 35   |
| 9PX2000IRTAU-L + 2 EBM  | 623    | 442 | 261   | 176  | 134  | 108   | 93    | 80    | 70    | 62   | 56   |
| 9PX2000IRTAU-L + 3 EBM  | 857.5  | 608 | 359.5 | 243  | 185  | 149.5 | 127.5 | 109.5 | 96.5  | 86   | 77   |
| 9PX2000IRTAU-L + 4 EBM  | 1091.5 | 744 | 457   | 309  | 235  | 190   | 163   | 140   | 122.5 | 109  | 98   |
| UPS+EBM \ Load (w)      | 150    | 300 | 600   | 900  | 1200 | 1500  | 1800  | 2100  | 2400  | 2700 | 3000 |
| 9PX3000IRTANZ-L         | 123    | 77  | 41    | 27.5 | 20.5 | 17    | 14    | 12    | 10.5  | N/A  | N/A  |
| 9PX3000IRTANZ-L + 1 EBM | 286    | 184 | 102   | 71   | 54   | 45    | 37    | 32    | 28    | 25   | 22   |
| 9PX3000IRTANZ-L + 2 EBM | 458    | 295 | 164   | 114  | 87   | 71    | 59    | 51    | 44    | 40   | 38   |
| 9PX3000IRTANZ-L + 3 EBM | 631    | 405 | 225   | 157  | 120  | 98    | 81    | 70    | 61    | 55   | 53   |
| 9PX3000IRTANZ-L + 4 EBM | 803    | 516 | 287   | 200  | 153  | 125   | 104   | 89    | 78    | 69   | 67   |

Runtimes are in minutes, approximate to +/- 15% accuracy as actual runtime may vary based on discharge conditions