


**OVERVIEW**



1. Power Connector	6. USB 3.2 Gen 1
2. HDMI 2.0	7. Audio-out (3.5mm)
3. DP 1.4	8. USB 3.2 Gen 1
4. USB-C 3.2 Gen 1 (DP 1.4 Alt Mode)	9. USB 3.2 Gen 1
5. Ethernet (RJ-45)	10. USB 3.2 Gen 1

## PERFORMANCE

### Panel

#### Panel

3-side NearEdgeless, VA

#### Display Size

34 inches

#### Max View Area

WxH: 792.2 x 333.7 mm (31.21 x 13.14 inches)

#### Resolution

3440 x 1440

#### Aspect Ratio

21:9

#### Pixel Pitch

0.232 x 0.232 mm

#### Dot / Pixel Per Inch

110 dpi

#### Brightness

350 nits

#### Contrast Ratio

- Contrast Ratio: 3000:1
- Dynamic Contrast Ratio: 3M:1

#### View Angle (H / V)

Horizontal: 178°, Vertical: 178°

#### Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

#### Refresh Rate

60 Hz

#### Color Gamut

- Coverage Ratio: 99% sRGB
- Color Area Ratio: 126% sRGB

#### Color Support

16.7 Million

#### Color Depth

8-bit

#### Anti-glare

Support

#### Curvature

1500R

### Operating System

#### Operating System

- Windows® 10 Support
- Windows 11 Support

### Multi-Media

#### Camera

- ThinkVision® MC 60 monitor webcam (Some models only)
- No bundled webcam (Support ThinkVision MC 60 Monitor Webcam, sold separately)

#### Speakers

Optional Modular Soundbar support (MS30 Monitor Soundbar)

## Power Supply

### Power Consumption

- Typical / Max: 31W / 130W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 30W
- Energy Star TEC: 93kWh
- Internal Power Supply

### Voltage Required

AC 100 to 240 V (50-60Hz)

## Special Features

### Special Features

- Natural Low Blue Light
- Lenovo® ThinkColour (Lenovo Display Control Center) Support  
ThinkColour can only be used with Windows 10 and Windows 11
- Smart Power  
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

## DESIGN

### Mechanical

#### Bezel Width

- Side: 2.1mm
- Top / Bottom: 2.1mm / 22.8mm

#### Video Cables

- 1x USB-C® to USB-C Cable (1.8m)
- 1x DP Cable (1.8m) (PRC Workstations)

#### Cable Management

Support

#### Case Color

Raven black

#### Dimensions (WxDxH)<sup>[1]</sup>

Models	Dimensions
Highest Position	808.4 x 231.6 x 569.3 mm (31.83 x 9.12 x 22.41 inches)
Lowest Position	808.4 x 231.6 x 414.3 mm (31.83 x 9.12 x 16.31 inches)
Head Only	808.4 x 110.1 x 367.5 mm (31.83 x 4.33 x 14.47 inches)

#### Packaging Dimensions (WxDxH)

1070 x 525 x 187 mm (42.13 x 20.67 x 7.36 inches)

#### Weight<sup>[2]</sup>

Models	Weight
Monitor With Stand	9.5 kg (20.94 lbs)
Monitor Head Only	7.0 kg (15.43 lbs)

#### Packaging Weight

14.8 kg (32.63 lbs)

#### Mounting

Supports VESA mount 100mm

#### Stand

Supports -5° to +23.5° tilt, left & right 45 swivel, up to 155mm lift

## In the Box

- Monitor with Stand
- 1x Power cable (1.8m)
- 1x DP Cable (1.8m) (PRC Workstations only)
- 1x USB-C to USB-C Cable (1.8m)
- Quick Setup Guide
- Warranty Booklet

### Notes:

1. The system dimensions vary depending on configurations.
2. The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

## CONNECTIVITY

### Network

#### Ethernet

Support 10M / 100M / 1000M

### Ports

#### Rear Ports<sup>[1]</sup>

- 1x USB-C 3.1 Gen 1 (DP 1.2 Alt Mode, data transfer, up to 75W), USB upstream
- 1x HDMI® 2.0
- 1x DisplayPort™ 1.4
- 4x USB 3.2 Gen 1 (1x BC 1.2), USB downstream
- 1x Ethernet (RJ-45)
- 1x audio-out (3.5mm)
- 1x Power Connector

### Notes:

1. Up to 75W power delivery to compatible devices by USB-C. Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

## SECURITY & PRIVACY

### Security

#### Physical Locks

Kensington® Security Slot™

## SERVICE

### Warranty

#### Base Warranty

3-year courier or carry-in service

## CERTIFICATIONS

### Green Certifications

#### Green Certifications

- EPEAT™ Gold
- Energy Star Certified
- TCO Certified 9.0
- TCO edge 2.0
- Volatile Organic Compound Certification
- RoHS compliant

## Other Certifications

### Other Certifications

- Eyesafe® Display Certified
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

