

Designed to provide comprehensive solutions for office, retail, education and industrial usages in only 0.9L compact size



24/7 Reliability



Fanless



DDR4
Memory



Triple
Storage



2.5" HDD
or 2.5" SSD



Wi-Fi 5
802.11ac



Wi-Fi 6
802.11ax



2.5G LAN



Kensington
Lock



4K



3 Displays

Maximum possibilities in only 0.62L compact size

- Powered by Intel® Celeron® or Pentium® processors
- Fanless chassis makes PN41 even more reliable and durable in industrial applications, and quieter in every scenario
- Delivers class-leading graphics performance with Integrated Intel UHD Graphics

Diverse application

- Classic black and stunning white can blend into any environment
- Support for triple displays in stunning 4K UHD resolution
- Can be placed almost anywhere and even attached to the back of a display with a VESA mount for a space-saving, all-in-one solution


Seamless media experience

- ASUS Mini PC PN41 supports HDMI® CEC and has a built-in IR sensor, allowing you to manage almost all your media devices
- Sets a personal digital assistant that helps you get things done easily such as accurate voice control

Longevity and manageability

- The ASUS Business Manager designed for businesses that lack adequate IT support, it simplifies the processes of management and maintenance
- An admin password can be applied to ensure that only authorized users are able to access the system's security settings

Over view:



Accessories list:



Feature table:

Power		Security		Remote	
PD input	Y	fTPM 2.0	Y	ASUS Control Center	optional
Extended Power Button	N	dTPM 2.0	optional	Watchdog timer	optional
BIOS		Kensington lock	Y	ASUS Cooperate Stable Model	optional
AC Power loss	Y	Pad-lock	Y	MyLogo	Y
HDMI-CEC	Y	Chassis Intrusion	N	MyASUS / CSM	
CrashFree	Y	Reliability		Smart Fan Control	N
EZ Flash	Y	24/7 Durability Test	Y	AI Noise Cancellation	N
BIOS Customization	Y	Military-grade Durability	N	Wi-Fi Smart Connect	N
PXE/WOL	Y	Anti-Surge	Y		
USB Single Port Control	Y	Fanless	N		

Model		PN41	
OS		Windows®11 64bit, Windows®11 Pro 64bit, Linux, or W/O OS (Please check with local rep on validated Linux version)	
CPU		Intel® Pentium® Silver N6000/ Intel® Celeron® N5100/ N4500	
Chipset		Integrated	
Graphics		Integrated - Intel® Gen11 Graphics	
Memory		2 x DDR4 SO-DIMM slots for DDR4 2933 MHz, 1 x 8GB - 2 x 8GB (total)	
Storage		1 x eMMC onboard for 32GB - 128GB 1 x 6Gb/s SATA connector for 2.5" 1TB HDD/SSD* 1 x M.2 2280 PCIe Gen3 slot for 128GB - 1TB SSD* (NVMe only) *For higher capacity please refer to QVL (location: official website → Support → CPU / Memory Support)	
Wireless Network		Intel® Wi-Fi 6 and Bluetooth 5 Intel® Wi-Fi 5 and Bluetooth 5	
LAN		Intel® LAN, 10/100/1000/2500 Mbps Supports Wake on LAN / PXE / Auto Power on / RTC Wake	
Interface	Front I/O	1 x USB 3.2 Gen2 Type-C (10 Gbps, support Battery Charging 1.2) 1 x USB 3.2 Gen1 (5 Gbps) 1 x Audio Jack(Line out/ Mic in/ Headphone out) 1 x Dual-Microphone Array (optional) 1 x IR receiver (optional) 1 x 3 in 1 Card reader (optional) *All data transfer speed is according to ASUS testing result, actual performance may vary depending on objective environmental changes.	
	Side I/O	1 x Kensington Lock	
	Rear I/O	1 x USB 3.2 Gen1 Type-C (5 Gbps, support Display Port 1.4, PD input) 2 x USB 3.2 Gen1 (5 Gbps) 1 x HDMI 2.0 Port 1 x Configurable Port (options: Display Port 1.4/COM/ VGA/ LAN) 1 x Intel LAN (RJ45) 1 x DC-in *All data transfer speed is according to ASUS testing result, actual performance may vary depending on objective environmental changes.	
TPM		fTPM 2.0 or TPM 2.0 chip (Optional)	
BIOS Function		64 Mb Flash ROM, UEFI AMI BIOS, PnP, DMI2.0, WfM2.0, SM BIOS 2.8, ACPI 5.0, Multi-language BIOS, ASUS EZ Flash 3, ASUS CrashFree BIOS 3, My Favorites, Quick Note and ASUS DRAM SPD (Serial Presence Detect) memory information	
Software		The following software are included in OS: ASUS Business manager, ASUS Product registration program, Asus Control Center test, Watchdog timer	
Power Supply		19Vdc, 3.42A or 19.5Vdc, 3.33A 65W	
Physical	Dimension	115 x 115 x 49 mm (0.62L)	
	Weight	0.55 kg (barebone)	
Max Resolution	HDMI	4096 x 2160 @ 60 Hz	
	DP	3840 x 2160 @ 60 Hz	
	VGA	1920 x 1200 @ 60 Hz	
Temperature	Operating	0°C~50°C	
	Storage	-40°C~85°C	
Humidity		0%~95% Relative Humidity	
Acoustic	Idle mode	<25 dBA	N/A
	Full loading	<35 dBA * Test results will vary slightly depending on the HDD/SSD SKU selected by customer	
Certificates		BSMI / CB / CE / FCC / UL / CCC / Energy Star / C-Tick / WiFi / RF / VCCI	