

Poly Blackwire 3220 Stereo USB-C Black Headset +USB-C/A Adapter (Bulk)



Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that's built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what's not to love?

Poly signature audio quality

Experience the high-quality audio you expect with a headset that offers PC wideband and a noise-canceling mic.

Advanced connectivity

Manage calls on your preferred device with the comfort and durability of a corded headset.

Long-lasting comfort and portability

Relax knowing your headset is secure - lightweight metal headband offers durability plus a custom fit.

Featuring

Enhanced call quality

Dynamic EQ optimizes your calls and auto-adjusts for high-quality media sound.

Connectivity options

Options for your device: USB-C cord with tethered USB-A adapter.

Wearing style

Hi-fi stereo wearing style for an immersive experience.

Lightweight design

Lightweight headband with a comfortable custom fit.

Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management.

Optimized for communications platforms

This headset is optimized and certified to work with top virtual meeting providers.

Poly Blackwire 3220 Stereo USB-C Black Headset +USB-C/A Adapter (Bulk)

Specifications

Compatible with

Compatible operating systems: Windows 11; Windows 10; macOS

Connectivity and communications

Connection type: Wired: USB Type-C®, USB Type-C®/A adapter

Ear cushions: Foam (surface material)

Headphone type: On-ear (stereo)

User interface features

Button user controls: Call answer/end; Call ignore/on hold; Redial; Mute; Volume +/-

Audio

Acoustic protection technology: SoundGuard¹

Microphone type: Noise cancelling

Microphone bandwidth: 100 Hz to 10 kHz

Speaker bandwidth: 200 Hz to 6.8 kHz (speech mode); 20 Hz to 20 kHz (media mode)

Speaker size: 28 mm

Signal-to-noise ratio: >24 dB

Frequency response (microphone): 100 Hz to 10 kHz

Sensitivity (microphone): 10 dB SLR

Sensitivity (speaker): 6 dB RLR

Power supply

Impedance: 32 ohm

Certifications

Certified collaboration software: Skype for Business; Avaya; Cisco Jabber

Ecolabels: TCO Certified

Poly Blackwire 3220 Stereo USB-C Black Headset +USB-C/A Adapter (Bulk)

Specifications

Management

Management software:
Poly Lens

Weight and dimensions

Product Primary Color: Black
Weight: 0.28 lb (with cable); 0.20 lb (without cable)
Product dimensions: 6.1 x 1.25 x 7.1 in
Package weight: 0.66 lb
Package dimensions: 7.48 x 8.26 x 2.16 in
Master carton quantity: 50
Master carton dimension: 19.17 x 20.55 x 15.47 in
Master carton weight: 17.63 lb
Cartons per layer: 4
Pallet (layers): 3
Cartons per pallet: 12
Products per layer: 200
Products per pallet: 600
Pallet weight: 787.05 lb
Pallet dimensions: 40 x 48 x 51.92 in
Cable length: 2.09 ft (inline module to headset); 4.72 ft (USB to inline module); 6.81 ft (total USB to headset)
Product number: 8X2J9A6
Product name: Poly Blackwire 3220 Stereo USB-C Black Headset +USB-C/A Adapter (Bulk)

Warranty

Poly standard two-year limited warranty

Country of origin

Country of origin: Made in China or Mexico

What is in the box

Headset
USB Type-C® cable
User guide
USB Type-C® to USB Type-A adapter

Poly Blackwire 3220 Stereo USB-C Black Headset +USB-C/A Adapter (Bulk)

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

March 2025
us-en

