

OVERVIEW



1. Control Buttons	8. Ethernet (RJ-45)
2. Kensington Security Slot	9. USB-C 3.2 Gen 1
3. AC Power-in	10. USB 3.2 Gen 1
4. HDMI 2.1 TMDS	11. Audio-out (3.5mm)
5. HDMI 2.1 TMDS	12. USB 3.2 Gen 1
6. USB-C 3.2 Gen 1 (DP 1.4 Alt Mode)	13. USB 3.2 Gen 1
7. DisplayPort 1.4	14. USB 3.2 Gen 1

PERFORMANCE

Panel

Panel

In-Plane Switching (IPS)

Backlight

WLED

Display Size

27 inches

Max View Area

WxH: 596.7 x 335.7 mm

Resolution

3840 x 2160 (2D)

Aspect Ratio

16:9

Pixel Pitch

0.155 x 0.155 mm

Dot / Pixel Per Inch

163 dpi

Brightness

310 cd/m²

Contrast Ratio

- Contrast Ratio: 1200:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

Refresh Rate

60Hz

Color Gamut

- 100% BT.709
- 100% sRGB
- 83% BT.2020
- 99% Adobe® RGB
- 99% DCI-P3

Color Support

16.7 Million

Color Depth

8-bit

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Operating System

Operating System

- Windows® 11 Support
- Windows® 10 Support

Multi-Media

Camera

No bundled webcam (Support ThinkVision® MC 60 Monitor Webcam, sold separately)

Microphone

No microphone

Speakers

Integrated Speakers, 2x 5W

Power Supply**Power Consumption**

- Typical / Max: 43.8W / 246W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features**Special Features**

- HDR Compliance (HDR10 Decoding)
- Factory Calibration: Avg. Delta E<1 (for DCI-P3, Adobe® RGB and sRGB)
- 3D Explorer5, available from Lenovo® Accessories and Display Manager (ThinkColour)
Lenovo® Accessories and Display Manager supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems)
- 3D Master (3D viewing App), Plugins, SDK
- Smart Power
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

3D Features

- 2D/3D Switchable
- 3D resolution: 1920 x 2160
- Environmental conditions: 0 lx - 1000 lx
- Eye tracking support
- Number of viewers: 1
- Optimal viewing angle: -20° to +20° horizontal, -20° to +20° vertical
- Optimal viewing distance: 60 - 100 cm
- Recommended 3D viewing distance: 70 - 90 cm
- Minimal PC Requirements:
Processor: Intel® Core™ i5-7400
Graphic: NVIDIA® GeForce GTX 1050 (or AMD, Intel® graphics card with equivalent performance)
Operating system: Windows® 10 (64-bit)
Memory: 8GB DDR5
Storage: 50GB available space
- Supported third-party software: Microsoft® 365, PTC Creo, Autodesk 3ds Max, Autodesk VRED, Lumiscaphe Patchwork 3D, Dassault Systems Deltagen, Unity & C++ (via SDK)
(Supported third-party products are listed. Compatibility is tested on limited versions/models only. Compatible product list is subject to change without notice. 3D monitor is developed to be compatible with and should be used with fully licensed specific versions of third-party software only. Lenovo® makes no representation or warranty, and assumes no responsibility with regard to, the selection, performance, or use of third-party products or services that are licensed/provided by third parties under their own terms and conditions and may be subject to license fees and/or other costs.)

DESIGN**Mechanical****ThinkCentre® M Series Support**

ThinkCentre® M Series Tiny, ThinkCentre® M Series Nano

Bezel Width

- Side: 8mm
- Top / Bottom: 8mm / 44.3mm

Buttons

- Menu joystick
- Power button
- Source Key
- Volume down button
- Volume up button

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	614.8 x 222.7 x 413 mm (24.2 x 8.77 x 16.26 inches)
Highest Position	614.8 x 222.7 x 568 mm (24.2 x 8.77 x 22.36 inches)
Head Only	614.8 x 72.3 x 390 mm (24.2 x 2.85 x 15.35 inches)

Packaging Dimensions (WxDxH)

720 x 165 x 520 mm (28.35 x 6.5 x 20.47 inches)

Weight^[2]

Models	Weight
Monitor With Stand	8.9 kg (19.6 lbs)
Monitor Head Only	6.6 kg (14.6 lbs)

Packaging Weight

12.4 kg (27.3 lbs)

Mounting

Supports VESA mount 100 x 100 mm

Stand

Supports -5° to +23.5° tilt, left & right 45 swivel, -90° to +90° pivot, up to 155mm lift

In the Box

- Monitor with Stand
- 1x DP Cable (1.8m)
- 1x HDMI® cable (1.8m)
- 1x USB-C® to USB-A Cable (1.8m)
- 1x USB-C® to USB-C® Gen 2 Cable (1.5m)
- 1x Power cable (1.8m)
- 1x Quick Setup Guide
- Factory Calibration Report
- Cleaning Cloth

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

Support 10M / 100M / 1000M

Ports^[1]

Rear Ports

- 1x USB-C® 3.2 Gen 1 (15W), USB downstream
- 1x USB-C® 3.2 Gen 1 (DP 1.4 Alt Mode and up to 100W PD), USB upstream

- 4x USB 3.2 Gen 1, USB downstream
- 2x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4
- 1x Ethernet (RJ-45)
- 1x Power Connector
- 1x audio-out (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™ (2.5 mm x 6 mm and 3 mm x 7 mm)

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- EU Energy Label Exempt (G-class)
- RoHS (2011/65/EU)

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

TÜV Rheinland® Eye Comfort Certification

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. **LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



