

OVERVIEW



1. Headphone / microphone combo jack (3.5mm)	6. USB-C (USB4 40Gbps), with DP 2.1
2. USB-A (USB 5Gbps)	7. USB-A (USB 5Gbps), Always On
3. USB-A (USB 5Gbps)	8. HDMI
4. Ethernet (RJ-45)	9. Power connector
5. USB-C (USB 10Gbps), with USB PD 65-100W & DP 2.1	

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ AI 7 300 Series Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics	NPU
AMD Ryzen™ AI 7 350	8	16	2GHz	5GHz	8MB L2 / 16MB L3	AMD Radeon™ 860M	AMD Ryzen™ AI

AI (Artificial Intelligence)

AI PC Category

AI-Powered Gaming PC

AI Performance

Up to 66 overall TOPS

NPU

Integrated AMD Ryzen™ AI, up to 50 TOPS

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- No preload operating system

Graphics

Graphics**

Graphics	Type	Memory	Boost Clock	TGP	AI TOPS (Peak)	Key Features
NVIDIA® GeForce RTX™ 5050 Laptop GPU	Discrete	8GB GDDR7	2662 MHz	115W	440 TOPS	DLSS 4, Reflex 2, DirectX® 12 Ultimate
NVIDIA® GeForce RTX™ 5060 Laptop GPU	Discrete	8GB GDDR7	2497 MHz	115W	572 TOPS	DLSS 4, Reflex 2, DirectX® 12 Ultimate
NVIDIA® GeForce RTX™ 5070 Laptop GPU	Discrete	8GB GDDR7	2347 MHz	115W	798 TOPS	DLSS 4, Reflex 2, DirectX® 12 Ultimate

Monitor Support

Monitor Support

Supports up to 4 independent displays (native display and 3 external monitors via HDMI® and USB-C®)

- HDMI® supports up to 8K@60Hz
- USB-C® supports up to 5K@60Hz

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 32GB DDR5-5600 offering

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Memory Type

DDR5-5600

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Max Storage Support^[1]

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 1TB each

Storage Slot

Two M.2 2280 PCIe® 4.0 x4 slots

Storage Type

Disk Type	Interface	Offering
M.2 2242 SSD	PCIe® NVMe®, PCIe® 4.0 x4	512GB / 1TB

Notes:

[1] The storage capacity supported is based on the test results with current Lenovo® storage offerings.

Removable Storage

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, audio by HARMAN, optimized with Nahimic Audio

Microphone

Dual-microphone array

Camera

FHD 1080p + IR, with E-shutter, fixed focus

Battery

Battery

80Wh Rechargeable Li-ion Battery, supports Super Rapid Charge (10min charge 0-30% capacity, 30min charge 0-70% capacity, 80min charge 0-100% capacity)

Max Battery Life^[1]

MobileMark® 30@250nits: 5.7 hr

Local video (1080p) playback@150nits: 11.2 hr

Notes:

[1] All battery life claims are approximate maximum and based on results using the MobileMark® 2014, MobileMark® 2018, MobileMark® 25, MobileMark® 30, JEITA 2.0, JEITA 3.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary depending on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter

245W slim tip (3-pin) AC adapter, 100-240V, 50-60Hz

Special Features

Special Features

AI Chip: LA3

DESIGN

Display

Display

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
15.1"	WQXGA (2560x1600)	None	OLED	500nits	Glossy	16:10	1,000,000:1	100% DCI-P3	165Hz	89° / 89° / 89° / 89°	Dolby Vision®, TÜV Low Blue Light (Hardware), DisplayHDR™ True Black 600, TÜV Rheinland® Flicker Free

Color Calibration

X-Rite® factory color calibration

Touchscreen

Non-touch

Input Device

Pen

No support

Keyboard

6-row, multimedia Fn keys, numeric keypad, Copilot key

Keyboard Backlight**

- 24-Zone RGB backlight
- White backlight

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

Mechanical

Dimensions (WxDxH)^[1]

344.9 x 255.35 x 22.50-23.99 mm (13.58 x 10.05 x 0.86-0.94 inches)

Weight^[2]

Around 2 kg (4.4 lbs)

Case Color

Eclipse black

Surface Treatment

Anodizing sandblasting

Case Material

Aluminium (top), PC-ABS (bottom)

System Lighting

No system lighting

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

WLAN + Bluetooth®^[1]

Wi-Fi® 7, 802.11be 2x2 Wi-Fi® + Bluetooth® 5.4, M.2 card^[2]

WWAN

No support

Ethernet^[3]

Gigabit Ethernet, 1x RJ-45, supports Wake-on-LAN

Notes:

[1] Bluetooth® may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

[2] Wi-Fi® 7 operation is subject to the regulation rules in each country.

[3] Wake-on-LAN needs the power adapter plugged in.

Ports^[1]

Standard Ports

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 65-100W and DisplayPort™ 2.1^[2]
- 1x USB-C® (USB4® 40Gbps), with DP 2.1
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Power connector

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

[2] Supports Lenovo® protocol for 140W charging but requires a unique Lenovo® adapter for operation.

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in SoC

Fingerprint Reader

No fingerprint reader

BIOS Security

- Hard disk password
- Master hard disk password
- Power-on password
- Supervisor password
- User hard disk password
- User password
- Self-healing BIOS

Other Security

E-shutter

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 1-year courier or carry-in with 2-year system board service (Korea only)
- 2-year (1-yr battery) courier or carry-in service

ACCESSORIES

Bundled Accessories

Bundled Accessories^[1]

None

Notes:

[1] For more compatible accessory solutions, please visit [Accessories for Legion 5 15AKP10](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature^[1]

At altitudes up to 2438 m (8,000 ft)

- Operating: 5°C to 35°C (41°F to 95°F)

- Storage: 5°C to 43°C (41°F to 109°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ErP Lot 3
- RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications


Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



AMD



AMD



AMD



AMD



AMD



AMD