


OVERVIEW



|                  |                    |
|------------------|--------------------|
| 1. HDMI 2.1 TMDS | 3. DisplayPort 1.2 |
| 2. HDMI 2.1 TMDS |                    |

## PERFORMANCE

### Panel

#### Panel

3-side NearEdgeless, In-Plane Switching

#### Backlight

WLED

#### Display Size

27 inches

#### Max View Area

- Active Area: 596.7 x 335.7 mm
- Screen Dimension: 608.1 x 348.9 mm

#### Resolution

2560 x 1440

#### Aspect Ratio

16:9

#### Pixel Pitch

0.2331 x 0.2331 mm

#### Dot / Pixel Per Inch

109 dpi

#### Brightness

350 cd/m<sup>2</sup>

#### Contrast Ratio

- Contrast Ratio (Typical): 1500:1
- Dynamic Contrast Ratio (Typical): 3000000:1

#### View Angle (H / V)

Horizontal: 178°, Vertical: 178°

#### Response Time

- Extreme Mode: 4ms GtG
- Normal Mode: 6ms GtG

#### Refresh Rate

100Hz

#### Color Gamut

Coverage Ratio: 99% sRGB (CIE 1931)

#### Color Support

16.7 Million

#### Color Depth

8-bit (6-bit+FRC)

#### Screen Surface Treatment

Anti-glare

#### Curvature

Flat Panel

### Operating System

#### Operating System

- Windows® 11 Support
- Windows® 10 Support

### Multi-Media

#### Speakers

Integrated Speakers, 2W x2

Power Supply

Power Consumption

- Typical / Max: 19.7W / 42W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 16.2W
- Energy Star TEC: 50.7kWh
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

Natural Low Blue Light

DESIGN

Mechanical

ThinkCentre® M Series Support

To support Tiny devices, an additional ThinkCentre® Tiny VESA Mount II (PN: 4XF0N03161) is required (sold separately).

Bezel Width

- Side: 1.8mm
- Top: 1.8mm
- Bottom: 20.5mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)<sup>[1]</sup>

| Models           | Dimensions                                            |
|------------------|-------------------------------------------------------|
| Lowest Position  | 613.1 x 220 x 383.5 mm (24.14 x 8.66 x 15.1 inches)   |
| Highest Position | 613.1 x 220 x 538.5 mm (24.14 x 8.66 x 21.2 inches)   |
| Head Only        | 613.1 x 40.4 x 366.4 mm (24.14 x 1.59 x 14.43 inches) |

Packaging Dimensions (WxDxH)

695.0 x 155.0 x 447.0 mm (27.36 x 6.10 x 17.60 inches)

Weight<sup>[2]</sup>

| Models             | Weight            |
|--------------------|-------------------|
| Monitor With Stand | 6.2 kg (13.7 lbs) |
| Monitor Head Only  | 4.0 kg (8.8 lbs)  |

Packaging Weight

- EPS: 7.9 kg (17.4 lbs)
- Pulp: 8.5 kg (18.7 lbs)

Mounting

Supports VESA mount 100 x 100 mm

Stand

Supports -5° to +22° tilt, left & right 360° swivel, -90° to +90° pivot, up to 155mm lift

In the Box

- Monitor with stand
- 1x HDMI® 2.0 cable (1.8m)
- 1x Power cable (1.8m)
- 4x Screws

- Quick setup guide

---

**Notes:**

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

## CONNECTIVITY

### Ports<sup>[1]</sup>

#### Rear Ports

- 2x HDMI® 2.1 TMDS, supports 2560x1440@100Hz
- 1x DisplayPort™ 1.2

---

**Notes:**

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

## SECURITY & PRIVACY

### Security

#### Physical Locks

Kensington® Security Slot™ (2.5 mm x 6 mm and 3 mm x 7 mm)

## SERVICE

### Warranty

#### Base Warranty

3-year limited warranty

## CERTIFICATIONS

### Green Certifications<sup>[1]</sup>

#### Green Certifications

- ENERGY STAR® Certified
- EPEAT™ Gold Registered
- EU Energy Label (E-class)
- TCO Certified 10.0
- TCO Edge 2.1

---

**Notes:**

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

### Other Certifications

#### Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

