OVERVIEW



1. Ethernet (2.5GbE RJ-45, for audio or video device) *	6. Power connector
2. Bring your Own Meeting (BYOM) connector *	7. 2x USB-C (USB 10Gbps)
3. HDMI-in *	8. HDMI-out 2.1 TMDS
4. 3x USB-A (USB 5Gbps), with BYOM	9. Ethernet (RJ-45)
5. USB-A (Hi-Speed USB), with IP Controller	10. HDMI-out 2.1 TMDS

Notes:

- Items with * are only available on selected models

PERFORMANCE

Compute Unit

Compute Unit[1]

Features	Information
Processor (Two Options)	(Optional 1) Intel® Core™ Ultra 5 135H, 14C (4P + 8E + 2LPE) / 18T, Max Turbo up to 4.6GHz, 18MB (Optional 2) Intel® Core™ Ultra 7 165H, 16C (6P + 8E + 2LPE) / 22T, Max Turbo up to 5.0GHz, 24MB
Operating System	Windows® 11 IoT Enterprise for Collaboration GAC 64
Graphics	Integrated Intel® Arc™ Graphics. Max Resolution: 3840x2160@60Hz(HDMI® 2.1 TMDS)
Chipset	Intel® SoC (System on Chip) platform
Memory (Two Options)	(Optional 1) 16GB (2x 8GB) DDR5 5600 SODIMM, Dual-Channel (Optional 2) 32GB (2x 16GB) DDR5 5600 SODIMM, Dual-Channel
Storage	One drive, 256GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0
Power Supply (Two Options)	(Optional 1) 135W 89% Adapter, autosensing, without BYOM (Optional 2) 170W 89% Adapter, autosensing, with BYOM
Onboard Ethernet	Gigabit Ethernet, Intel® Ethernet Connection I219-LM, 1x RJ45 (Optional) 2.5GbE, Realtek® RTL8125BGS-CG, 1x RJ-45
WLAN + Bluetooth®	Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, Intel® vPro® technology support, M.2 Card
Case Color	Black
Rear Ports	• 2x USB-C® (USB 10Gbps / 3.2 Gen 2), with 15W power supply and DisplayPort™ 1.4 • (Optional) 1x USB-C® in (USB 5Gbps / USB 3.2 Gen 1), with BYOM and 45W power supply • 3x USB-A (USB 5Gbps / USB 3.2 Gen 1) • 1x USB-A (Hi-Speed USB / USB 2.0), with IP controller • (Optional) 1x HDMI®-in • 2x HDMI®-out 2.1 TMDS • 1x Ethernet (RJ-45) • (Optional) 1x 2.5GbE Ethernet (RJ-45) • 1x Power connector
Dimension (WxDxH)	with cable management with rubber feet: 185 x 220 x 42.8 mm (7.28 x 8.66 x 1.69 inches) with cable management without rubber feet: 185 x 220 x 38 mm (7.28 x 8.66 x 1.5 inches) without cable management: 185 x 140 x 38 mm (7.28 x 5.51 x 1.5 inches)
Weight	with cable management: 1.01 kg (2.23 lbs) without cable management: 0.86 kg (1.90 lbs)
BIOS Security	• Supervisor password • Power-on password • Hard disk password
Security Chip	Discrete TPM 2.0, TCG certified
Physical Locks	Kensington® Security Slot™

Notes:

[1] Bring Your Own Meeting(BYOM) mode setting by BIOS setup or by ThinkSmart® Manager Portal

DESIGN

Mechanical

Component Options**

Product	Compute System	Controller	Audio Bar
ThinkSmart® Core Gen 2	1x ThinkSmart® Core Gen 2	-	-
ThinkSmart® Core Gen 2+CTRL	1x ThinkSmart® Core Gen 2	1x ThinkSmart® Controller	-

ThinkSmart® Core Gen 2+IPCTRL	1x ThinkSmart® Core Gen 2	1x Lenovo® IP Controller	-
ThinkSmart® Core Gen 2 FRK	1x ThinkSmart® Core Gen 2	1x ThinkSmart® Controller	1x ThinkSmart® Bar 180
ThinkSmart® Core Gen 2 IPFRK	1x ThinkSmart® Core Gen 2	1x Lenovo® IP Controller	1x ThinkSmart® Bar 180

Controller

ThinkSmart® Controller

Features	Information
Display	• 10.1" Display, 1920*1200 • 10-point touch • Up to 340 nits brightness • 16:10 aspect ratio • 30° and 60° rotatable • Anti-Fingerprint, Anti-Glare
Ports	• 1x USB-C® (connect to compute unit, 10m USB-C® cable incluided) • 1x Ultrasound Speaker
Security	Kensington® MiniSaver Security Slot
Dimension (WxDxH)	269.46 x 84.34 x 168.1 mm (10.61 × 3.32 × 6.62 inches)
Weight	811 g(1.79 lbs)

Lenovo® IP Controller

Features	Information
Display	• 10.1" Display, 1280x800 • 10-point touch • Up to 340 nits brightness • 16:10 aspect ratio • 30° and 60° rotatable • Anti-Fingerprint, Anti-Glare
Ports	• 1x Gigabit Ethernet (RJ-45) • 1x HDMI®-in • 1x Power Connector (on Link Box) • 1x Gigabit Ethernet (RJ-45, on Link Box) • 1x HDMI® out (on Link Box) • 1x USB-B (on Link Box)
Security	Kensington® MiniSaver Security Slot
Dimension (WxDxH)	248 x 151 x 100 mm (9.76 x 5.94 x 3.94 inches)
Weight	0.97 kg (2.16 lbs)

Audio Bar

ThinkSmart® Bar 180

Features	Information
Audio	• 4x Speaker (2x woofer, 2x tweeter) • Stereo audio out • 80 Hz to 20 KHz frequency range
Microphone	• 8x microphone beamforming array • -37dBFS sensitivity • 100 Hz to 8 KHz frequency range
Camera	• 3x Camera • Up to 3840 x 1080@30fps • 16:10 • 13 megapixels • Panoramic 4K • 180° Horizontal FoV, 54° Vertical FoV
Ports	• 1x USB-C® • 1x USB-A • 1x RJ 45

Dimension (WxDxH)	650 x 80 x 125 mm (25.6 x 3.1 x 4.9 inches)
Weight	2.2 kg (4.85 lbs)

MANAGEABILITY

System Management

System Management

Intel® vPro® Enterprise

SERVICE

Warranty[1]

Base Warranty

3-year limited onsite service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to https://smartfind.lenovo.com/. To learn more details of warranty policy, please access https://support.lenovo.com/warrantylookup/warrantypolicy.

ACCESSORIES

Bundled Accessories

Bundled Accessories***

- (Optional) External adapter cage
- (Optional) Lenovo® BYOM Cable for ThinkSmart® Core Gen 2 - USB-C® to USB-C® 3m
- (Optional) Lenovo® BYOM Cable for ThinkSmart® Core Gen 2 - USB-C® to USB-C® 5m (non-Display)
- (Optional) Removable cable management box
- (Optional) VESA mount bracket

CERTIFICATIONS

Other Certifications

Other Certifications

Microsoft® Teams Certification

SOFTWARE

Preinstalled Software

Preinstalled Software

Microsoft® Teams Rooms

- This is a telepresence technology product.
- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Feature with *** means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS", WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.









