



BUSINESS DEVICES THAT ARE A CLASS APART



The Lenovo V Series provides security, data protection and productivity features in an affordable package.

Lenovo V14 G3 IAP

Smarter
technology
for all

Lenovo

Designed for today's hybrid employees and students on the go, this 14" laptop comes packed with performance and portability features. Powered by 12th Gen Intel Core i7 processor, and with up to 12GB DDR4 memory support, users can perform a range of tasks without the device slowing them down. Multiple ports like USB-C 3.2, HDMI and USB 2.0 ensure users can transfer data, listen to audio, and connect to wired networks seamlessly.



REASONS TO BUY

Features like Dolby audio stereo speakers and dual-array microphone with intelligent noise-cancelling make digital meetings a breeze. Integrated Li-Polymer battery supports rapid Charge, so users can quickly get back to where they left, no matter where they are working from.

A slew of security features like power-on password, Kensington lock slot, camera privacy shutter and Firmware TPM 2.0 keep user data stays safe and encrypted.

This affordable laptop is ideal for basic productivity tasks, supporting smooth multitasking of browser windows and office applications.

Lenovo V14 G3 IAP

KEY SPECIFICATIONS

Processor	Up to 12th Gen Intel Core i7 processor
Operating System	Powered by Windows 11 Pro on select models
Display	14.0" screen, FHD (1920x1080), IPS, 300nits, anti-glare, 45% NTSC colour gamut 14.0" screen, FHD (1920x1080), TN, 250nits, anti-glare, 45% NTSC colour gamut
Graphics	Intel UHD Graphics or Intel Iris Xe Graphics in processor in select models
Memory	Up to 16GB DDR4-3200
Storage	Model with 45Wh battery: one drive, 1x M.2 SSD/Model with 38Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD
Audio	Stereo speakers, 1.5W x2, Dolby® Audio™, Dual array microphone with noise-cancelling
Battery†	Up to 5.8hrs (38Wh), up to 7.1hrs (45Wh)
Power Adapter	One of the following 65W Round Tip (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin)
Camera	720p with Privacy Shutter
Keyboard	6-row, spill-resistant, multimedia Fn keys
Dimensions	324.2 x 215.2 x 19.9 mm (12.76 x 8.47 x 0.78 inches)
Weight	Starting at 1.43 kg (3.15 lbs)

GREEN CERTIFICATIONS

EPEAT™ Silver, ENERGY STAR® 8.0, RoHS compliant

OTHER CERTIFICATIONS

TÜV Rheinland® Low Blue Light (Software Solution)

CONNECTIVITY

I/O Ports	1x USB 2.0, 1x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.2), 1x HDMI 1.4b, 1x Ethernet (RJ-45), 1x Headphone / microphone combo jack (3.5mm), 1x Power connector
WLAN + Bluetooth	One of the following 11ac, 2x2 + BT5.0 Wi-Fi 6 11ax, 2x2 + BT5.2

Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. † Based on testing with MobileMark 2014. Battery life varies significantly with settings, usage, and other factors. © 2020 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others.

Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.

SECURITY & PRIVACY

Firmware TPM 2.0 integrated in chipset, Kensington® Nano Security Slot, Camera privacy shutter

Recommended for this device



Lenovo 15.6” Laptop Casual Backpack

Modern design backpack with quick access pocket, crafted from water-repellent fabric

Dedicated, fully-padded PC compartment fits up to 15.6” laptops

Spacious main compartment for books and other items, and a range of internal pockets for accessories



Lenovo 400 Wireless Mouse

Ergonomic mouse designed for both right-hand and left-hand use, 2.4 GHz wireless connection

Comes with responsive and clear tracking with 1200 DPI resolution, up to 8 million clicks for left and right buttons

Lightweight for travel at 65g (2.29oz) with a battery that lasts up to 12 months



Warranty Extensions

Purchase additional warranty periods from 1 to 5 years

Buy at any point with or after your device purchase

Optional On-site Service