

OVERVIEW



1. Power button	6. USB-C 3.2 Gen 1
2. Volume button	7. USB 3.2 Gen 1
3. USB 3.2 Gen 1	8. Headphone / microphone combo jack (3.5mm)
4. HDMI 1.4b	9. MicroSD card reader
5. Kensington Nano Security Slot	10. Pen slot

Notes:

- Optional nano-SIM card slot on the rear side (not shown on the sample product above)

PERFORMANCE

Processor

Processor Family

AMD 3000 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
AMD 3015Ce	2	4	1.2GHz	2.3GHz	1MB L2 / 4MB L3	DDR4-1600	AMD Radeon™ Graphics

Operating System

Operating System

Google Chrome OS

Graphics

Graphics

Graphics	Type	Memory	Key Features
AMD Radeon Graphics	Integrated	Shared	DirectX® 12

Monitor Support

Monitor Support

Supports up to 3 independent displays (native display and 2 external monitors via HDMI® and USB-C)

- HDMI supports up to 4K@30Hz
- USB-C supports up to 4K@30Hz

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory^[1]

4GB soldered memory, not upgradable

Memory Slots

Memory soldered to systemboard, no slots

Memory Type^[2]

DDR4-1600

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.
2. Installed memory is actually 3200MHz but run at 1600MHz due to processor limitation

Storage

Storage Support^[1]

- 32GB eMMC 5.01 on systemboard
- 64GB eMMC 5.01 on systemboard

Storage Slot

eMMC on systemboard, no slots

Storage Type

Disk Type	Interface	Offering
Flash Memory	eMMC 5.01	32GB / 64GB

Notes:

- The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Optical

None

Card Reader

MicroSD card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® 5682I-CGT codec

Speakers

Stereo speakers, 2W x2

Microphone

Single microphone

Camera**

- Front 720p, with privacy shutter, fixed focus
- Front 720p, with privacy shutter, fixed focus; rear 5.0-megapixel, autofocus

Battery

Battery

Integrated Li-Polymer 47Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter

Max Battery Life^[1]

Google power load test: 10.8 hr

Notes:

- All battery life claims are approximate maximum and based on results using the MobileMark® 2014, MobileMark 2018, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter^[1]**

- 45W USB-C (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 45W USB-C (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

- AC adapter offerings depend on the country.

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
11.6"	HD (1366x768)	Multi-touch	IPS	250 nits	Glossy, anti-fingerprint	16:9	800:1	50% NTSC	170°	Corning® Gorilla® Glass

Touchscreen

GF2 or OGM (On-glass Metal mesh) Direct Bonding, capacitive-type multi-touch, supports 10-point touch

Notes:

- California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product.
For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Multi-mode

Multi-mode

Laptop, tent, stand, and tablet modes supported by 360° hinge

Input Device

Pen

- Lenovo USI Pen, on-board garaged and rechargeable
- No support

Keyboard

Chrome keyboard, 6-row, spill-resistant

Keyboard Backlight

Non-backlight

Touchpad

One-piece multi-touch touchpad, 60.5 x 104 mm (2.38 x 4.09 inches)

Mechanical^[1]

Dimensions (WxDxH)

289.6 x 202.4 x 19.9 mm (11.4 x 7.97 x 0.78 inches)

Weight

Starting at 1.33 kg (2.93 lbs)

Case Color

Grey

Surface Treatment

Texture

Case Material

PC + ABS covered with rubber bumper (top), PC + ABS (bottom)

Others

Buttons: power key, volume key

Notes:

- The system dimensions and weight vary depending on configurations.

CONNECTIVITY

Network

Onboard Ethernet

No Ethernet

WLAN + Bluetooth^[1]

Realtek RTL8822CE, 802.11ac Dual Band 2x2 Wi-Fi® + Bluetooth 5.0, M.2 card

WWAN

- Integrated Mobile Broadband 4G LTE-A, CAT9, Fibocom L850-GL, M.2 card
- No support

SIM Card

No SIM card inbox

Notes:

- Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.4)
- 1x HDMI 1.4b
- 1x microSD card reader
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports

1x Nano-SIM card slot (WWAN support models)

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
 - USB 2.0: 480 Mbit/s;
 - USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
 - USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
 - USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
 - Thunderbolt™ 3/4: 40 Gbit/s;
 - FireWire 400: 400 Mbit/s;
 - FireWire 800: 800 Mbit/s

SECURITY & PRIVACY

Security

Security Chip

Google Security Chip H1

Physical Locks

Kensington® Nano Security Slot

Fingerprint Reader

No fingerprint reader

BIOS Security

No support

Other Security

Camera privacy shutter

SERVICE

Warranty

Base Warranty**^[1]

- 1-year mail-in service
- 1-year depot service
- 1-year depot with 2-year system board service (Korea only)
- 2-year (1-yr battery) depot service

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: 5°C (41°F) to 43°C (109°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

CERTIFICATIONS

Green Certifications

Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified
- RoHS compliant

Other Certifications


Mil-Spec Test

MIL-STD-810H military test passed

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



AMD



AMD



AMD



AMD



AMD



AMD