



LENOVO DEVICES THAT ARE A CLASS APART

Lenovo 14e Chromebook Gen 3

Smarter technology for all



With an aluminum top cover, a superfast Intel Core i3 N-series processor and Intel UHD Graphics, the Lenovo 14e Chromebook Gen 3 delivers a quantum leap in both performance and aesthetics. Its up to 8GB memory and up to 128GB eMMC storage support boosts system performance and enables users to handle massive workloads with ease. The 14" device also features all the essential peripherals including, 2x USB 3.2 Gen 1 ports, HDMI 1.4 and Intel Wi-Fi 6E to keep your productivity powered on.



REASONS TO BUY

- The full HD (1920x1080) resolution, 16:9 aspect ratio and up to 100% sRGB color gamut offers a full majesty of color accuracy and ultra-crisp image quality. An optional multi-touch screen also makes it easier to navigate and browse through your favorite films, videos and TV shows.
- The Chromebook is loaded with multi-media features such as HD audio chip, 2Wx2 stereo speakers optimized with Waves MaxxAudio, dual-array microphone and 1080p FHD camera with privacy shutter to enhance web conferencing experience.

The 12.7" screen dimension and 1.45 kg (3.2lb) weight makes it ideal to fit into a workspace of any size.

Purpose-built for modern education. Robust, secure, and easy to manage, our laptops offer versatile performance and collaboration tools to support teachers and students in the classroom or at home.

Lenovo 14e Chromebook Gen 3

KEY SPECIFICATIONS

Processor	Intel N-series or Intel Core i3 N-series
Operating System	ChromeOS
Display	14.0", HD (1366x768), TN, Anti-glare display, 16:9 Aspect Ratio - 250nits Brightness, 45% NTSC Color Gamut 14.0", FHD (1920x1080), IPS, Anti-glare display, 16:9 Aspect Ratio - 300nits Brightness, 100% sRGB Color Gamut, touch - 300nits Brightness, 45% NTSC Color Gamut
Touchscreen	Optional Multi-touch
Graphics	Intel UHD Graphics (integrated)
Memory	4GB LPDDR5-4800, soldered 8GB LPDDR5-4800, soldered
Storage	1. 32GB eMMC 5.1 on systemboard 2. 64GB eMMC 5.1 on systemboard 3. 128GB eMMC 5.1 on systemboard
Audio	High Definition (HD) Audio, Realtek ALC5682I codec 2W x2 Stereo speakers, optimized with Waves MaxxAudio Dual- array microphone
Battery†	57Wh battery (up to 14 hr) Rapid Charge with 65W AC adapter
Power Adapter	One of the following 45W USB-C (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin)
Camera	One of the following FHD 1080p with Privacy Shutter HD 720p with Privacy Shutter
Keyboard	Chrome keyboard, 6-row, spill-resistant, Anti-pick proof keycaps with full skirt design Optional backlight Mylar surface touchpad- 60.5 x 104 mm (2.38 x 4.09 inches)
Dimensions	324.4 x 216.2 x 16.9 mm (12.77 x 8.51 x 0.67 inches)
Weight	N100 / N200 models: Around 1.45 kg (3.2 lb)

GREEN CERTIFICATIONS

EPEAT Gold, ENERGY STAR 8.0, ErP Lot 6, ErP Lot 26, TCO Certified 9.0, RoHS compliant

OTHER CERTIFICATIONS

MIL-STD-810H military tested

Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. † Based on testing with MobileMark 2014. Battery life varies significantly with settings, usage, and other factors. © 2023 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.

CONNECTIVITY

I/O Ports	2x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 2, 1x HDMI 1.4, 1x Headphone / microphone combo jack (3.5mm)
WLAN + Bluetooth	Intel Wi-Fi 6E AX211, 11ax 2x2 + BT5.1

SECURITY & PRIVACY

Google Security Chip H1

Camera privacy shutter
Kensington Nano Security Slot

Recommended for this device



ThinkPad Bluetooth Silent Mouse

Left/Right hand, easy-to-carry low profile mouse
Switch between 2 devices with dual-host Bluetooth 5.0 connectivity

2-way scrolling with on-the-fly DPI adjustment (2400, 1600, 800)



Thinkpad Universal USB-C Smart Dock

Access to multiple 4K monitors, and blazing-fast data transfers with USB-C and USB-A

Supports both Thunderbolt™ 3 and 4, USB 4™ and USB-C, and extended compatibility with a wide range of brands and Multi-OS notebooks

11+ expansion possibilities in a single quick-release cable for maximum efficiency



On-site Service

If a problem can't be fixed remotely, we will visit your location

Normally next business day service

Agreed appointment times