

Lenovo 100w Gen 4

Powered by an Intel N100 processor and Intel UHD Graphics, this laptop lets professionals annotate documents and collaborate virtually. It comes with a 47Wh integrated Li-Polymer battery that supports rapid charge, enabling users to work from anywhere without any hassle. Plus, ports including dual USB 3.2 Gen1, USB-C 3.2 Gen1, HDMI, and a 3.5-mm headphone or microphone combo jack allow users to connect to peripherals or plug-in headphones for listening to meetings on the go.



Configured with up to 128GB SSD storage and up to 8GB LPDDR5 memory, this device enables multitasking productivity helping professionals with faster retrieval of memory-intensive spreadsheets and at the same time improving the overall system responsiveness.

The dual 2W stereo speaker with a single microphone ensures clear sound quality allowing professionals to virtually collaborate with teams more effectively.

Powered by an Intel N100 processor and Intel UHD Graphics, this laptop lets professionals run memory-intensive applications faster.

Lenovo devices that are a class apart

Lenovo Mini Series offers smaller notebooks for users with basic computing needs like email and web browsing.

Lenovo services

Lenovo offers a comprehensive portfolio of end-to-end services to support and protect your investment - so you can focus on learning, not IT.



Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center
 Lenovo pays for all shipping between the customer and service facility
 Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Eco Pro 15.6" Backpack

Eco-friendly design – contains over 83% recycled material
 The equivalent of 34 plastic water bottles are turned into soft polyester to make each backpack
 Convenient large storage area and quick access accessory pockets



PN: 4X40Z32891

Thinkpad Essential 16" Backpack (Eco)

Two internal compartments (one for notebooks up to 16"), two front zipper pockets, and one side mesh water bottle sleeve that ensure you'll never run out of space.
 A padded top handle. And a rear luggage strap.
 Every feature is crafted for convenience and comfort.
 Elegant black nylon exterior, grey interior lining, and a splash of red accents.



PN: 4X41C12468

Lenovo 100w Gen 4

Key Specifications

Processor

Intel N Series

Operating System

Windows 11 Pro, Windows 11 Pro (National Academic License), Windows 11 Home, Windows 11 Home Single Language, Windows 11 SE, Windows 11 DG Windows 10 Pro 64, Windows 11 DG Windows 10 Pro 64(National Academic License)

Display

11.6" HD (1366x768) TN Anti-glare 16:9 - 250nits, 45% NTSC

Touchscreen

Non-touch

Graphics

Intel UHD Graphics (integrated)

Memory

4GB LPDDR5-4800, soldered
8GB LPDDR5-4800, soldered

Storage

UFS model:
128GB UFS 3.1 on systemboard

SSD model:

One drive, 128GB M.2 2242 SSD

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2
Single microphone

Battery[†]

47Wh battery (up to 12.3 hr)Rapid Charge

Power Adapter

One of the following
45W USB-C (2-pin)
45W USB-C (3-pin)
65W USB-C (2-pin)
65W USB-C (3-pin)

Camera

HD 720p

Keyboard

Top-load keyboard, 6-row, spill-resistant,
Anti-pick proof keycaps with full skirt design
Mylar surface touchpad
60.5 x 104 mm (2.38 x 4.09 inches)

Dimensions

287 x 200 x 19.75 mm (11.3 x 7.9 x 0.78 inches)

Weight

Starting at 1.16 kg (2.56 lbs)

Green Certifications

ENERGY STAR 8.0, ErP Lot 6, ErP Lot 26, EPEAT Gold, TCO Certified 9.0, RoHS compliant

Other Certifications

MIL-STD-810H military test passed (23 test items)

Connectivity

I/O Ports

1x HDMI 1.4, 1x USB 3.2 Gen 1 (Always On), 1x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 2 (data, PD, DP), 1x Headphone / microphone combo jack (3.5mm)

WLAN + Bluetooth

Intel Wi-Fi 6 AX201, 11ax 2x2 + BT5.1

Security & Privacy

Discrete TPM 2.0, TCG certified
Kensington Nano Security Slot
Camera privacy shutter