

OVERVIEW



1. Joystick	5. HDMI
2. Source Key	6. VGA
3. Kensington Security Slot	7. Audio line-out (3.5mm)
4. Power connector	

PERFORMANCE

Panel

Panel
3-side NearEdgeless, VA

Backlight
WLED

Display Size
21.45 inches

Max View Area
WxH: 478.7 x 260.3 mm

Resolution
1920 x 1080

Aspect Ratio
16:9

Pixel Pitch
0.249 x 0.241 mm

Dot / Pixel Per Inch
103 dpi

Brightness
250 nits

Contrast Ratio

- Contrast Ratio: 3000:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)
Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms
- Off Mode: 14 ms

Refresh Rate
75Hz (HDMI® only)

Color Gamut
72% NTSC

Color Support
16.7 Million

Color Depth
8-bit

Anti-glare
Support

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Power Supply

Power Consumption

- Typical / Max: 15W / 20W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- Natural Low Blue Light
- Lenovo® Artery (Lenovo Display Control Center) Support
Lenovo Artery can only be used with Windows 10 & Windows 11
- AMD FreeSync™
AMD FreeSync technology only can work with AMD Radeon™ series graphics card.

DESIGN

Mechanical

ThinkCentre® M Series Support

ThinkCentre M Series Tiny, ThinkCentre M Series Nano
For supporting Tiny / Nano devices, additional Tiny / Nano VESA Mount Kits (PN: 4XFON03161) / (PN: 4XFOV81630) are needed (sold separately).

Bezel Width

- Side: 1.5mm
- Top / Bottom: 1.5mm / 22mm

Cable Management

Support

Case Color

Cloud grey

Dimensions (WxDxH)^[1]

Models	Dimensions
Highest Position	491.6 x 182.8 x 401.6 mm (19.35 x 7.19 x 15.81 inches)
Lowest Position	491.6 x 182.8 x 401.6 mm (19.35 x 7.19 x 15.81 inches)
Unpacked Head Only	491.6 x 290.3 x 41.0 mm (19.35 x 1.61 x 11.43 inches)

Packaging Dimensions (WxDxH)

588 x 117 x 353 mm (23.15 x 4.61 x 13.90 inches)

Weight^[2]

Models	Weight
Monitor With Stand	3.1 kg (6.8 lbs)
Monitor Head Only	2.2 kg (4.9 lbs)

Packaging Weight

4.2 kg (9.26 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +22° tilt

In the Box

- Monitor with Stand
- 1x Power cable (1.8m)
- 1x HDMI cable (1.8m)
- 1x Screw
- Quick Setup Guide
- Warranty Booklet

Notes:

- 1 . The system dimensions may vary depending on configurations.
- 2 . The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight

for each specific model.

CONNECTIVITY

Ports

Rear Ports

- 1x HDMI 1.4
- 1x VGA
- 1x audio-out (3.5mm)

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™ (2.5 mm x 6 mm)

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 3-year courier or carry-in service

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

RoHS (2011/65/EU)

Notes:

1. The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

