

OVERVIEW



1. Kensington Security Slot	8. DisplayPort out
2. Power connector	9. Ethernet (RJ-45)
3. HDMI 2.0	10. USB 3.2 Gen 1
4. HDMI 2.0	11. USB 3.2 Gen 1
5. DisplayPort 1.2	12. Audio-out (3.5mm)
6. 1x USB-C 3.2 Gen 1 (DP 1.2 Alt Mode)	13. USB-C 3.2 Gen 1
7. USB-B 3.2 Gen 1	14. USB 3.2 Gen 1

PERFORMANCE

Panel

Panel

3-side NearEdgeless, In-Plane Switching

Backlight

WLED

Display Size

34.14 inches

Max View Area

WxH: 799.8 x 334.8 mm

Resolution

3440 x 1440

Aspect Ratio

21:9

Pixel Pitch

0.2325 x 0.2325 mm

Dot / Pixel Per Inch

109 dpi

Brightness

300 cd/m²

Contrast Ratio

- Dynamic Contrast Ratio: 3000000:1
- Contrast Ratio: 1000:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

Refresh Rate

60Hz

Color Gamut

99% sRGB

Color Support

1.07 Billion

Color Depth

10-bit (8-bit+FRC)

Screen Surface Treatment

Anti-glare

Curvature

3800R

Operating System

Operating System

- Windows® 11 Support
- Windows® 10 Support

Multi-Media

Camera

- No bundled webcam (Support ThinkVision® MC 50 Monitor Webcam, sold separately)
- ThinkVision® MC 50 monitor webcam (Some models only)

Microphone

- Built-in dual microphone in MC 50 (Models with MC 50 only)
- No microphone

Speakers

Integrated Speakers, 2x 3W

Power Supply

Power Consumption

- Typical / Max: 36W / 230W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 30W
- Energy Star TEC: 93kWh
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- HDR Compliance
- Factory Calibration: Avg. Delta E<2
- Picture In Picture (PIP) / Picture By Picture (PBP) Support
- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support
Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- DaisyChain Support (DP out)
- KVM Switch
- Smart Power
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

DESIGN

Mechanical

ThinkCentre® M Series Support

ThinkCentre® M Series Tiny, ThinkCentre® M Series Nano

For supporting Tiny devices, additional Tiny Monitor Clamp II (PN: 4XH0Z42451) are needed (sold separately).

For supporting Nano devices, additional Nano Monitor Clamp II (PN: 4XH0Z42451) are needed (sold separately).

Bezel Width

- Side: 9.5mm
- Top / Bottom: 9.5mm / 28.4mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	817.3 x 245.0 x 469.3 mm (32.18 x 9.65 x 18.48 inches)
Highest Position	817.3 x 245.0 x 621.4 mm (32.18 x 9.65 x 24.46 inches)
Head Only	817.3 x 76.8 x 372.7 mm (32.18 x 3.02 x 14.67 inches)

Packaging Dimensions (WxDxH)

937 x 220 x 475 mm (36.89 x 8.66 x 18.70 inches)

Weight^[2]

Models	Weight
Monitor With Stand	10.8 kg (23.81 lbs)

Monitor Head Only	7.4 kg (16.31 lbs)
-------------------	--------------------

Packaging Weight

15.5 kg (34.17 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +35° tilt, left & right 45 swivel, up to 150mm lift

In the Box

- Monitor with Stand
- 1x DP Cable (1.8m) (NA only)
- 1x USB-B to USB-A Cable (1.8m) (NA only)
- 1x USB-C® to USB-A Cable (1.8m) (NA only)
- 1x USB-C® to USB-C® Cable (1.8m)
- 1x Power Cable (1.8m)
- Factory Calibration Report
- Quick Setup Guide

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

Support 10M / 100M / 1000M

Ports^[1]**Rear Ports^[2]**

- 1x USB-C® 3.2 Gen 1 (DP 1.2 Alt Mode and up to 100W PD), USB upstream
- 1x USB-C® 3.2 Gen 1, USB downstream
- 1x USB-B 3.2 Gen 1, USB upstream
- 3x USB 3.2 Gen 1, USB downstream
- 2x HDMI® 2.0
- 1x DisplayPort™ 1.2
- 1x DisplayPort™ out
- 1x Ethernet (RJ-45)
- 1x Power Connector
- 1x audio-out (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

[2] Up to 100W power delivery to compatible devices by USB-C®. Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ENERGY STAR® Certified
- EPEAT™ Gold Registered^[2]
- EU Energy Label (F-class)
- RoHS compliant
- TCO Certified 9.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ is registered where applicable, please visit epeat.net for registration status by country.

Other Certifications

Other Certifications

- Eyesafe® Certified
 - TÜV Rheinland® Eye Comfort Certification
 - TÜV Rheinland® Flicker Free
 - TÜV Rheinland® Low Blue Light
 - TÜV Rheinland® Low Blue Light (Hardware Solution)
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

