



Poly Zoom Room Intelligent Director Camera Kit Studio E70x3 Camera (ABA) (9J688AA)

Overview

Stay engaged in every conversation

Experience truly inclusive meetings with a ready-to-deploy solution certified for Zoom Intelligent Director, offering AI-enhanced in-room views that capture perfect angles, ensuring everyone feels part of the conversation [1].

AI-enhanced Zoom meetings

Poly Studio Solution for Zoom Rooms gives you everything you need to activate enhanced camera framing and zooming with Zoom Intelligent Director AI-driven tech. Meetings stay productive with technology that empowers the whole team, wherever they work [1].

Peace of mind you can call on

Our Poly+ device support team is available 24/7, across the world. This extensive global network of support professionals help you confidently plan and successfully deploy Zoom Rooms [2,3].

Skip the configuration

Certified and built for Zoom Rooms, this cutting-edge meeting room solution offers a consistent user experience and are simple for IT to setup [1].

Features

Smart + intuitive meetings

Zoom Intelligent Director uses AI-driven tech to choose the best view of in-room participants from three Poly cameras, enhancing video clarity and resolution. This provides the best experience for all attendees, ensuring everyone feels connected.^[4]

Effortless meeting setup

With the Poly Studio Solution for Zoom Rooms enjoy seamless meetings with a ready-to-deploy setup featuring a powerful HP PC, three Poly Studio E70 cameras and a Poly TC10 controller, all certified for Zoom Rooms Intelligent Director.^[1,5,6]

Crystal clear video

Experience lifelike clarity in your large meeting rooms with an intelligently built camera made for connecting hybrid teams. And with the dual camera, 20-megapixel 4K sensors, – everyone is seen in sharp detail.

[1] Poly Studio E70 camera kit for Zoom Intelligent Director includes three Poly Studio E70 cameras with power supplies. Required and sold separately for the complete Poly Studio Solution for Zoom Rooms solution are the following: Poly Base Room Kit for Zoom Rooms, which includes a Poly TC10 touch control panel and HP Mini Conferencing PC with Zoom Rooms; a Poly Trio C60 conference phone is available for audio, or room Digital Signal Processor (DSP) can be connected to the Collaboration PC; and a Zoom Rooms license.

[2] Customers can contact Poly to receive 24x7 priority support for the Customer's supported solution. Regional telephone numbers to contact Poly can be found at: <https://www.poly.com/us/en/support/contact/support-phone-numbers>. Support is available via chat, phone, web and video. Poly support can be reached at the following link: <https://www.poly.com/support>.

[3] Complete Zoom Room requires audio and video, not included in the Poly Studio Base Room Kit.

[4] Zoom Intelligent Director is a feature available on Zoom Rooms app on Windows running on the HP Mini Conferencing PC with Zoom Rooms and the Poly Studio E70 cameras included in the Poly Studio E70 camera kit for Zoom Intelligent Director.

[5] HP Mini Conferencing PC with Zoom Rooms. Zoom Rooms license not included, sold separately.

[6] Zoom Rooms license not included, sold separately.

Additional specifications

Bundle components	842F8AA, 875K6AA, 874T5AA
Camera range (imperial)	Up to 25 ft
Camera range (metric)	Up to 7.62 m
Camera resolution	2160p, 4K UHD (3840 x 2160)
Camera type	Dual-lens
Color	White
Diagonal field of view (dFoV)	78°; 140°
Horizontal field of view (hFoV)	120°; 70°
Lens cover capabilities	Integrated
Management Software	Poly Lens
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	321 x 102 x 89.1 mm <i>(for each Studio E70 camera)</i>
Minimum dimensions (W x D x H)	12.63 x 4.02 x 3.51 in <i>(for each Studio E70 camera)</i>
Minimum order quantity	1
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-40 to 70 °C
Non-operating temperature - fahrenheit	40 to 158 °F
Operating altitude	4,877 m
Operating altitude	16,000 ft
Operating humidity range	15 to 80%
Operating temperature range	32 to 104 °F
Operating temperature range	0 to 40 °C
Package dimensions (W x D x H)	550 x 210 x 23.5 mm
Package dimensions (W x D x H)	21.65 x 8.26 x 9.25 in
Package weight	9.6 kg
Package weight	21.16 lb
Pallet weight	357 kg
Pallet weight	787.05 lb
Ports	1 USB Type-C® 5Gbps signaling rate; 1 RJ-45
Power	100 - 240 VAC 50/60 Hz, 1.5A input; 12 VDC, 5A, 60 W output; Power over Ethernet (PoE), compatible with IEEE 802.3af Class 4

Power adapter port	1 x 4.5 mm
Power supply type	External
Smart camera technology	Poly DirectorAI with speaker framing; People framing; Group framing; Presenter tracking; DirectorAI perimeter
Special features	Air Quality Sensor; Meeting participant counting; Electronic privacy shutter
Total camera resolution (megapixels)	2 x 20 MP
UNSPSC code	45111902
Weight	2 lb <i>(for each Studio E70 camera)</i>
Weight	907 g <i>(for each Studio E70 camera)</i>
What's in the box	3 Poly Studio E70; 3 AC power adapter; 3 power cable; 3 USB Type-C® cable; 3 Ethernet cable; 3 Wall mount kit
Zoom capability	7.3x digital

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 16, 2024 12:05 PM UTC+0000