

Product data sheet

Specifications



Line-R 1200VA Automatic Voltage Regulator

LE1200

⚠ To be discontinued on: Aug 6, 2024

⚠ To be discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Product or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	120 V
Kw Rating	1200 W
Rated power in VA	1200 VA
Input Connection Type	NEMA 5-15P
Cable length	6.5 ft (2.0 m)
Number of cables	1
Provided equipment	User Manual

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0

Physical

Color	Beige
Height	4.6 in (11.6 cm)
Width	8.4 in (21.4 cm)
Depth	5.6 in (14.1 cm)
Net Weight	9.7 lb(US) (4.4 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Input Frequency	50/60 Hz
-----------------	----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Output

Max Configurable Power (Watts)	1200 W
--------------------------------	--------

Conformance

Product Certifications	cUL Listed NOM
Standards	FCC Part 15 class B UL 1012
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient Air Temperature for Operation	32.0000000000...104.0000000000 °F (0...40 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13.0000000000...149.0000000000 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

Surge energy rating	680 J
---------------------	-------

Ordering and shipping details

GTIN	731304197911
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.9 in (17.5 cm)
Package 1 Width	8.1 in (20.7 cm)
Package 1 Length	10.7 in (27.3 cm)
Package 1 Weight	10.4 lb(US) (4.7 kg)
SCC14	10731304197918

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.


Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65 WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
