

Manual Supplement

Manual Title:	323/324/325 Calibration	Supplement Issue:	3
Part Number:	Web-Only	Issue Date:	1/22
Print Date:	February 2013	Page Count:	2
Revision/Date:			

This supplement contains information necessary to ensure the accuracy of the above manual.

Change #1, 66148

On page 6, under **EMI, EMC** add the following:

Electromagnetic Compatibility Applies to use in Korea only. Class A Equipment (Industrial Broadcasting & Communication Equipment) ^[1]

[1] This product meets requirements for industrial (Class A) electromagnetic wave equipment and the seller or user should take notice of it. This equipment is intended for use in business environments and is not to be used in homes.

Change #2

On page 13, Table 4, replace the Frequency section with:

Frequency	0.2 A, 5 Hz	N/A	N/A	X	4.6 Hz	5.4 Hz
	0.2 A, 50 Hz	N/A	N/A	X	49.6 Hz	50.4 Hz
	0.2 A, 500 Hz	N/A	N/A	X	497.1 Hz	502.9 Hz

On page 14, Table 4, replace the AC Amps (with 50-Turn Coli) section with:

Test (Switch Position)	Calibrator Output	323	324	325	Meter Reading Limit	
					Low	High
AC Amps (with 50-Turn Coil)	0.12 A @ 50 Hz	X	N/A	N/A	5.4 A	6.6 A
	0.48 A @ 150 Hz	X	N/A	N/A	22.9 A	25.1A
	4.2 A @ 50Hz	X	N/A	N/A	205.3 A	214.7 A
	7.8 A @ 50 Hz	X	N/A	N/A	381.7 A	398.3 A
	7.8 A @ 150 Hz	X	N/A	N/A	379.7 A	400.3 A
	7.8 A @ 400 Hz	X	N/A	N/A	379.7 A	400.3 A
	0.004 A @ 50 Hz	N/A	X	N/A	0.15 A	0.25 A
	0.2 A @ 50 Hz	N/A	X	N/A	9.80 A	10.20 A
	0.6 A @ 50 Hz	N/A	X	N/A	29.50 A	30.50 A
	2 A @ 50 Hz	N/A	X	N/A	98.0 A	102.0 A
	6 A @ 50 Hz	N/A	X	N/A	295.0 A	305.0 A
	0.2 A @ 50 Hz	N/A	N/A	X	9.75 A	10.25 A
	0.6 A @ 50 Hz	N/A	N/A	X	29.35 A	30.65 A
	2 A @ 50 Hz	N/A	N/A	X	97.5 A	102.5 A
	6 A @ 50 Hz	N/A	N/A	X	293.5	306.5 A

Change #3

On page 13, Table 4, in the Ohms section, change the bottom two rows:

From:

10K Ω	N/A	X	X	9.85 K Ω	10.15 K Ω
30K Ω	N/A	X	X	34.65 K Ω	30.35 Ω

To:

10K Ω	N/A	N/A	X	9.85 K Ω	10.15 K Ω
30K Ω	N/A	N/A	X	34.65 K Ω	30.35 Ω