

OVERVIEW



1. Power Connector	4. DP 1.4
2. HDMI 2.0	5. Audio line-out (3.5mm)
3. HDMI 2.0	

PERFORMANCE

Panel

Panel

3-side NearEdgeless, VA

Display Size

27 inches

Max View Area

WxH: 597.9 x 336.3 mm

Resolution

1920 x 1080

Aspect Ratio

16:9

Pixel Pitch

0.311 x 0.311 mm

Dot / Pixel Per Inch

82 dpi

Brightness

350 nits

Contrast Ratio

- Contrast Ratio: 3000:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Moving Picture Response Time (MPRT): 1 ms
- Level 1: 7 ms
- Level 2: 6 ms
- Level 3: 5 ms
- Level 4: 4 ms
- Moving Picture Response Time (MPRT) improves the response time and reduces motion blur in the monitor. Enabling MPRT will disable AMD FreeSync™ technology, and may causes a negligible flicker.

Refresh Rate

165 Hz

Color Gamut

- 99% sRGB, 90% DCI-P3
- 123% sRGB, 93% DCI-P3

Color Support

16.7 Million

Color Depth

8-bit

Anti-glare

Support

Curvature

1500R

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Multi-Media

Speakers

Integrated Speakers, 2x 3W

Power Supply

Power Consumption

- Typical / Max: 22W / 49W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- Processor LUT: 8 bit
- HDR Compliance
- Natural Low Blue Light
- Lenovo® Artery (Lenovo Display Control Center) Support
Lenovo Artery can only be used with Windows 10 & Windows 11
- AMD FreeSync Premium
AMD FreeSync technology only can work with AMD Radeon™ series graphics card.

DESIGN

Mechanical

ThinkCentre® M Series Support

None

Bezel Width

- Side: 2mm
- Top / Bottom: 2mm / 24mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Highest Position	610.4 x 239.2 x 528.9 mm (24.03 x 9.42 x 20.82 inches)
Lowest Position	610.4 x 239.2 x 394.3 mm (24.03 x 9.42 x 15.52 inches)
Head Only	610.4 x 88.2 x 369.8 mm (24.03 x 3.47 x 14.56 inches)

Packaging Dimensions (WxDxH)

789 x 162 x 463 mm (31.06 x 6.38 x 18.23 inches)

Weight^[2]

Models	Weight
Monitor With Stand	6.1 kg (13.4 lbs)
Monitor Head Only	4.2 kg (9.3 lbs)

Packaging Weight

8.0 kg (17.6 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +22° tilt, up to 135mm lift

In the Box

- Monitor with Stand
- 1x Power cable (1.8m)
- 1x DP Cable (1.8m)
- 4x Screws
- Quick Setup Guide
- Warranty Booklet

Notes:

1. The system dimensions vary depending on configurations.
2. The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports

Rear Ports

- 2x HDMI® 2.0
- 1x DisplayPort™ 1.4
- 1x audio-out (3.5mm)
- 1x Power Connector

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

- 1-year courier or carry-in service
- 3-year courier or carry-in service

CERTIFICATIONS

Green Certifications

Green Certifications

- Volatile Organic Compound Certification
- RoHS compliant

Other Certifications

Other Certifications

- Eyesafe® Certified
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.



- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

