

Lenovo 300e Yoga Chromebook Gen 4

Powered by MediaTek Kompanio 520 processor, this lightweight, convertible device is purpose-built with the versatility to help professionals annotate documents and collaborate easily. It comes with up to 16 hours of battery life enabling users to work from anywhere without any hassle. Plus, dual USB 3.2 Gen1, USB-C 3.2 Gen1, HDMI, and a 3.5-mm headphone or microphone combo jack allow users to connect to peripherals or plug-in headphones for listening to meetings on the go.



The 11.6-inch multi-touch display provides a rich visual experience while its 360-degree hinge allows for a seamless transition between use modes for reading, content creation, or presentations. Additionally, with optional Lenovo USI pen navigate through documents easily.

Configured with up to 64GB SSD storage and up to 8GB LPDDR4 memory, this device enables multitasking productivity helping professionals with faster retrieval of detailed spreadsheets.

Lenovo devices that are a class apart

Purpose-built for modern education. Robust, secure, and easy to manage, our laptops offer versatile performance and collaboration tools to support teachers and students in the classroom or at home.

Lenovo services

Lenovo offers a comprehensive portfolio of end-to-end services to support and protect your investment - so you can focus on learning, not IT.



Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center
 Lenovo pays for all shipping between the customer and service facility
 Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Essential Compact Wireless Mouse

Compact and easy to carry, weighs just under 50g (1.76oz)
 Ergonomic and ambidextrous design with 3 buttons
 Highly durable design, tested to last up to 8 million clicks



PN: 4Y50R20864 – (with battery) 4Y50R20865 – (w/o battery)

Lenovo Go Wireless Numeric Keypad

21-key numeric keypad with industry-leading scissor switch keys
 Minimalist design with ultra slim profile at 13 mm with dedicated productivity keys (Calculator, Tab, Equal, Esc keys)
 Rechargeable , up to 3 months use in single charge (may vary based on usage)



PN: 4Y41C33791, 4Y41C33979

Lenovo 300e Yoga Chromebook Gen 4

Key Specifications

Processor

MediaTek Kompanio 520

Operating System

ChromeOS

Display

11.6" HD (1366x768), IPS, glossy, 16:9 - 250nits, 50% NTSC, Anti-fingerprint, Corning Gorilla Glass, touch

Touchscreen

11.6" HD (1366x768), IPS, glossy, 16:9 - 250nits, 50% NTSC, Anti-fingerprint, Corning Gorilla Glass, touch

Graphics

ARM Mali-G52 2EE MC2 GPU (integrated)

Memory

4GB LPDDR4x-3733, soldered

8GB LPDDR4x-3600, soldered

Storage

32GB eMMC 5.1 on systemboard

64GB eMMC 5.1 on systemboard

Audio

High Definition (HD) Audio

Stereo speakers, 2W x2, optimized with Waves MaxxAudio

Single microphone or two microphones

Battery†

47Wh battery (up to 19.36 hr) Rapid Charge with 65W AC adapter

Power Adapter

One of the following

45W USB-C (2-pin)

45W USB-C (3-pin)

65W USB-C (2-pin)

65W USB-C (3-pin)

Camera

One of the following

Front HD 720p with Privacy Shutter

Front HD 720p with Privacy Shutter + Rear 5.0MP

Keyboard

Chrome keyboard, 6-row, spill-resistant,

Anti-pick proof keycaps with full skirt design

Mylar surface touchpad

60.5 x 104 mm (2.38 x 4.09 inches)

Dimensions

287 x 200 x 18.6 mm (11.3 x 7.9 x 0.73 inches)

Weight

1.33 kg (2.93 lbs)

Green Certifications

ENERGY STAR 8.0, ErP Lot 6, ErP Lot 26, EPEAT Gold, TCO Certified 9.0, RoHS compliant

Other Certifications

ENERGY STAR 8.0, ErP Lot 6, ErP Lot 26, EPEAT Gold, TCO Certified 9.0, RoHS compliant

Connectivity

I/O Ports

2x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 1 (data, PD, DP), 1x HDMI 1.4b, 1x Headphone / microphone combo jack (3.5mm)

WLAN + Bluetooth

Mediatek Wi-Fi 6 MT7921, 11ax 2x2 + BT5.1

Security & Privacy

Google Security Chip H1, Camera privacy shutter, Kensington Nano Security Slot