


HP Z24u G3 WUXGA USB-C Display

Exquisitely crafted for every detail

Meticulously crafted to surpass every design standard, the HP Z24u G3 WUXGA USB-C Display is composed of authentic aluminum and delivers an impressive, frameless viewing experience. Bring your ideas to life with remarkable color accuracy in precise WUXGA resolution. Refine your work experience and transform your PC into a powerhouse with this 24 inch diagonal screen monitor with USB-C 100W Power Delivery.



*Product image may differ from actual product

Universally consistent colors

Out of the box, you get remarkable color accuracy from screen to screen¹. Achieve precise, vibrant detail with 99% sRGB color gamut and WUXGA resolution.

Design pushed to the edge

Meticulously crafted with a razor-thin profile and frameless design, this stunning 24-inch diagonal screen monitor effortlessly powers your PC or Mac[®]. Get ultimate comfort with 4-way ergonomic adjustability.

Always on low blue light

Experience exceptional vibrancy with HP Eye Ease, the always on low blue light filter that reduces blue light exposure with zero impact to true color accuracy.

Sustainability in action



Responsibly reimagined

Make a conscious choice with this monitor that's been built with the environment in mind. Its plastics consist of over 80% recycled materials² plus it has 100% sustainably sourced and recyclable packaging³. It is ENERGY STAR[®] certified and EPEAT[®] 2020 registered⁴.



HP Z24u G3 WUXGA USB-C Display

Featuring



Easily connect multiple monitors

Declutter your desk and connect a series of displays by daisy chaining with a single DisplayPort™ cable.⁵

All the ports you need

Connect to a Workstation, a PC and additional displays.

Easily mount a Mini

Mount your HPZ2 Mini or HP Desktop Mini directly to the monitor for a clean workspace.⁶

HP Zero BrightDot Guarantee

Even if just a third of a pixel fails or is stuck in one position, HP will replace the entire display.⁷

Optional integrated audio

Easily attach the Z Display Conferencing Speaker Bar for stereo quality audio and dual microphones.⁸

3-year limited warranty

The assurance of HP's three-year standard limited warranty.

HP Z24u G3 WUXGA USB-C Display

Specifications

Display specifications

Display size
24"¹

Aspect ratio
16:10¹

Curvature
Flat

Native resolution
WUXGA (1920 x 1200)¹

Resolution (maximum)
WUXGA (1920 x 1200 @ 60 Hz)

Resolutions supported
640 x 480; 800 x 600; 1024 x 768; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1600 x 1200; 1680 x 1050; 1920 x 1080; 1920 x 1200

Panel type
IPS¹

Bezel
4-sided micro-edge

Panel bit depth
8 bit (6 bit + 2 FRC)

Display colors
Up to 16.7 million colors supported (through FRC technology)

Display color gamut
99% sRGB; 85% DCI-P3

Display scan frequency
50-60 Hz (Vertical) 30-80 KHz (Horizontal)

Response time
5ms GtG (with overdrive)¹

Brightness
350 nits¹

Contrast ratio
1000:1 (Static)¹ 10000000:1 (Dynamic)¹

Pixel pitch
0.270 mm

Pixels per inch (ppi)
96 ppi

Viewing angle
178° (Vertical) 178° (Horizontal)

Backlight type
Edge-lit

Display features
Language selection; On-screen controls; Anti-glare; Height Adjust/Tilt/Swivel/Pivot

Display User Control Options
Exit; Information; Management; Power control; Input control; Menu control; Brightness+; Image; Color

Management software
HP Display Center; HP Display Manager

Low blue light modes
Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)

Flicker-free
Yes

Screen treatment
Anti-glare

Hardness
3H

VESA mount
100 mm x 100 mm (bracket included)

Height adjustment range
150 mm

Tilt
-5 to +20°

Swivel
±45°

Pivot
±90°

Camera
No integrated camera

Microphone
No

Connectivity and communications

Port and connectors
1 HDMI 2.0
1 DisplayPort™ 1.4
1 DisplayPort™ 1.4-out
1 RJ-45
1 SuperSpeed USB Type-C® 5Gbps signaling rate (Up to 100W USB Power Delivery, Alt Mode DisplayPort™ 1.4)
4 SuperSpeed USB Type-A 5Gbps signaling rate
1 RJ-45 (10/100/1000 Mbps)
No
HDCP
Yes, DisplayPort™ and HDMI

Power supply
100 - 240 VAC 50/60 Hz (Internal)

Power consumption
160 W (maximum), 32 W (typical), 0.5 W (standby)

Logistics and Physical

Product color
Turbo silver head, turbo silver stand

Detachable stand
Yes

Physical security
Security lock-ready²

Dimensions without Stand (W x D x H)
20.93 x 1.52 x 13.5 in

Dimensions with stand (W x D x H)
20.93 x 7.68 x 20.53 in

Weight
11.69 lb (With stand.)

Packaged Dimensions (W x D x H)
24.61 x 16.34 x 5.59 in

Packaged weight
17.86 lb

Certification and compliance

Energy efficiency
ENERGY STAR® certified

Certifications
Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CEL; CEL Grade 1; cTUVus; EAC; FCC; GS Mark; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TUV-S; VCCI; Vietnam MEPS; WEEE; Low blue light; Ukraine Energy label; WW application; UAE⁵

Operating temperature range
41 to 95°F

Additional information

What's in the box
Monitor; Documentation; VESA Mount adapter; Cable manager; 1 USB Type-C® to Type-C cable; AC power cord; DisplayPort™ 1.4 cable⁴



HP Z24u G3 WUXGA USB-C Display

Footnotes

Messaging Footnotes

¹ All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

² Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT standard.

³ 100% outer box/corrugate cushion packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic. Excludes plastic bags and plastic foam sheeting.

⁴ Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.

⁵ Requires an additional DisplayPort™ cable to daisy chain.

⁶ Z2 Mini and Desktop mini and B550 Z Display G3 PC Mounting Bracket sold separately.

⁷ The HP Pixel Policy allows no bright sub-pixel defects for this display. For complete details, see <http://support.hp.com/us-en/document/c00288895>.

⁸ Z Display Conferencing Speaker Bar Sold Separately.

Technical Specifications Footnotes

¹ All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

² Lock sold separately.

³ Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. EPEAT® status varies by country. Visit www.epeat.net for more information.

⁴ Included cables may vary by country.

⁵ Monitors produced before June 1st 2024 comply with China regulation GB 21520-2015.

