

Product data sheet

Specifications



APC Universal Transfer Switch 10-Circuit 120/240V

UTS10BI

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V 240 V
Product or Component Type	Transfer switch
Main Output Voltage	120 V 240 V
Other Output Voltage	240 V
Input Connection Type	IEC 60320 C14
Number of cables	1
Provided Equipment	Bypass fast-ons Hardwire panel User Manual Installation guide Warranty card

Physical

Color	Black
Height	23.4 in (59.5 cm)
Width	15.5 in (39.4 cm)
Depth	3.3 in (8.4 cm)
Net Weight	27.6 lb(US) (12.5 kg)
mounting location	Front Side Top
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Input Frequency	47...63 Hz
Max line current	20 A

Conformance

Product Certifications	cTUVus
------------------------	--------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

Ambient Air Temperature for Operation	-13...104 °F (-25...40 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304247463
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26.7 in (67.9 cm)
Package 1 Width	8.4 in (21.3 cm)
Package 1 Length	18.7 in (47.5 cm)
Package 1 Weight	29.06 lb(US) (13.18 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)