

OVERVIEW



1. Power Connector	4. DP 1.4
2. HDMI 2.0	5. Audio line-out (3.5mm)
3. HDMI 2.0	

PERFORMANCE

Panel

Panel

VA

Backlight

WLED

Display Size

31.5 inches

Max View Area

WxH: 697.3 x 392.3 mm

Resolution

2560 x 1440

Aspect Ratio

16:9

Pixel Pitch

0.272 x 0.272 mm

Dot / Pixel Per Inch

93 dpi

Brightness

350 cd/m²

Contrast Ratio

- Contrast Ratio: 3500:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Moving Picture Response Time (MPRT): 0.5 ms
- Level 1: 4 ms
- Level 2: 3 ms
- Level 3: 2 ms
- Level 4: 1 ms
- Moving Picture Response Time (MPRT) improves the response time and reduces motion blur in the monitor. Enabling MPRT will disable AMD FreeSync™™ technology, and may causes a negligible flicker.

Refresh Rate

- DP: 165Hz (Overclock to 170Hz)

Overclocking at 170Hz is based on laboratory test data, and this function may cause irregularities in the display.
- HDMI®: 144Hz

Color Gamut

- Coverage Ratio: 99% sRGB
- Color Area Ratio: 119% sRGB
- Color Area Ratio: 90% DCI-P3

Color Support

16.7 Million

Color Depth

8-bit

Screen Surface Treatment

Anti-glare

Curvature

1500R

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Multi-Media

Camera

No bundled webcam (Support Lenovo® LC 50 Monitor Webcam, sold separately)

Speakers

Integrated Speakers, 2x 3W

Power Supply

Power Consumption

- Typical / Max: 35W / 70W
- Switch-off Mode: <0.3W
- Sleep / Off mode: <0.5W
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- Processor LUT: 10 bit
- HDR10 Compliance
- Natural Low Blue Light
- Lenovo Artery (Lenovo Display Control Center) Support
Lenovo Artery can only be used with Windows 10 & Windows 11
- AMD FreeSync
AMD FreeSync technology only can work with AMD Radeon™ series graphics card.

DESIGN

Mechanical

Bezel Width

- Side: 1mm
- Top / Bottom: 1mm / 24.4mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	709.8 x 278.7 x 458.3 mm (27.94 x 10.97 x 18.04 inches)
Highest Position	709.8 x 278.7 x 593.3 mm (27.94 x 10.97 x 23.36 inches)
Head Only	709.8 x 88.1 x 426.2 mm (27.94 x 3.47 x 16.78 inches)

Packaging Dimensions (WxDxH)

940 x 522 x 187 mm (37.00 x 20.55 x 7.36 inches)

Weight^[2]

Models	Weight
Monitor Head Only	6.2 kg (13.7 lbs)
Monitor With Stand	8.3 kg (18.3 lbs)

Packaging Weight

11.1 kg (24.5 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +22° tilt, up to 135mm lift

In the Box

- 1x DP Cable
- 1x Power cable
- Information flyer
- Monitor with Stand

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports^[1]

Rear Ports

- 2x HDMI 2.0
- 1x DisplayPort™ 1.4
- 1x audio-out (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

- 1-year courier or carry-in service
- 3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

