



**ThinkEdge**<sup>SE30</sup>

# Setup Guide





**Lenovo**

# Initial Setup



\* For selected models

# Overview



1. Power button
2. Serial connectors (2)
3. USB-C® connector (USB 3.2 Gen 2)
4. USB 3.2 connectors Gen 2 (2)
5. Headset connector
- \* 6. Wireless WAN antenna slot
7. Power adapter connector
8. DisplayPort™ connector / HDMI™ connector
9. USB 3.2 connector Gen 2
10. USB-C connector (Thunderbolt™ 4)
11. Ethernet connector
12. Ethernet connector
13. Security-lock slot
- \* 14. Wireless WAN antenna slot
- \* 15. Wi-Fi® antenna slot
- \* 16. Wireless WAN antenna slot
- \* 17. Reserved antenna slot

 Read the statement on USB transfer rate in the *User Guide*. Refer to the *Safety and Warranty Guide* for accessing the *User Guide*.

## E-manual


---




\* For selected models

## More Accessories

---



ThinkEdge SE30 IO BOX



ThinkCentre Tiny/Nano  
Monitor Clamp II



<https://support.lenovo.com/solutions/nanofeaturevideo>



# Additional information

## European Union — compliance with the Radio Equipment Directive

Hereby, Lenovo (Singapore) Pte. Ltd., declares that the radio equipment type ThinkEdge SE30 is in compliance with Directive 2014/53/EU.

The full text of the system EU declaration of conformity is available at the following Internet address:

<https://www.lenovo.com/us/en/compliance/eu-doc>

This radio equipment operates with the following frequency bands and maximum radio-frequency power:

Technology	Frequency band [MHz]	Maximum transmit power
WLAN 802.11b/g/n	2400 - 2483.5	< 20 dBm
WLAN 802.11a/n/ac	5150 - 5725	< 23 dBm
WLAN 802.11a/n/ac	5725 - 5875	< 13.98 dBm
Bluetooth BR/EDR/LE	2400 - 2483.5	< 20 dBm
Qualcomm Snapdragon X24 Modem- RF System (UMTS)	1/3/8	< 25.2 dBm
Qualcomm Snapdragon X24 Modem- RF System (LTE)	1/3/7/8/20/28/38/ 40/42/43	< 24.8 dBm

Technology	Frequency band [MHz]	Maximum transmit power
Qualcomm Snapdragon X55 5G Modem-RF System (UMTS)	1/8	< 24.5 dBm
Qualcomm Snapdragon X55 5G Modem-RF System (LTE)	1/3/7/8/20/28//34 /38/40/42	< 24.5 dBm
Qualcomm Snapdragon X55 5G Modem-RF System (5G NR)	1/3/7/8/20/28/38	< 24 dBm
Qualcomm Snapdragon X55 5G Modem-RF System (5G NR)	41/77/78	< 27 dBm

Usage of all the radio devices is limited to indoor in the band 5150 MHz to 5350 MHz (channels 36, 40, 44, 48, 52, 56, 60, 64).

LENOVO, LENOVO logo, THINKEDGE, and THINKEDGE logo are trademarks of Lenovo. DisplayPort is a trademark of the Video Electronics Standards Association. The terms HDMI and HDMI High-Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Wi-Fi is a registered trademark of Wi-Fi Alliance. USB-C is a registered trademark of USB Implementers Forum. Thunderbolt is a trademark of Intel Corporation or its subsidiaries in the U.S. and/or other countries. All other trademarks are the property of their respective owners. © 2021 Lenovo.

**First Edition (March 2021)**

**© Copyright Lenovo 2021.**

LIMITED AND RESTRICTED RIGHTS NOTICE: If data or software is delivered pursuant to a General Services Administration "GSA" contract, use, reproduction, or disclosure is subject to restrictions set forth in Contract No. GS-35F-05925.

**Reduce | Reuse | Recycle**

