



You are browsing the product catalog for

United States

DESKTOP PRINTERS

PC42E-T

The PC42E-T desktop printer is a compact, high-speed, and high-resolution desktop printing solution designed for mid-volume printing businesses that require reliable and continuous operation.

Overview



Feedback

Compact & Efficient Design

The PC42E-T is a reliable desktop printer, ideal for various industries like retail, transportation, logistics, light manufacturing, and warehousing.

High-Performance Printing

Featuring high-performance print heads, the PC42E-T delivers resolutions of 203 dpi or 300 dpi and fast printing speeds of up to 6 inches per second. This ensures high-quality output for applications such as logistics tracking and asset labeling.

User-Friendly Features

The printer includes an ECO button to reduce label waste and calibration time, as well as easy switching between 0.5-inch and 1-inch ribbon cores for versatile printing tasks.

Diverse Connectivity Options

Equipped with built-in Ethernet and USB hosting capabilities, the PC42E-T supports accessories like cutters, peelers, Wi-Fi, and Bluetooth, enhancing productivity and reducing cable dependency.

Smart Management Solutions

With Honeywell Printer Edge™ and OpIntel, the PC42E-T features remote management and real-time monitoring, improving printer speed and lower maintenance costs.

Industry Applications

Whether for receipts, tags, or labels, the PC42E-T maximizes productivity and meets the diverse needs of retail, logistics, and manufacturing environments.



FEATURES

Features	Compatible Software	Compatible Drivers
Multilingual	BarTender	Inter Driver Windows® printer driver, CUPS driver for Linux, Honeywell Device Types for SAP, Honeywell label design and print package
Application		
- Light Manufacturing - Retail - T&L - Warehouse		

DIMENSIONS

Overall Dimensions	Weight range	Image File Format
L x W x H: 268 mm x 198 mm x 168 mm (10.5 in x 7.8 in x 6.6 in)	2.04 kg (4.5 lb) kilogram	BMP, GIF, PCX, PNG

PRINTING SPECIFICATIONS

Print Speeds	Print Method	Resolutions	Feedback
•203 dpi: 1-6 ips •300 dpi:1-5 ips	•Thermal Transfer and Direct Transfer	•203 dpi/300dpi	
2D Barcodes •All major 2D barcodes			

MEDIA

Maximum Media Roll Diameter	Maximum Ribbon Length	Printer Media Type
127 5	300	Label, Ribbon

NETWORK

Wireless Communication	Bluetooth Specifications
Wifi 5.0 & Bluetooth 5.0 (optional)	Bluetooth 5.0 (optional)

SOFTWARE & FIRMWARE

Printer Command Language
Direct Protocol (DP), DPL, ZSim2 (ZPL II), ESim (EPL), XML enabled for SAP® All and Oracle® WMS

HARDWARE

Printer Connection Interface

- USB Device, USB Host, factory installed
- Internal Ethernet

ELECTRICAL

Operating Voltage

- 90~264V voltage

ENVIRONMENTAL

Operating Temperature

- +5°C to +40°C (+41°F to +104°F)

Storage Temperature

- 40°C to +60°C (-40°F to +140°F)

Operating Humidity

- 10 to 80% RH non- condensing

SERVICE TERMS

Warranty Duration

- 1 year

OTHERS

Print Technology

- Thermal Transfer

Print Resolution

- 203 dpi
- 300 dpi

Print Volume

- Up to 2,000

Connectivity

- Ethernet

Print Width

- 4 inch

Industry

- Aerospace
- Healthcare
- Logistics & Warehouses
- Manufacturing
- Retail

Feedback



Please sign in to view part numbers available for purchase based on your account

[Sign In](#)

Showing 1 to 10 of 10 parts

Q Search		
PART NUMBER	DESCRIPTION	ORDER ONLINE
3012-6754-001	KIT, ROLLER, PC300TPC42E-TOT800 SERIES	SIGN IN
3012-6755-001	KIT, PEEL OFF, PC310TPC42E-TOT820	SIGN IN
3012-6756-001	KIT, CUTTER, PC310TPC42E-TOT820	SIGN IN

PART NUMBER	DESCRIPTION	ORDER ONLINE
3012-6758-001	TPH 300DPI, PC300TPC42E-TOT800 SERIES	SIGN IN
3012-6761-001	KIT, WIFI&BT, ROW, PC310TPC42E-TOT820	SIGN IN
3012-6762-001	KIT, U2S CBL, PC300TPC42E-TOT800 SERIES	SIGN IN
PC42E-TB02200	PC42E-T, U, E, 200DPI, BK, 1&0.5, NO PC	SIGN IN
PC42E-TB02300	PC42E-T, U, E, 300DPI, BK, 1&0.5, NO PC	SIGN IN
PC42E-TW02300	PC42E-T, U, E, 300DPI, WH, 1&0.5, NO PC	SIGN IN

Rows 10 ▾

[Previous](#) [1](#) [Next](#)

Product Number



Please sign in to view part numbers available for purchase based on your account

[Sign In](#)


PART NUMBER	DESCRIPTION
3012-6754-001	KIT,ROLLER,PC300TPC42E-TOT800 SERIES
3012-6754-001	KIT,ROLLER,PC300TPC42E-TOT800 SERIES
3012-6755-001	KIT,PEEL OFF,PC310TPC42E-TOT820
3012-6755-001	KIT,PEEL OFF,PC310TPC42E-TOT820
3012-6756-001	KIT,CUTTER,PC310TPC42E-TOT820
3012-6756-001	KIT,CUTTER,PC310TPC42E-TOT820
3012-6757-001	TPH 203DPI,PC300TPC42E-TOT800 SERIES
3012-6757-001	TPH 203DPI,PC300TPC42E-TOT800 SERIES
3012-6758-001	TPH 300DPI,PC300TPC42E-TOT800 SERIES
3012-6758-001	TPH 300DPI,PC300TPC42E-TOT800 SERIES
3012-6761-001	KIT,WIFI&BT,ROW,PC310TPC42E-TOT820
3012-6761-001	KIT,WIFI&BT,ROW,PC310TPC42E-TOT820
3012-6762-001	KIT,U2S CBL,PC300TPC42E-TOT800 SERIES
3012-6762-001	KIT,U2S CBL,PC300TPC42E-TOT800 SERIES
PC42E-TB02200	PC42E-T,U,E,200DPI,BK,1&0.5,NO PC
PC42E-TB02200	PC42E-T,U,E,200DPI,BK,1&0.5,NO PC
PC42E-TB02300	PC42E-T,U,E,300DPI,BK,1&0.5,NO PC
PC42E-TB02300	PC42E-T,U,E,300DPI,BK,1&0.5,NO PC
PC42E-TW02300	PC42E-T,U,E,300DPI,WH,1&0.5,NO PC

Feedback

PC42E-TW02300

PC42E-T,U,E,300DPI,WH,1&0.5,NO PC


Complete Your Solution



Honeywell Operational Intelligence

Intelligence data insights, asset management and automation for specific pain points to improve functionality and increase ROI.

[→ LEARN MORE](#)



Honeywell Support Services

Maximize the value of your printers with complete support throughout the full lifecycle.

[→ LEARN MORE](#)

Feedback

Honeywell
Industrial Automation
855 S Mint St
Charlotte, NC 28202
800-582-4263

Product name
© Current year Honeywell International Inc.
All rights reserved.

[Safety and Productivity Solutions homepage](#)



This document was generated on (YYYY-MM-DD, HH:mm:ss). Subject to change without notice.

Feedback