


OVERVIEW



1. Headphone / microphone combo jack (3.5mm)	10. USB-A (USB 10Gbps)
2. USB-A (USB 10Gbps)	11. Ethernet (GbE RJ-45)
3. USB-A (USB 10Gbps), Always On	12. Punch out port 1 *
4. USB-C (USB 20Gbps)	13. Punch out port 2 *
5. DisplayPort 1.4a	14. DisplayPort 1.4a
6. USB-A (USB 5Gbps)	15. HDMI 2.1a FRL
7. HDMI 2.1 TMDs	16. DisplayPort 1.4a
8. USB-A (USB 5Gbps)	17. DisplayPort 1.4a
9. USB-A (USB 10Gbps)	

Notes:

- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

14th Generation Intel® Core™ i5 / i7 / i9 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i5-14500	14 (6 P-core + 8 E-core)	20	P-core 2.6GHz / E-core 1.9GHz	P-core 5.0GHz / E-core 3.7GHz	24MB	DDR5-4800	Intel® UHD Graphics 770
Core i5-14500T	14 (6 P-core + 8 E-core)	20	P-core 1.7GHz / E-core 1.2GHz	P-core 4.8GHz / E-core 3.4GHz	24MB	DDR5-4800	Intel® UHD Graphics 770
Core i7-14700	20 (8 P-core + 12 E-core)	28	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.4GHz / P-core 5.3GHz / E-core 4.2GHz	33MB	DDR5-5600	Intel® UHD Graphics 770
Core i7-14700T	20 (8 P-core + 12 E-core)	28	P-core 1.3GHz / E-core 0.9GHz	Max Turbo up to 5.2GHz / P-core 5.0GHz / E-core 3.7GHz	33MB	DDR5-5600	Intel® UHD Graphics 770
Core i9-14900	24 (8 P-core + 16 E-core)	32	P-core 2.0GHz / E-core 1.5GHz	Max Turbo up to 5.8GHz / P-core 5.4GHz / E-core 4.3GHz	36MB	DDR5-5600	Intel® UHD Graphics 770
Core i9-14900T	24 (8 P-core + 16 E-core)	32	P-core 1.1GHz / E-core 0.8GHz	Max Turbo up to 5.5GHz / P-core 5.1GHz / E-core 4.0GHz	36MB	DDR5-5600	Intel® UHD Graphics 770

AI (Artificial Intelligence)

NPU

- Discrete NPU card
- None

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- No preload operating system

Graphics

Graphics***[1]

Graphics	Type	Memory	Max Resolution	Connector	Key Features
Intel® UHD graphics 770	Integrated	Shared	4096x2160@60Hz(HDMI®), 1920x1200@60Hz(VGA), 4096x2304@60Hz(DP)	1x HDMI® 2.1 TMDS, 1x DP 1.4a (HBR2, DSC), 2x optional punch out ports (2x HDMI®/VGA/DP)	DirectX® 12
NVIDIA® GeForce RTX™ 4060	Discrete	8G GDDR6	7680x4320@60Hz(HDMI®), 7680x4320@60Hz(DP)	1x HDMI® 2.1a FRL, 3x DP 1.4a (HBR3, DSC)	DirectX® 12, OpenGL 4.6

Notes:

[1] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

Monitor Support

Monitor Support

Supports up to 8 independent displays. 4 displays support via onboard ports (1x DP, 1x HDMI® + 2x optional port [VGA / DP / HDMI®]), 4 displays support via discrete graphics ports (3x DP + 1x HDMI®)

Chipset

Chipset

Intel® Q670 chipset

Memory

Max Memory^[1]

Up to 64GB DDR5-5200

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Memory Type

- DDR5-4800
- DDR5-5200
- DDR5-5600

Memory Protection

Non-ECC

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Storage Support^[1]

Dual SSD mode: up to two drives, 2x M.2 SSD

- M.2 2280 SSD up to 2TB

Storage Type^{***}

Disk Type	Interface	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	Opal 2.0
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4 Performance	Opal 2.0

RAID

RAID 0/1 support for SSDs

Notes:

[1] The max capacity of each disk type is based on the test results with current Lenovo® storage offerings.

Removable Storage

Optical

None

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio

Speakers

Single speaker, 2W x1

Power Supply

Power Supply

Power	Type	Key Features
350W	Fixed	100-240V, 50-60Hz

DESIGN

Input Device

Keyboard**

- Wireless EOS Keyboard, black
- Lenovo® Calliope Keyboard (USB connector), black
- No keyboard

Mouse**

- Wireless EOS Mouse, black
- Lenovo® Calliope Mouse (USB connector), black
- No mouse

Mechanical

Form Factor

Tiny (3.6L)

Dimensions (WxDxH)^[1]

195 x 191 x 108 mm (7.68 x 7.52 x 4.25 inches)

Packaging Dimensions (WxDxH)

538 x 240 x 290 mm (21.18 x 9.45 x 11.42 inches)

Weight^[2]

Around 3.5 kg (7.72 lbs)

Packaging Weight

Around 5.7 kg (12.57 lbs)

Case Color

Luna grey

Expansion Slots

Four M.2 slots (one for WLAN, one for AI Card, two for SSD)

EOU

EOU design for M.2 SSD and memory installation.

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, Intel® Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

Optional Ethernet

No optional Ethernet

WLAN + Bluetooth®**

- Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, Intel® vPro® technology support, M.2 Card
- Intel® Wi-Fi® 7 BE200, 802.11be 2x2 Wi-Fi® + Bluetooth® 5.3 (Bluetooth® 5.4 hardware ready), Intel® vPro® technology support, M.2 Card
- No WLAN and Bluetooth®

Ports^[1]

Front Ports

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports 5V@2.1A charging
- 1x headphone / microphone combo jack (3.5mm)
- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only

Rear Ports^[2]

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x HDMI® 2.1 TMDS
- 1x Ethernet (GbE RJ-45)
- 1x HDMI® 2.1a FRL
- 4x DisplayPort™ 1.4a

Optional Rear Ports

- Punch out port 1 (one of VGA / DisplayPort™ / HDMI® / serial / USB-C® (USB 5Gbps) with DisplayPort™ function)
- Punch out port 2 (one of VGA / DisplayPort™ / HDMI® / serial / 2.5GbE RJ-45)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

[2] For video ports on discrete graphics, please see graphics section.

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

Physical Locks

Kensington® Security Slot™

Chassis Intrusion Switch

Chassis intrusion switch

Fingerprint Reader

No fingerprint reader

BIOS Security

- Administrator password
- Power-on password
- Hard disk password
- Individual USB port disablement
- Smart USB protection (allows keyboard / mouse only, blocks all storage devices)

MANAGEABILITY

System Management

System Management^[1]

- Intel® vPro® Enterprise
- Non-vPro®

Notes:

[1] Intel® vPro® offers a superset of DASH's defined capabilities.

SERVICE

Warranty^[1]

Base Warranty**

- 1-year courier or carry-in service
- 1-year limited onsite service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

OPERATING REQUIREMENTS

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

Relative Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

ENVIRONMENTAL

Sustainability

Material

50% Recycled & 50% Hydroelectric Aluminum
35% PCC recycled PC/ABS with coconut shell powder
85% PCC recycled plastic used in product chassis
95% PCC recycled plastic used in USB keyboard/mouse
90% PIC recycled plastic EPE cushion
30% OBP used in bag
FSC certified paper in packaging

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- (Optional) ENERGY STAR® 8.0
- (Optional) EPEAT™ Gold Registered
- ErP Lot 3
- GREENGUARD®
- RoHS compliant
- TCO Certified

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications

Other Certifications

(Optional) TÜV Rheinland® Low Noise

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES

OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

