Manual Supplement

Manual Title:	377/377 FC/378/378 FC Calibration Manual	**Supplement Issue:**	1
Print Date:	8/2021	**Issue Date:**	12/23
Revision/Date	Rev. 1, 9/23	**Page Count:**	1

This supplement contains information necessary to ensure the accuracy of the above document.

© 2023 Fluke Corporation. All rights reserved.

FLUKE®

Change #1, 352, 682

On page 10, in **Table 2. Performance Test and Readout Limits**, replace the iFlex rows with:

Table 2. Performance Test and Readout Limits

Test (Switch Position)	Calibrator Output	52120A Range	Readout Limit	
			Low	High
iFlex **iFlex Current Probe (with ac voltage simulation)**	1.05 mV @ 35 Hz	NA	48.0 A	52.0 A
	3 mV @ 100 Hz			
	15 mV @ 500 Hz			
	11.4 mV @ 20 Hz		921.0 A	979.0 A
	57 mV @ 100 Hz			
	285 mV @ 500 Hz			
	29.4 mV @ 20 Hz		2372 A	2529 A
	147 mV @ 100 Hz			
	735 mV @ 500 Hz			