



Projector feature comparison

		MC453X MC423W ME453X ME423W ME403U	M380HL M430WL	M401H M421W	P474W P474U P554W P554U	PE506WL PE506UL	PE456USL	P547UL P627UL	P601Q P721Q	PA803U P853W	PA804UL PA1004UL	PA1505UL PA1705UL	PV710UL PV800UL	PX1004UL	X141Q	PX2200UL
PROJECTOR FEATURE	Status	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Shipping	Sep-24	Shipping
	Technology	LCD	DLP (1-chip)	DLP (1-chip)	LCD	LCD	LCD	LCD	DLP (1-chip)	LCD	LCD	LCD	LCD	DLP	DLP	DLP (1-chip)
	Light Source	Lamp	Laser / Phosphor	Laser / Phosphor	Lamp	Laser / Phosphor	Laser / Phosphor	Laser / Phosphor	Laser / Phosphor	Lamp	Laser / Phosphor	Laser / Phosphor	Laser / Phosphor	Laser / Phosphor	Laser / Phosphor	Laser / Phosphor
	Speaker	16W	10W	8W	20W	16W	16W	20W	10W x 2	-	-	-	-	-	-	-
GEOMETRY CORRECTION	Keystone	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical	Horizontal & Vertical
	Auto Keystone	X	-	Vertical	-	-	-	-	-	-	-	-	-	-	-	-
	3D Reform / Cornerstone / Pincushion	X	X	X	X	X	X	X	X	X	X	X	-	X	X	X
	Geometric Correction Tool	-	-	-	X	-	-	ProAssist	-	X	X	X	ProAssist	X	X	X
	Stacking Correction Tool	-	-	-	-	-	-	-	-	X	X	X	-	X	X	-
CONTROL (Network and RS232)	PC Control 3.0	-	-	-	-	-	-	-	-	X	X	X	-	-	-	-
	PC Control PRO 3.0	-	-	-	-	-	-	-	-	X	X	X	-	-	-	-
	PC Control PRO 4.0	-	-	-	-	-	-	-	-	X	X	X	-	X	X	-
	PC Control PRO 5.0 (Mac OS)	-	-	-	-	-	-	-	-	X	X	X	-	X	X	-
	Naviset Administrator 2.0	X	-	-	X	X	X	X	X	X	X	X	X	X	X	X
	Virtual Remote	X	-	-	X	-	-	X	-	X	X	X	-	X	X	X
	Auto Power ON (via COMP/HDMI)	-	X	X	X	-	-	X	-	X	X	X	-	X	X	X
	Auto Power OFF (via Timer)	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
	Windows Network Projector (Video transmission)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
NETWORKING	ProAssist	-	-	-	-	-	-	X	-	-	X	X	X	X	X	X
	Windows Remote Desktop	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	Windows Network Drive Function	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	Windows Media Connect Function	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	Image Express Utility 2.0 (Video transmission)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	Image Express Utility Lite (USB Display)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	MultiPresenter	X	-	-	-	X	X	X	-	-	-	-	-	-	-	-
	Desktop Control	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	Crestron RoomView	X	-	-	X	X	X	X	X	X	X	X	X	X	X	X
AMX BEACON	X	-	-	X	-	-	X	X	X	X	X	X	X	X	X	
Optional lenses	-	-	-	-	-	-	-	-	X	X	X	X	X	X	X	
Panasonic Lens Support	-	-	-	-	-	-	-	-	-	-	-	-	X	-	-	
Motorized Zoom, Focus & Lens Shift	-	-	-	-	-	-	-	-	X	X	X	X	X	X	X	
Lens shift	-	X	-	X	X	-	X	X	X	X	X	X	X	X	X	
Lens Memory	-	-	-	-	-	-	-	-	-	X	X	X	-	-	X	
Variable Audio Out	X	X	X	X	X	X	X	X	X	X	X	X	X	-	-	
Auto Focus	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Tilt Free	-	X	X	-	X	X	X	X	X	X	X	X	X	X	X	
Roll Free / Portrait	-	-	-	-	X	X	X	X	X	X	X	X	X	X	X	
Advanced AccuBlend	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
Wall Color Correction	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
Software Edge Blending (MST)	-	-	-	-	-	-	-	-	X	-	-	-	-	-	-	
Hardware Edge Blending	-	-	-	-	-	-	-	-	X	X	X	-	X	X	X	
BrilliantColor™	-	-	-	-	-	-	-	-	-	-	-	-	-	X	X	
DynamicBlack™	-	-	-	-	-	-	-	-	-	-	-	-	-	X	X	
Direct Power On	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
Direct Power Off	-	-	-	X	X	X	X	X	X	X	X	X	X	X	X	
Quick Power Off	X	X	X	X	X	X	X	X	X	-	-	-	X	X	-	
DICOM-Sim	-	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
Multi-Screen Compensation	-	-	-	-	-	-	-	-	X	X	X	-	X	X	X	
Eco-Mode™	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
Closed Caption	X	X	-	X	-	-	-	-	X	-	-	-	-	-	-	
Picture-in-Picture	-	-	-	-	-	-	-	-	X	X	X	-	X	X	X	
Picture-by-Picture	-	-	-	-	-	-	-	-	X	X	X	-	X	X	X	
3-D Ready (Active 3D)	-	-	-	-	-	-	-	-	X	X	X	-	X	-	X	
Passive 3D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Office Viewer	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
CONNECTIONS	5pin	X	X	-	X	X	X	X	-	X	X	X	-	X	X	X
	15pin	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	5BNC	-	-	-	-	-	-	-	-	-	-	-	-	X	X	
	HDBaseT	-	-	-	X	-	-	X	X	X	X	X	X	X	X	
	DVI	-	-	-	-	-	-	-	-	-	-	-	-	-	X	
	HDMI	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
	HDMI	X	X	X	X	X	X	X	X	X	X	X	X	-	X	
	DisplayPort	-	-	-	-	-	-	-	-	X	X	X	-	X	X	
	DisplayPort	-	-	-	-	-	-	-	-	-	-	-	-	Optional	-	
	3G-SDI	-	-	-	-	-	-	-	-	-	-	-	-	-	X	
	Composite Video	X	X	-	X	-	-	-	-	-	-	-	-	-	-	
	S-Video	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Component (shared with 15pin input)	-	-	-	-	-	-	-	-	-	-	-	-	X	-	
	Component (shared with 5BNC input)	-	-	-	-	-	-	-	-	-	-	-	-	X	-	
	OPS Option Slot	-	-	-	-	-	-	-	-	-	-	-	-	X	-	
	Monitor Out (loop out)	X	-	-	X	X	X	X	-	X	X	X	-	X	X	
	USB Viewer	X	X	-	X	X	X	X	X	-	-	-	-	-	-	
RS232 (9pin)	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
RJ45	X	-	-	X	X	X	X	X	X	X	X	X	X	X		
Wireless LAN	Optional	-	-	Optional	Optional	Optional	Optional	Optional	-	-	-	-	-	-		