ThinkEdge SE30n Gen2 13LV000CUT





The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core 5 120U, 10C (2P + 8E) / 12T, P-core 1.4 / 5.0GHz, E-core 0.9 / 3.8GHz, 12MB Intel Smart Cache
- 1x 16GB SODIMM DDR5-5600
- 512GB SSD M.2 2280 PCIe 4.0x4 NVMe Opal 2.0
- Integrated Intel Graphics
- Windows 11 IoT Enterprise LTSC 2024, English
- Case color - Black
- 3-year, Onsite

Premier Support - A direct 24x7x365 line to our most elite technicians.

- Advanced technical support, 24x7x365, in more than 100 markets
- Comprehensive hardware & OEM software support
- Single point of contact for simplified end-to-end case management
- Technical Account Managers for proactive relationship and escalation management
- Priority on service delivery and repair parts
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories

UAE (United Arab Emirates)



ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792



Lenovo Ultra High Speed HDMI™ Cable 1.8m

4X91U92141



Lenovo Analog In-Ear Headphones Gen II Bulk Package (20pcs)

4XD1T54899

>> View More Accessories

Recommended Services

Best

5Y Onsite upgrade from 3Y Onsite (5WS1U63800)

Better

4Y Onsite upgrade from 3Y Onsite (5WS1U63834)

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkEdge SE30n Gen2 13LV000CUT

PERFORMANCE

Processor
Intel Core™ 5 120U, 10C (2P + 8E) / 12T, P-core 1.4 / 5.0GHz, E-core 0.9 / 3.8GHz, 12MB Intel® Smart Cache

Graphics
Integrated Intel® Graphics

Chipset
Intel® SoC Platform

Memory
1x 16GB SODIMM DDR5-5600

Max Memory
Up to 48GB DDR5-5200

Memory Slots
One DDR5 SODIMM slot

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support
Up to two drives, 1x M.2 SATA SSD + 1x M.2 SSD • M.2 2280 SSD up to 2TB each • M.2 2242 SATA SSD up to 1TB each

Power Supply
90W 88% Adapter

DESIGN

Keyboard
None

Mouse
None

Case Color
Black

Mounting
None

Dimensions (WxDxH)
179 x 125 x 38.7 mm (7.05 x 4.92 x 1.52 inches)

Weight
Around 1.1 kg (2.43 lbs)

CONNECTIVITY

Ethernet
Intel® I219-LM + Intel® I226-V 2.5G, 2x RJ-45

WLAN + Bluetooth
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

WWAN
WWAN Not Supported

Optional Left Ports (configured)
Flexible I/O support one of DIO (4DI / 4DO) or CAN (OPEN)

Front Ports
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 1x microphone-in (3.5mm)
- 1x headphone / microphone combo jack (3.5mm)
- 2x serial (RS232 / RS422 / RS485, BIOS selectable)

Rear Ports
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 4x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 4x HDMI® 2.1 TMDS
- 1x 12V DC-in with lockable DC jack
- 1x 2.5GbE Ethernet (RJ-45)
- 1x Ethernet (RJ-45)

Optional Rear Ports (configured)
Flexible I/O (DIDO)

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified

Physical Locks
Kensington Security Slot™, 3 x 7 mm

Other Security
Hardware Watch Dog Timer

MANAGEABILITY

System Management
Intel® vPro®

SERVICE

Base Warranty
3-year, Onsite

Included Upgrade
None

ENVIRONMENTAL

Operating Temperature
Standard Temperature 0℃ to 50℃ (32℉ to 122℉)

CERTIFICATIONS

Green Certifications
- GREENGUARD®
- RoHS compliant

Other Certifications
Red Hat Enterprise Linux Certified

SOFTWARE


Operating System
Windows® 11 IoT Enterprise LTSC 2024, English

ACCESSORIES

Bundled Accessories
None

MODEL

TopSeller	: Yes	**EAN / UPC / JAN**	: 199275164842
Announce Date	: 2026-03-30	**End of Support**	: 2032-09-27



Product image is a sample, it may not match the real color of this model

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.