

# Product data sheet

Specifications



## APC 24 Port 10/100 Ethernet Switch



AP9224110

⚠ Discontinued on: Jun 30, 2024

⚠ To be discontinued

### Overview

Lead time Usually in Stock

### Main

|                       |   |
|-----------------------|---|
| Main Input Voltage    | 100 V<br>120 V<br>200 V<br>208 V<br>230 V |
| Input Connection Type | IEC 60320 C14                             |
| Number of rack unit   | 1U  |
| Number of cables      | 1   |
| Provided equipment    | User Manual<br>Rack Mounting brackets     |

### Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Black                 |
| Height              | 1.5 in (3.7 cm)       |
| Width               | 9.8 in (25 cm)        |
| Depth               | 5.2 in (13.2 cm)      |
| Net Weight          | 2.60 lb(US) (1.18 kg) |
| Mounting Location   | Front<br>Rear         |
| Mounting preference | No preference         |
| Mounting Mode       | Rack-mounted          |

### Conformance

|                        |                                      |
|------------------------|--------------------------------------|
| Product Certifications | cUL Listed<br>CE<br>TÜV<br>UL Listed |
| Standards              | EN 60950<br>FCC Part 15 class A      |

### Environmental

|                                       |                         |
|---------------------------------------|-------------------------|
| Ambient Air Temperature for Operation | 32...113 °F (0...45 °C) |
| Relative Humidity                     | 10...90 %               |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

|  |                          |
|--|--------------------------|
| <b>Ambient Air Temperature for Storage</b> | 5...149 °F (-15...65 °C) |
| <b>Storage Relative Humidity</b>           | 10...90 %                |

---

## Ordering and shipping details

---

|             |              |
|-------------|--------------|
| <b>GTIN</b> | 731304226635 |
|-------------|--------------|

## Packing Units

---

|                                     |                   |
|-------------------------------------|-------------------|
| <b>Unit Type of Package 1</b>       | PCE               |
| <b>Number of Units in Package 1</b> | 1                 |
| <b>Package 1 Height</b>             | 4.02 in (10.2 cm) |
| <b>Package 1 Width</b>              | 8.4 in (21.3 cm)  |
| <b>Package 1 Length</b>             | 20.5 in (52.1 cm) |
| <b>Package 1 Weight</b>             | 4.4 lb(US) (2 kg) |

## Contractual warranty

---

|                 |                           |
|-----------------|---------------------------|
| <b>Warranty</b> | 2 years repair or replace |
|-----------------|---------------------------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

**Weee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile [End of Life Information](#)