





ACC-MBF




⚠ WARNING

ENG - Before installing make sure the supporting surface will support the combined load of the equipment and hardware. Screws must be tightly secured. Do not overtighten screws or damage can occur and product may fail. Never exceed the Maximum Load Capacity. Always use an assistant or mechanical lifting equipment to safely lift and position equipment. This product is intended for indoor use only. Use of this product outdoors could lead to product failure or personal injury. Be careful not to pinch fingers when operating the mount. For support please call customer care at 1-800-865-2112.


ENG Symbols



ENG WARNING



ENG Skip to step.




ENG Do not overtighten screws.




ENG Screws must get at least three full turns and fit snug.



ENG To properly tighten screws: Tighten until screw head makes contact, then tighten another 1/2 turn. Do not overtighten screws.



ENG Tools Needed for Assembly.




[ENG] Parts (Before beginning, make sure you have all parts shown below).

Parts List		
Description	Qty	Part#
A retaining collar	1	1800-375
B large washer	1	540-9432
C 4mm allen wrench	1	560-9646
D main frame	1	10021679-RBLK
E main post	1	146-1434
F carriage bolt	4	520-1175
G small washer	4	540-9440
H nylock nut	4	530-9413
I hex head screw	20	520-1321
J #10 x 1/2" phillips screw	2	520-1320
K M5 x 10mm socket pin screw	1	520-1164
L support bracket	2	146-1053
M 1/4-20 x 1/2" phillips screw	2	510-9108


B (1)

large washer




C (1)

4mm allen wrench




A (1)

retaining collar




D (1)

main frame




E (1)

main post




F (4)

carriage bolt




G (4)

small washer




H (4)

nylock nut




I (20)

hex head screw




J (2)

#10 x 1/2" phillips screw




K (1)

M5 x 10mm socket pin screw




L (2)

support bracket






M (2)


1/4-20 x 1/2"




1





2




3-1



3-2





3-3




3-4




ENG Align slot of extension column





4-1







4-2









ENG Loosen, adjust, tighten.





I (6)



ENG This page intentionally left blank.

ENG	Warranty	ESP	Garantía	FRN	Garantie	DEU	Garantie	NEL	Garantie
ITL	Garanzia	ČES	Záruka	SLK	Záruka	POR	Garantia	TÜR	Garanti

www.peerless-av.com/warranty • www.peerless-av.com • www.peerless-av.com/patents

peerless-AV®

Peerless-AV
2300 White Oak Circle
Aurora, IL 60502, USA
info@peerless-av.com

(800) 865-2112
(630) 375-5100

Peerless-AV EMEA
Unit 2, Curo Park
Frogmore, St. Albans,
Hertfordshire, AL2 2DD
United Kingdom

+44 (0) 1923 200 100

Peerless-AV B.V.
Papendorpseweg 75
3528 BJ Utrecht
The Netherlands

+31 (0) 70 770 8037

Peerless-AV Latin America
Av. de las Industrias 413
Parque Industrial Escobedo
General Escobedo N.L.,
México 66062

+52 (81) 8384-8300