




SAMSUNG




BN68-23476A-01

Unpacking and Installation Guide
Guide de déballage et d'installation
Guía de desembalaje e instalación
Manual de desempacotamento e instalação
Руководство по распаковке и установке
Посібник з розпаковки та встановлення
Қаптамадан шығару және орнату нұсқаулығы




1


43"- 55"




65"



75"




85"




2

43"- 65"




75"- 85"









3

43"- 65"






3





75"- 85"



4




5



	A	B	C	D	E	F	G	H
BE43FX-**-	37.7 inches (957.8 mm) (957.8 mm) (95.78 cm)	22.0 inches (558.8 mm) (558.8 mm) (55.88 cm)	3.0 inches (76.3 mm) (76.3 mm) (7.63 cm)	24.0 inches (609.0 mm) (609.0 mm) (60.90 cm)	6.2 inches (157.0 mm) (157.0 mm) (15.70 cm)	42.5 inches (107.9 cm) (107.9 cm)	14.1 lbs (6.4 kg) (6.4 кг)	14.6 lbs (6.6 kg) (6.6 кг)
BE50FX-**-	43.7 inches (1110.8 mm) (1110.8 mm) (111.08 cm)	25.3 inches (643.8 mm) (643.8 mm) (64.38 cm)	3.0 inches (76.4 mm) (76.4 mm) (7.64 cm)	27.4 inches (695.1 mm) (695.1 mm) (69.51 cm)	7.8 inches (199.0 mm) (199.0 mm) (19.90 cm)	49.5 inches (125.7 cm) (125.7 cm)	18.3 lbs (8.3 kg) (8,3 кг)	19.0 lbs (8.6 kg) (8,6 кг)
BE55FX-**-	48.2 inches (1224.6 mm) (1224.6 mm) (122.46 cm)	27.9 inches (707.8 mm) (707.8 mm) (70.78 cm)	3.0 inches (76.6 mm) (76.6 mm) (7.66 cm)	29.9 inches (759.1 mm) (759.1 mm) (75.91 cm)	7.8 inches (199.0 mm) (199.0 mm) (19.90 cm)	54.6 inches (138.7 cm) (138.7 cm)	21.2 lbs (9.6 kg) (9,6 кг)	21.8 lbs (9.9 kg) (9,9 кг)
BE65FX-**-	56.9 inches (1444.1 mm) (1444.1 mm) (144.41 cm)	32.7 inches (831.2 mm) (831.2 mm) (83.12 cm)	3.0 inches (76.8 mm) (76.8 mm) (7.68 cm)	34.7 inches (882.2 mm) (882.2 mm) (88.22 cm)	8.7 inches (222.0 mm) (222.0 mm) (22.20 cm)	64.5 inches (163.9 cm) (163.9 cm)	31.3 lbs (14.2 kg) (14,2 кг)	32.0 lbs (14.5 kg) (14,5 кг)
BE75FX-**-	65.7 inches (1668.1 mm) (1668.1 mm) (166.81 cm)	37.7 inches (957.8 mm) (957.8 mm) (95.78 cm)	3.0 inches (77.0 mm) (77.0 mm) (7.70 cm)	39.6 inches (1005.9 mm) (1005.9 mm) (100.59 cm)	11.0 inches (280.0 mm) (280.0 mm) (28.00 cm)	74.5 inches (189.3 cm) (189.3 cm)	49.4 lbs (22.4 kg) (22,4 кг)	50.3 lbs (22.8 kg) (22,8 кг)
BE85FX-**-	74.4 inches (1889.9 mm) (1889.9 mm) (188.99 cm)	42.7 inches (1083.5 mm) (1083.5 mm) (108.35 cm)	3.0 inches (77.0 mm) (77.0 mm) (7.70 cm)	44.6 inches (1132.8 mm) (1132.8 mm) (113.28 cm)	12.8 inches (326.0 mm) (326.0 mm) (32.60 cm)	84.5 inches (214.7 cm) (214.7 cm)	63.3 lbs (28.7 kg) (28,7 кг)	64.4 lbs (29.2 kg) (29,2 кг)

*: 0-9, A-Z



	VESA A x B (mm) VESA A x B (mm)	C (mm) C (mm)	D x 4
BE43FX-**-	200 x 200	23-25	M8
BE50FX-**-			
BE55FX-**-			
BE65FX-**-			
BE75FX-**-	400 x 300	10-12	
BE85FX-**-			

*: 0-9, A-Z